

Motor Circuit Protector Time/Current Curves

Series C – Type HMCP, 3 Pole

Maximum Voltage	Maximum Current
600 V., Ac (50/60 Hz)	1200 A.

Catalog Number	Instantaneous Pick-Up Settings (Amperes)						
3-Pole	A	B	C	D	E	F	G
HMCP12Y8W	2400	3600	4800	6000	7200	8400	9600

Note:
Motor circuit protectors are for use only in combination controllers.

Typical Trip Unit Nameplate

Push to Trip — Engaged — Open
Instantaneous Trip — A B C D E F G — See Amps Above
HMCP
DIGITRIP RMS 310
TRIP UNIT
TEST

Adjusts all poles.