

Eaton 5E UPS

650 – 2000VA



Essential power protection for workstations and POS equipment

Performance

- The Eaton 5E UPS provides effective power protection, even in disturbed electrical environments. Voltage fluctuations are automatically corrected using an AVR device (booster/fader), without needing the batteries.

Reliability

- Trust a leading manufacturer with decades of experience dedicated to developing reliable power quality equipment
- Rely on batteries anytime: 5E batteries are permanently recharged (even when the UPS is turned off but mains is present). 5E can start without mains (Cold-start).

Versatility

- 5E's compact form factor allows it to be easily integrated into environments with space constraints.
- The 5E features an HID-compliant USB port, for automatic integration with common operating systems (Windows/ Mac OS/Linux). 5E is compatible with Eaton UPS Companion power management software.
- 650 & 850VA models have no fan so are perfect for deployment at an operators workstation, where fan noise can be an issue.

Made for the local ANZ market

- ANZ general purpose outlets are features on all models, no need for conversion cables.

Ideal for protecting:

- Workstations
- Business Telephony
- Routers
- Point-of-sale equipment



Powering Business Worldwide

Eaton 5E UPS

1. LED user interface - On/Off button
2. USB port
3. Battery replacement panel
4. Fixed input cord
5. ANZ outlets
6. Fan



Eaton 5E UPS (1100 - 2000VA)

Technical Specifications	650	850	1100	1500	2000
Rating (VA/W)	650VA/360W	850VA/480W	1100VA/660W	1500VA/900W	2000VA/1200W
Electrical Characteristics					
Technology	Line-Interactive (AVR with Booster + Fader)				
Input voltage range	170-280V				
Output voltage	230V				
Frequency	50-60 Hz autoselect				
Connections					
Number of AUS outlets	2		3		
Batteries					
Typical backup times for 1 PC*	16 min	20 min	45 min	50 min	50 min
Typical backup times for 2 PC*	6 min	8 min	20 min	26 min	26 min
Typical backup times for 3 PC*	-	-	7 min	10 min	10 min
Typical backup times for 4 PC*	-	-	-	-	5 min
Battery management	Permanent battery charge, cold start				
Communication					
User Interface	LED				
Communication	Port HID-compliant USB port for automatic integration with most common operating systems (Windows Vista, 7 & 8, Linux, Mac OS X)				
Standards					
Safety & EMC	IEC/EN 62040-1, IEC/EN 62040 -2, C-Tick				
Dimensions & Weight					
Dimensions H x W x D	148 x 100 x 288 mm		180 x 133 x 330 mm		
Weight	4.6kg	5.1kg	9.3kg	10.5kg	10.5kg
Customer Service & Support					
Warranty	12 months				
Part Numbers					
5E	5E650iUSB-AU	5E850iUSB-AU	5E1100iUSB-AU	5E1500iUSB-AU	5E2000iUSB-AU

* Backup times are approximate and may vary with equipment, configuration, battery age, temperature, etc.



Eaton Australia:
 Eaton Industries Pty. Ltd.
 Electrical Sector
 10 Kent Road Mascot,
 NSW 2020 Australia
 1300 UPS UPS (1300 877 877)
www.eaton.com/powerquality

Eaton New Zealand:
 Eaton Industries Company
 Electrical Sector
 1 Barry Hogan Place,
 Christchurch 8041 NZ
 0508 EATON NZ (0508 328 6669)
www.eaton.com/powerquality

Eaton is a registered trademark of Eaton © 2013

All other trademarks are property of their respective owners.

Switch ON to Eaton.

778PQ

In the interests of continuous product improvement all specifications are subject to change without notice. © 2014 Eaton All Rights Reserved.