

Eaton 9SX Tower AU Models Estimated Autonomy Time in Minutes

% of rated load (at 0.9pf)	10%	20%	30%	40%	50%	60%	70%	80%	90%	100%
9SX700I-AU	62	37	23	18	13	10	8	7	6	5
9SX1000I-AU	63	36	27	19	16	12	10	8	7	6
9SX1000I-AU + 1 EBM	233	137	99	73	60	48	41	35	31	28
9SX1000I-AU + 2 EBM	449	248	176	135	109	90	76	66	57	50
9SX1000I-AU + 3 EBM	591	392	267	199	162	135	111	98	86	76
9SX1000I-AU + 4 EBM	871	503	384	266	221	175	153	133	113	103
9SX1500I-AU	84	41	28	20	15	11	9	8	6	5
9SX1500I-AU + 1 EBM	309	154	103	76	59	48	40	36	29	27
9SX1500I-AU + 2 EBM	542	276	184	141	108	88	74	66	54	48
9SX1500I-AU + 3 EBM	855	443	275	208	161	132	109	99	82	73
9SX1500I-AU + 4 EBM	1076	542	400	276	219	170	150	134	109	99
9SX2000I-AU	95	47	31	23	19	14	11	9	8	7
9SX2000I-AU + 1 EBM	466	220	154	112	88	68	59	50	43	38
9SX2000I-AU + 2 EBM	855	450	285	217	165	134	112	97	83	73
9SX2000I-AU + 3 EBM	1140	611	465	343	255	200	168	148	126	110
9SX2000I-AU + 4 EBM	1774	887	561	468	367	270	233	199	167	152
9SX3000I-AU	80	42	28	20	15	11	9	8	6	6
9SX3000I-AU + 1 EBM	285	156	103	75	58	48	40	34	29	28
9SX3000I-AU + 2 EBM	527	279	184	140	107	88	74	63	55	49
9SX3000I-AU + 3 EBM	814	447	275	207	160	133	109	94	83	75
9SX3000I-AU + 4 EBM	1045	546	400	274	217	171	150	127	109	101
9SX6KI-AU	122	51	30	22	16	13	10	8	7	6
9SX6KI-AU + 1 EBM	506	198	122	84	59	50	41	34	30	27
9SX6KI-AU + 2 EBM	912	418	219	160	110	95	77	66	58	51
9SX6KI-AU + 3 EBM	1140	570	380	226	168	147	119	101	88	76
9SX6KI-AU + 4 EBM	1646	823	506	353	220	195	164	141	122	106

Notes:

- Actual runtime may vary from +/- 15% dependant on environment and battery age
- Runtime values in red are not encouraged, please consult with an Eaton engineer for verification

