Vickers®

Relief Valves

Balanced Piston Type Relief Valves

CG-H06-BV-50
CG-H06-CV-50
CG-H06-FV-50

Model	■ Spring	Pressure Range PSI	■ Included in Cover S/A
CG-H06-BV-50	2280	125-1000	941280
CG-H06-CV-50	583937	500-2000	941281
CG-H06-FV-50	2281	1500-3000	941282



◆ Not available for sale as individual parts

All seals, except interface, are F3. Use the F3 seal kit to service all units.

▲ Included in F3 Seal Kit 919444

Model Code Breakdown

(F3) C G - H06 - * - V - 50

1 2 3 4 5 6

1 Seals

F3 - Multi-fluid capability (Viton® seals)

Viton is a regsitered trademark of E.I. DuPont

2 Model Series

CG - Relief valve, manifold or subplate mounted

3 Size

H06 - 3/4 inch high flow

4 Pressure Range

B - 125-1000
C - 500-2000
F - 1500-3000

5 Vent Pressure

V - High vent pressure

6 Design

For satisfactory service life of these components, use full flow filtration to provide fluid which meets ISO cleanliness code 18/15 or cleaner. Selections from Eaton OFP,OFR and OFRS filter series are recommended.

Printed in U.S.A.