Vickers®

Relief Valves

Balanced Piston Type Relief & Sequence Valves

CG-06-*-(V)(Y)-50

Model	■ Cover	Spring (Outer)	Spring (Inner)	■ Spring	Pressure Range PSI	■ Included in Cover S/A
CG-06-B-50	581702		2077	2280	125-1000	941280
CG-06-BV-50		184458				
CG-06-BVY-50	590315					941283
CG-06-BY-50			2077			
CG-06-C-50	581702			583937	500-2000	941281
CG-06-CV-50		184458				
CG-06-CVY-50	590315					941284
CG-06-CY-50			2077			
CG-06-F-50	581702			2281	1500-3000	941282
CG-06-FV-50		184458				
CG-06-FVY-50	590315					941285
CG-06-FY-50			2077			



Model	◆ Body
CG-06-*(V)-50	580456
CG-06-*(V)Y-50	590350

All seals, except interface, are F3. Use the F3 seal kit to service all units.

▲ Included in F3 Seal Kit 919444

◆ Not available for sale as individual parts

Model Code Breakdown

(F3) C G - 06 - * - (V) (Y) - 50

1 2 3 4 5 6 7

1 **Seals**

F3 - Multi-fluid capability (Viton® seals)

Viton is a regsitered trademark of E.I. DuPont

2 **Model Series**

CG - Relief valve, manifold or subplate mounted

3 **Size**

06 - 3/4 inch

4 **Pressure Range**

B - 125-1000 PSI
C - 500-2000 PSI
F - 1500-3000 PSI

5 **Vent Pressure**

V - High vent pressure
(Omit for standard vent pressure.)

6 **External Drain Feature**

Y - Sequence valve
(Omit for standard relief.)

7 **Design**

For satisfactory service life of these components, use full flow filtration to provide fluid which meets ISO cleanliness code 18/15 or cleaner. Selections from Eaton OFP,OFR and OFRS filter series are recommended.

Printed in U.S.A.