Pressure Controls

Pressure Reducing Valves

X(C)G-H06-**-30



● For XCG Models only

Model	Cover Spring	Spacer	Maximum P.S.I.
X(C)G-H06-1-30	2280	——	1000
X(C)G-H06-2-30	583937		2000
X(C)G-H06-3-30	401700	386715	2850

□ Included in Spool S/A Kit 941390

▲Service all units with F3 Seal Kit 919615

⊖ Note
Install Lockscrew with stepped O.D. end toward Spacer or Plunger as shown.

Model Code

(F3) - X (C) G - H 0 6 - * - 3 0

1 2 3 4 5 6

1 **Seal Material**

F3 - Seals for mineral oil and fire resistant fluids

2 **Model Series**

XC - Pressure reducing valve, integral check valve

Mount Type

G - Manifold of subplate mounted

3 **High Flow**

70 USGPM

4 **Nominal Valve Size**

3/4 inch

5 **Maximum Adjustable Pressure**

1 - 1000 PSI
2 - 2000 PSI
3 - 2850 PSI

6 **Design**

For satisfactory service life of these components, use full flow filtration to provide fluid which meets ISO cleanliness code 20/18/15 or cleaner. Selections from Eaton OFP,OFR and OFRS filter series are recommended.

Printed in U.S.A.