

Fuse Accessory Selection Guide

Fuse Family	Size	PCB Fuse Clip	PCB Mount Holder	Panel Mount Holder	In-Line Fuse Holder	Fuse Block
ABC AGC	1/4" x 1 1/4"	1A1119 1A1120 1A1907 1A3398 1A4534 1A4533	HBH-I HBV-I	HTB HKP HMR HGA-C	HRK HHB HFA HHK HHN HFB	S-8000
AGA	1/4" x 5/8"	1A1119 1A1120 1A1907 1A3398 1A4534 1A4533	-	-	-	-
AGX	1/4" x 1"	1A1119 1A1120 1A1907 1A3398 1A4534 1A4533	-	HJL	HRK HHB HFA	3828-1
ATC	-	1A5600 1A5780	-	-	HHF-JFCU	-
ATM	-	1A5778 1A5779	-	-	HHM	-
BAF	13/32" x 1 1/2"	1A3400	-	HPG	HEB	BMM603
BBS	13/32" x 1 3/8"	1A3400	-	HPS-L	HEH	BMM603
C519	5 mm x 15 mm	1A3399 1A5601 1A5602 1A5018	-	-	HHT	-
C520	5 mm x 15 mm	1A3399 1A5601 1A5602 1A5018	-	-	HHT	-
FNM	13/32" x 1 1/2"	1A3400	-	HPG	HEB	BMM603
FNO	13/32" x 1 1/2"	1A3400	-	HPG	HEB	BMM603
FNO-R	13/32" x 1 1/2"	1A3400	-	HPG	-	BCM603
FWH	1/4" x 1 1/4"	1A1119 1A1120 1A1907 1A3398 1A4534 1A4533	HBH-I HBV-I	-	-	-
GBA GLD	1/4" x 1 1/4"	1A1119 1A1120 1A1907 1A3398 1A4534 1A4533	HBH-I HBV-I	HLD	HRK HHB HFA HHK HHN HFB	S-8000
GBB	1/4" x 1 1/4"	1A1119 1A1120 1A1907 1A3398 1A4534 1A4533	HBH-I HBV-I	HTB HKP HMR HGA-C	HRK HHB HFA HHK HHN HFB	S-8000
GDA GDB GDC	5 mm x 20 mm	1A3399 1A5601 1A5602 1A5018 HTC-200M	HTC-45M HTC-50M HTC-15M H15 HBH-M HBV-M	HTB HTC	HHT	HTC-15M
GMA	5 mm x 20 mm	1A3399 1A5601 1A5602 1A5018 HTC-200M	HTC-45M HTC-50M HTC-15M H15 HBH-M HBV-M	HTB HTC	HHT	HTC-15M

Fuse Family	Size	PCB Fuse Clip	PCB Mount Holder	Panel Mount Holder	In-Line Fuse Holder	Fuse Block
GMC	5 mm x 20 mm	1A3399 1A5601 1A5602 1A5018 HTC-200M	HTC-45M HTC-50M HTC-15M H15 HBH-M HBV-M	HTB HTC	HHT	HTC-15M
GMD	5 mm x 20 mm	1A3399 1A5601 1A5602 1A5018 HTC-200M	HTC-45M HTC-50M HTC-15M H15 HBH-M HBV-M	HTB HTC	HHT	HTC-15M
KLM	13/32" x 1 1/2"	1A3400	-	HPG	HEB	BMM603
KTK	13/32" x 1 1/2"	1A3400	-	HPG	HEB	BMM603
KTK-R	13/32" x 1 1/2"	1A3400	-	HPG	-	BCM603
LP-CC	13/32" x 1 1/2"	1A3400	-	HPG	-	BCM603
MDA MDL MDQ	1/4" x 1 1/4"	1A1119 1A1120 1A1907 1A3398 1A4534 1A4533	HBH-I HBV-I	HTB HKP HMR HGA-C	HRK HHB HFA HHK HHN HFB	S-8000
MDH	1/4" x 1 1/4"	1A1119 1A1120 1A1907 1A3398 1A4534 1A4533	HBH-I HBV-I	HTB HKP HMR HGA-C	HRK HHB HFA HHK HHN HFB	S-8000
PCB	-	-	PCS	-	-	-
PCD	-	-	PCS	-	-	-
S500 S501 S505 S506	5 mm x 20 mm	1A3399 1A5601 1A5602 1A5018 HTC-200M	HTC-45M HTC-50M HTC-15M H15 HBH-M HBV-M	HTB HTC	HHT	HTC-15M
SC-1 to 15A	13/32" x 1.31"	1A3400	-	HPS-EE	HEG	BG3011PQ
SC-20A	13/32" x 1.41"	1A3400	-	HPS-JJ	HEH	BG3011PQ
SC-25 to 30A	13/32" x 1.62"	1A3400	-	HPS-FF	HEC	BG3011PQ
SC-35 to 60A	13/32" x 2 1/4"	1A3400	-	-	HEJ	G30060-1CR
SR-5 SS-5	-	-	PCS	-	-	-
TDC10/11	1/4" x 1 1/4"	1A1119 1A1120 1A1907 1A3398 1A4534 1A4533	HBH-I HBV-I	HTB HKP HMR HGA-C	HRK HHB HFA HHK HHN HFB	S-8000
TDC180	1/4" x 1"	1A1119 1A1120 1A1907 1A3398 1A4534 1A4533	-	HJL	HRK HHB HFA	3828-1
SFE	1/4" x various lengths (5/8" to 1 7/16")	1A1119 1A1120 1A1907 1A3398 1A4534 1A4533	-	-	HR/HM	-
TCP70	1/4" x 1"	1A1119 1A1120 1A1907 1A3398 1A4534 1A4533	-	HJL	HRK HHB HFA	3828-1

Eaton
Electronics Division
1000 Eaton Boulevard
Cleveland, OH 44122
United States
www.eaton.com/electronics

© 2017 Eaton
All Rights Reserved
Printed in USA
Publication No. 10575 BU-MC16086
May 2017



Eaton is a registered trademark.

All other trademarks are property of their respective owners.