Solenoid Controlled Relief Valve Module

(F3)-DGC5-060A(P)-*(V)-M(P**)-**-*-70



Note
Use as required to obtain proper adjustment range.

Model	■ Included in Cover S/A	Spring	Washer
DGC5-060A-B-*-M-70	926570	2280	Omit
DGC5-060A-C-*-M-70	926571	583937	233110
DGC5-060A-F-*-M-70	926572	2281	Omit

▲Included in Seal Kit 920363
† Available in lot kits of 25
□Coat with oil before assembly.

Refer to I-3862-S for Pilot Valve parts breakdown.

Model Code

(F3) - DGC5 06 0A (P) - * (V) - M (P) - ** - * - 70**

1 2 3 4 5 6 7 8 9 10 11 12

1 Seal Material

F3 - Mineral oil & fire resistant seals

2 Model Series

DGC5 - Solenoid controlled relief valve module

3 Valve Size

06 - 3/4 inch

4 Pilot Valve Spool Type & Function

0A

5 Manual Overdrive in Pilot Valve

(Omit if not required.)

6 Pressure Range

B - 125-1000 psi
C - 500-2000 psi
F - 1500-3000 psi

7 High Vent Option

(Omit if not required.)

8 Flag Symbol Heading for Electrical Features & Options at Pilot Valve

9 Elecrical Features

(Refer to drawing I-3866-S.)

10 Electrical Connector Options

U - DIN 43650
W - 1/2" NPT
WL - 1/2" NPT with solenoid indicator light

11 Coil Voltage I.D. Letter Code

(Refer to drawing I-3866-S.)

12 Design Number

† Available in Lot Kits of 25	
Item	Lot Kit
1485 Nut	944064
36212 Screw	944053
64520 Washer	944068
68905 Washer	944077
199312 Pin	944059
292330 Screw	944072
233110 Washer	944076
326317 Washer	944073
329463 Plug	944041
343740 Plug	944038
422849 Spacer	944075

For satisfactory service life of these components, use full flow filtration to provide fluid which meets ISO cleanliness code **20/18/15** or cleaner. Selections from Eaton OFP,OFR and OFRS filter series are recommended.

Printed in U.S.A.