**Air Tubing-1/8” Nylon**
68526 50’ White



82013 50’ Black

**Sheathing**
80000 50’



**“O” Ring Clamp**
13571



**Tubing Connectors - 1/8” Nylon**

Connector 84001




Connector 84002




Union 84101



Elbow 85002




Nut 83501

Collet 83001

## Air Lines and Connectors

### Tubing Connectors-5/32” Nylon Push to Connect

Connector Assembly
5/32” Tube — 1/16” NPTF
Part Number: 84005



Straight Connector Assembly:
5/32” Tube — 1/8” NPTF
Part Number: 84006



Union Assembly (optional)
5/32” Tube
Part Number: 84103



Elbow Assembly
5/32” Tube — 1/8” NPTF
Part Number: 85003



### Tubing Connectors-5/32” Nylon

Connector 84003




Connector 84004




Elbow 85001




Union 84102




Nut 83502




Collet 83002

### Roadranger Valve Port Markings

**A - Supply - Non - Regulated**
**(From Air Filter End Cap)**

**B - Brake Signal**

**E - Exhaust**
**(Line and Fitting Optional - Exhaust to Remote Area)**

**H/L - Splitter/Deep Reduction Supply**
**(From High/Low Shift Cylinder)**

**P - Pilot**
**(Signal for Range Shift)**

**S - Supply**
**(Air Supply From Filter Regulator)**

**SP - Splitter/Deep Reduction Cylinder Pilot**

## Air Tubing-5/32” Nylon

75120 (Red) 50’ S-Supply

75320 (Black) 50’ P-Pilot

75520 (Green)
50’ H/L-Splitter or Deep Reduction Supply

5547002 (Orange) 50’ A-Supply-Non-Regulated

75720 (Blue) 50’ SP-Splitter Pilot

75820 (Yellow) 50’
B-Brake Signal

75920 (Brown) 50’ E-Exhaust

## Sheathing

80120 50’



## “O” Ring Clamp

13571



## Tubing Harness

52601 50’




52701 50’




52801 50’




52901 50’




74701 50’




74601 50’