



Cutler-Hammer® Series UL Classified Replacement Circuit Breakers by Eaton Corporation are the key to safe installation and streamlined inventory. They virtually eliminate the need to carry any other manufacturer's circuit breakers. Why carry up to seven different brands when the industry's most reputable brand, Eaton, is all you need.

Coming in both 3/4-inch Type CHQ and 1-inch Type CL, one- and two-pole configurations, these breakers are classified as direct replacements by Underwriters Laboratories Inc. In addition to a UL listing, they also come with an outstanding 15-year warranty.

Streamline Breaker Inventory
UL Classified breakers are produced by one manufacturer for use in place of the breakers specified on the panelboard. Like specified breakers, UL Classified breakers have been tested in the panels for which they are approved.

Testing and Safety
We test each Classified breaker extensively in breaker extension panels, Murray, Thomas & Betts, Square D, and Crouse-Hinds from Underwriters Laboratories Inc. and involve short-circuit, temperature, and insertion/withdrawal testing assures that the specified breakers are listed by the manufacturer of the panelboard for use in a particular panel. This doesn't mean that the panelboard manufacturer produced the specified breaker, it merely means that the panelboard manufacturer has tested the breaker in the panel. In fact, through the years the Eaton business has manufactured thousands of breakers for other panelboard manufacturers.

1 Please use the compatibility chart provided with each classified breaker for the list of approved panels.

Specified vs. Classified
Specified breakers are listed by the manufacturer of the panelboard for use in a particular panel. This doesn't mean that the panelboard manufacturer produced the specified breaker, it merely means that the panelboard manufacturer has tested the breaker in the panel. In fact, through the years the Eaton business has manufactured thousands of breakers for other panelboard manufacturers.

The Most Complete Line
Not only do we cover more manufacturers, we also offer breakers in standard one- and two-pole configurations as well as Ground Fault Circuit Interrupters, Remote Control, and Arc Fault Circuit Interrupters. Breakers are available in standard packaging, and many are available in clear shells for counter area displays.

The Eaton Warranty – The Industry's Best
The Eaton business warrants its CL and CHQ Direct Replacement Circuit Breakers to be free from failures due to defects in material or workmanship for 15 years from the date of purchase. Additionally, should a failure occur of a CL or CHQ breaker installed, the Eaton business would repair or replace the loadcenter in which it is installed, the Eaton business

Code Acceptance
Financially, it makes sense for manufacturers to specify their own breakers for use in their panelboards and not list competitors' products, even though they too are suitable for use. This is why a third-party organization (Underwriters Laboratories Inc.) is responsible for listing suitable replacements for the manufacturer's specified circuit breakers. Our classified circuit breakers meet all code acceptance regulations governed by the National Electric Code® and Underwriters Laboratories Inc.

Original Panelboard Warranty
Manufacturers may claim that the use of breakers other than those specified voids their warranty. However, the Magnusson-Moss Warranty Act prevents manufacturers from making warranties contingent upon the use of their replacement parts, as long as the third-party part is proven by UL, the panelboard manufacturer's warranty is still effective when you choose a CL or CHQ breaker.

The Eaton Warranty – The Industry's Best
The Eaton business warrants its CL and CHQ Direct Replacement Circuit Breakers to be free from failures due to defects in material or workmanship for 15 years from the date of purchase. Additionally, should a failure occur of a CL or CHQ breaker installed, the Eaton business would repair or replace the loadcenter in which it is installed, the Eaton business

Understanding Classified Breaker Terminology
Skip the legalese. Here's what you need to know to save time, hassle, and shelf space. Each manufacturer lists the brands of circuit breakers that can be used in their panelboards. Often, manufacturers will not list competitors as specified, even though they are suitable replacements.

Listed Breaker
According to the NEC, the listing of a product is by an independent third-party. Eaton Cutler-Hammer Series Classified Breakers are listed by UL. A breaker that is considered suitable, by Underwriters Laboratories, for use in place of the specified circuit breaker.

UL Classified to Fit Virtually Any Panel... Even Square D® HOMELINE®

Eaton
Cutler-Hammer® Series
Classified Circuit Breakers

- Square D® HOMELINE®
- Square D®
- QO®
- Crouse-Hinds® General Electric® Crouse-Hinds®
- Murray® Thomas & Betts®

UL Classified Replacement Circuit Breakers



Proud Sponsor of
ESFi
Electrical Safety Foundation International

GE is a registered trademark of General Electric Company.
ITE/Siemens is a federally registered trademark of Siemens AG.
Quincy, Mass. Thomas & Betts is a federally registered trademark of Thomas & Betts Corporation.
Square D, HOMELINE, and QO are federally registered trademarks of SNA Holdings Inc.
Murray is a federally registered trademark of Siemens Energy & Automation, Inc.
Crouse-Hinds is a federally registered trademark of Cooper Industries.
UL is a registered trademark of Underwriters Laboratories.
The National Electrical Code is a registered trademark of the National Fire Protection Association.
All other trademarks are property of their respective owners.

EATON
Powering Business Worldwide

Eaton
1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com
© 2014 Eaton
All Rights Reserved
Printed in USA
Publication No. SA00304001E
March 2014

EATON
Powering Business Worldwide

UL Classified Circuit Breaker Replacement Chart



Classified Breaker
Type CL
1-inch



Classified Ground
Fault Breaker
Type CL_GF
1-inch



Classified Branch
Feeder Arc Fault Breaker
Type CL_AF
1-inch



Classified
Combination Arc
Fault Breaker
Type CL_CAF
1-inch



Classified Breaker
Type CHQ
3/4-inch



Classified Ground
Fault Breaker
Type CHQ_GF
3/4-inch



Classified
Surge Arrester
Type CHQ
3/4-inch



Classified
Latching Remote
Control Breaker
Type CLR

TYPE CL 1" CLASSIFIED BREAKER SOLUTIONS											
Amp Rating	Cutler-Hammer Series Type CL Circuit Breakers (Standard Pack)	Cutler-Hammer Series Type CL Circuit Breakers (Clamshell Pack)	Square D ¹ HOMELINE	Crouse-Hinds ¹	General Electric ¹	Siemens ¹	Murray ¹	Thomas & Betts ¹			
									Catalog Number	Carton Pack	Catalog Number
1-Pole 120/240 VAC 10,000 AIC	15	CL115	CL115CS	6	HOM115	MP115	THQ115	Q115	MP115	TB115	
	20	CL120	CL120CS	6	HOM120	MP120	THQ120	Q120	MP120	TB120	
	25	CL125	—	—	HOM125	MP125	THQ125	Q125	MP125	TB125	
	30	CL130	—	—	HOM130	MP130	THQ130	Q130	MP130	TB130	
	35	CL135	—	—	HOM135	MP135	THQ135	Q135	MP135	TB135	
	40	CL140	—	—	HOM140	MP140	THQ140	Q140	MP140	TB140	
	45	CL145	—	—	HOM145	MP145	THQ145	Q145	MP145	TB145	
2-Pole 120/240 VAC 10,000 AIC	15	CL215	—	—	HOM215	MP215	THQ215	Q215	MP215	TB215	
	20	CL220	CL220CS	3	HOM220	MP220	THQ220	Q220	MP220	TB220	
	25	CL225	—	—	HOM225	MP225	THQ225	Q225	MP225	TB225	
	30	CL230	CL230CS	3	HOM230	MP230	THQ230	Q230	MP230	TB230	
	40	CL240	CL240CS	3	HOM240	MP240	THQ240	Q240	MP240	TB240	
	45	CL245	—	—	HOM245	MP245	THQ245	Q245	MP245	TB245	
	50	CL250	CL250CS	3	HOM250	MP250	THQ250	Q250	MP250	TB250	
TYPE CL 1" GFCI BREAKERS											
1-Pole 120 VAC 10,000 AIC GFCI	15	CL115GF	CL115GFCS	6	HOM115GF	MP115GFI	THQL115GFI	QF115	MP115GF	GFB115GF	
	20	CL120GF	CL120GFCS	6	HOM120GF	MP120GFI	THQL120GFI	QF120	MP120GF	GFB120GF	
	30	CL130GF	—	—	—	MP130GFI	THQL130GFI	QF130	MP130GF	GFB130GF	
TYPE CL 1" AFCI BREAKERS											
1-Pole 120 VAC 10,000 AIC	Branch Feeder AFCI	15	CL115AF	CL115AFCS	6	HOM115AFI	—	THQL115AF	Q115AF	MP115AF	—
		20	CL120AF	CL120AFCS	6	HOM120AFI	—	THQL120AF	Q120AF	MP120AF	—
	Combination AFCI	15	CL115CAF	CL115CAFCS	6	HOM115AFIC	—	THQL115AF2	Q115AFC	MP115AFC	—
		20	CL120CAF	CL120CAFCS	6	HOM120AFIC	—	THQL120AF2	Q120AFC	MP120AFC	—
TYPE CL 1" LATCHING REMOTE CONTROL BREAKERS—SMART BREAKERS™											
1-Pole 120 VAC 10,000 AIC	15	CLR115	—	—	Unfortunately, we cannot give a cross-reference because no manufacturer has a functional equivalent of Eaton's Cutler-Hammer Series Smart Breaker™—however, our devices have been UL Classified to be installed in their panels, and you can offer the benefits of Smart Breaker™ to your customers regardless of their installed base.						
	20	CLR120	—	—							
	25	CLR125	—	—							
30	CLR130	—	—								
2-Pole 120/240 VAC 10,000 AIC	15	CLR215	—	—							
	20	CLR220	—	—							
	25	CLR225	—	—							
30	CLR230	—	—								
TYPE CHQ 3/4" CLASSIFIED BREAKER SOLUTIONS FOR SQUARE D QO											
Amp Rating	Cutler-Hammer Series Type CHQ Circuit Breakers (Standard Pack)	Cutler-Hammer Series Type CHQ Circuit Breakers (Clamshell Pack)	Square D QO	Amp Rating	Cutler-Hammer Series Type CHQ Circuit Breakers (Standard Pack)	Cutler-Hammer Series Type CHQ Circuit Breakers (Clamshell Pack)	Square D QO				
1-Pole 120/240 VAC 10,000 AIC	15	CHQ115	CHQ115CS	6	QO115						
	20	CHQ120	CHQ120CS	6	QO120						
	25	CHQ125	CHQ125CS	6	QO125						
	30	CHQ130	CHQ130CS	6	QO130						
	35	CHQ135	—	—	QO135						
	40	CHQ140	—	—	QO140						
	45	CHQ145	—	—	QO145						
2-Pole 120/240 VAC 10,000 AIC	15	CHQ215	CHQ215CS	3	QO215						
	20	CHQ220	CHQ220CS	3	QO220						
	25	CHQ225	—	—	QO225						
	30	CHQ230	CHQ230CS	3	QO230						
	35	CHQ235	—	—	QO235						
	40	CHQ240	CHQ240CS	3	QO240						
	45	CHQ245	—	—	QO245						
TYPE CHQ 3/4" GFCI BREAKERS											
1-Pole 120 VAC 10,000 AIC GFCI	15	CHQ115GF	CHQ115GFCS	6	QO115GFI						
	20	CHQ120GF	CHQ120GFCS	6	QO120GFI						
	25	CHQ125GF	—	—	QO125GFI						
	30	CHQ130GF	CHQ130GFCS	6	QO130GFI						
	2-Pole 120/240 VAC 10,000 AIC GFCI	15	CHQ215GF	—	—	QO215GFI					
		20	CHQ220GF	—	—	QO220GFI					
25		CHQ225GF	—	—	QO225GFI						
30		CHQ230GF	—	—	QO230GFI						
35	CHQ235GF	—	—	QO235GFI							
40	CHQ240GF	—	—	QO240GFI							
45	CHQ245GF	—	—	QO245GFI							
50	CHQ250GF	—	—	QO250GFI							
TYPE CHQ 3/4" SURGE ARRESTOR											
Surge Arrester	N/A	CHQSA	—	—							

Ordering in carton packs reduces the possibility of breakage.

See compatibility chart inside each classified breaker box for list of the approved panel installations.