







EMI318-10
G3 METERED INPUT

FUNCTIONALITY	INPUT	OUTPUT	OPERATING TEMPERATURE
CURRENT, POWER, AND ENERGY METERING FOR INPUT	NEMA L21-20P 10FT 12AWG / 5C POWERCORD	(30) IEC 60320 C13 GRIP (6) IEC 60320 C19 GRIP (3) NEMA 5-20R	32° TO 140° F 0° TO 60° C
MECHANICAL	INPUT RATING	OUTPUT RATING	CERTIFICATIONS
66.50" (1689mm) LENGTH 2.05" (52mm) WIDTH 2.09" (53mm) DEPTH ALUMINUM CHASSIS, BLACK	120/208V~ WYE 3W+N+PE 16A 50/60HZ	120V~, 16A PER 5-20 200-240V~, 15A PER C13; 16A PER C19 16A MAX PER SECTION 16A MAX PER PHASE	
CIRCUIT BREAKERS	FILTER AND SPIKE/SURGE	ACCESSORIES	CONFIGURATION
NONE	NONE	INCLUDED SPK012 - INSTALLATION INCLUDED SPK013 - NETWORK OPTIONAL EMP001 - ENVIRONMENTAL PROBE	EMI3PB15AMG78AC

TITLE	ePDU G3 SPECIFICATION EMI318-10	DRAW	Spock Liu	2013-11-20
DWG NO.	B9001-221310-01P	DESIGN		
MATERIAL		CHECKED	Elon Guo	2013-11-20
COATING		SAFETY		
UNITS	in[mm]	APPROVED	Vicky Shen	2013-11-20
SHEET	1/1			

SCALE
1:5

ELECTRICAL SECTOR