

MEM Circuit Protection & Control

Pipe Earth Clamps




**Quick & easy earth bond connections
Available through leading electrical wholesalers**

Eaton MEM have introduced a NEW easy to use pipe earth clamp to suit a variety of pipe diameters. This completely new type of earth clamp offers significant advantages over traditional metal models, drastically reducing installation times, thanks to it's simple design and also providing a superior earth connection and easier cross-bonding. Manufactured in heat and UV stabilised nylon 6.6 embodying excellent mechanical properties, chemical, heat resistance and self extinguishing characteristics.

Significant advantages include:

- Continuous uniform metal contact
- No screws or loose parts
- ASTA approved electrical tests to BS951:1999
- No sharp edges and no corrosion
- Unique security locking system
- Cross-bonding becomes a simple operation with continuous uniform contact
- Patented double tooth jaw action



Advanced Earthing Technology - Made in the UK



Strip at least 40mm of cable (conductor). Insert cable through both holes in the clamp. Bend over at exit to act as retention during installation using pliers.



Install the clamp around the pipe to be earth bonded and using finger pressure only squeeze the serrated jaws to engage at least one tooth. Check that the cable is properly positioned.



Using gland pliers tighten clamp firmly on the pipe engaging the security locks that ensure it's permanent grip. Check that the clamp is firmly installed and test the connection for compliance to I.E.E. Regulations.

MEM Circuit Protection & Control
Eaton Electric Limited
Reddings Lane
Birmingham
B11 3EZ
Tel: +44(0)121 685 2100
Fax: +44(0)121 706 2012
Email: meminfo@eaton.com
www.memonline.com

Ordering Details

Pipe Diameter	Conductor Size	List No.
15mm	A-C (2.5mm ² - 6mm ²)	EZB15AC
22mm	A-C (2.5mm ² - 6mm ²)	EZB22AC
15mm	D (10mm ²)	EZB15D
22mm	D (10mm ²)	EZB22D