

Introducing the Eaton® Aluminium Flat Face ADB coupling

Developed for cooling systems in electric applications with circulating water and antifreeze fluids. This coupling is providing an enhanced solution for preventing spillage of cooling agent which can cause technical failures, system shutdowns, and difficult clean-ups.

Eaton Aluminium Flat Face ADB coupling offers no-spill, flat-face design and high reliability

Endurance to exposure

Aluminium construction extends life for safer operations and reduced maintenance.



Eaton Flat face Aluminum (ADB) coupling is light weight and strong, providing resistance to environmental exposure, pressure and mechanical stress.

It is designed to extend the life of the coupling, minimizing spill risk in critical electric cooling applications, offering end users reduced maintenance and safer operations.

Safe connection

Aluminium construction enhances operations in demanding applications with heat and vibration compared to plastic couplings.



Optimal to be used in environments with vibration and heat exposure.

It connects with 4-times safety factor at maximum operating pressure of 25 bar.

Options are available for railway applications with an enhanced version for vibration resistance tested according to EN 61373.

High flow rates

Up to 62% higher flow than ISO 16028 requirements to improve efficiency.



Higher pressure rate from 29% to 62% compared to ISO 16028 requirements, reducing pressure drops and increasing cooling system efficiency.



Powering Business Worldwide



- **Pre-guided system** that helps users pre-position the coupling in difficult environments, making connection easy and reducing maintenance time.
- **Full range of optional seals, end connections and sizes**, helping manufacturers benefit from the design in any type of application.
- Eaton Flat face ADB couplings, due to the aluminum material, are available in a **variety of color coding options**, and can be anodized in colors such as red, blue and even in Gold, aiding assembly and field maintenance processes.

ADB Model	Body size (in)	Nominal Flow Diameter (mm)	Max. Operating Pressure (bar)	Rated flow* (lpm)
–				
A2DB	1/4"	5.9	25	15
A3DB	3/8"	9	25	33
A4DB	1/2"	11.5	25	73
A6DB	3/4"	15	25	120
A8DB	1"	18.5	25	207

* Indicated values refer to a 1 bar/14.5 psi pressure drop

Eaton
Hydraulics Group Europe
Route de la Longeraie 7
1110 Morges
Switzerland
Tel: +41 (0) 21 811 4600
Fax: +41 (0) 21 811 4601

Eaton
Hydraulics Group Asia Pacific
Eaton Building
No.7 Lane 280 Linhong Road
Changning District,
Shanghai 200335
China
Tel: (+86 21) 5200 0099
Fax: (+86 21) 2230 7240

Eaton
Hydraulics Group USA
14615 Lone Oak Road
Eden Prairie, MN 55344
USA
Tel: 952-937-9800
Fax: 952-294-7722
www.eaton.com/hydraulics

© 2018 Eaton
All Rights Reserved
Printed in USA
Document No. E-MEQD-TT003-E
May 2018

Eaton is a registered trademark.
All other trademarks are property
of their respective owners.