

The Eaton logo is displayed in white, bold, sans-serif capital letters. The letter 'O' is stylized with a white dot in the center, resembling a target or a specific symbol. The logo is positioned in the upper left quadrant of the image, set against a dark blue background that is part of a larger photograph of an offshore oil rig.

EATON

Synflex® Subsea Hose Solutions





HCR Collapse-Proof Hose



High Pressure Hose



HCR Collapse-Proof Hose

Applications

- Hydraulic Flying Leads
- Workover Umbilical Component
- Hot Lines
- Chemical and Water Injection

Specifications

- **Working Pressure:** Available in 5,000 psi and 7,500 psi working pressure. Contact us for additional ratings.
- **Differential Pressure:** All sizes have a minimum of 5,000 psi differential pressure and up to 9,000 psi. Capable of service at more than 10,000 feet below sea level.
- **Compliance and Testing:** API 17E, ExxonMobile GP 65-05-06, GP 65-05-03

Construction

- **Cover** – Nylon. Standard cover is chemical resistant and UV resistant.
- **Reinforcement** – Aramid (Kevlar®) fiber bonded to the core tube. Engineered to provide high pressure and lower volumetric expansion.
- **Core** – The tube is a smooth, seamless, continuous extrusion of Nylon 11 Besno P40TLO for compatibility with methanol and other commonly used well chemicals.
- **Carcass** – A flexible 316 stainless steel interlocking metal carcass capable of withstanding over 5,000 psi differential pressure. 316 stainless steel provides excellent corrosion resistance.

High Pressure Hose

Applications

- Hydraulic Flying Leads
- Workover Umbilical Component
- BOP Bundle Component
- Hot Lines
- Chemical Injection
- Water Injection

Specifications

- **Working Pressure:** Available in 5,000, 10,000 and 15,000 psi working pressure. Most sizes with a 4:1 safety factor.
- **Compliance and Testing:** API 17E for most sizes
- SAE J343 test procedures

Construction

- **Cover** – Nylon and urethane. Standard cover is highly UV resistant formulated for long term aging and resistance to hydrolysis.
- **Reinforcement** – Aramid (Kevlar) fiber. Engineered to provide high pressure and lower volumetric expansion.
- **Core** – The tube is a smooth, seamless, continuous extrusion of Besno Nylon 11 P40TLO.

Synflex® Subsea Hose from Eaton™

For more than 40 years, Synflex has provided innovative products for subsea applications. Our engineers are experts in understanding material properties and solving technical problems. Synflex bundles are built to meet and exceed the most demanding requirements, including API 17E. We specialize in producing long continuous lengths of subsea hose.





Blow-Out Prevention Bundles (BOP)

Workover Bundles

Over the years, our world-class operations have created tens of millions of feet of high-quality subsea hose.

We have the right hoses and bundles for your subsea needs.



Blow-Out Prevention (BOP) Bundles

Applications

- Pod Hose Bundles
- Hydraulic Control Bundles
- Electro-Hydraulic Bundles
- Optic-Hydraulic Bundles

Specifications

- **Working Pressure:** Available in 3,000 psi and 5,000 psi configurations. Other pressures can be used up to 10,000 psi working pressure. Most sizes with a 4:1 safety factor.
- All qualification data, cleanliness data and FAT testing available.

Construction

- **Cover** – Selection of durable extruded materials including urethane, polyethylene and nylon. Black, yellow or other colors available. Jacket labeling in footage increments.
- **Reinforcement** – Aramid (Kevlar) fiber in most pilot lines for immediate signaling. Polyester reinforcement available for hydraulic supply lines.
- **Core** – The tube is typically a smooth, seamless and continuous extrusion of Nylon 11.

Workover Bundles

Applications

- IWOC
- Configured for Multiple Tasks
- Hydraulic Control, Chemical Injection, Signaling
- Optic Fiber, Electric, Hydraulic

Specifications

- **Working Pressure:** Hose components up to 15,000 psi working pressure. Most sizes with a 4:1 safety factor.
- Most hoses and bundle configurations fully tested to API 17E.

Construction

- **Cover** – Selection of durable extruded materials including urethane, polyethylene and nylon. Black, yellow or other colors available. Jacket labeling in footage increments.
- **Reinforcement** – Jacket can be constructed with embedded Aramid (Kevlar) fiber for additional strength.
- **Bundle Components** – Can be comprised of high pressure hose, electrical cables and fiber optics.

For more information on Synflex Products, please refer to our website at: www.synflexhose.com

Eaton
14615 Lone Oak Road
Eden Prairie, MN 55344
USA
Tel: 952 937-9800
Fax: 952 974-7722
www.hydraulics.eaton.com

Eaton
115 Lena Dr.
Aurora, OH 44202
USA
Tel: 330 274-3171
Toll Free: 800 837-1467
Fax: 330 274-0473

Eaton
Gembloux S.A./N.V.
Chaussee de Tirlemont, 100
B-5030 Gembloux
Belgium
Tel: (32) 81-626-211
Fax: (32) 81-615-789

