




PRESSURE FILTER, change-over

Series HDD 30 4568 PSI

Sheet No.
2510 H



Pos. I: left filter-side in operation
Pos. II: right filter-side in operation

Connection III and IV to be used to bleed filter or to relieve pressure

1) connection for the potential equalisation, only for the application in the explosive area

1. Type index:

1.1. Complete filter: (ordering example)

HDD.30.10VG.HR.E.P.-.UG.3A.-.AE

1	2	3	4	5	6	7	8	9	10	11
---	---	---	---	---	---	---	---	---	----	----

1 series:

HDD = pressure filter, change-over

2 nominal size: 30

3 filter-material and filter-fineness:

25 VG = 20 $\mu\text{m}_{(c)}$, 16 VG = 15 $\mu\text{m}_{(c)}$, 10 VG = 10 $\mu\text{m}_{(c)}$,
6 VG = 7 $\mu\text{m}_{(c)}$, 3 VG = 5 $\mu\text{m}_{(c)}$ Interpor fleece (glass fiber)

4 resistance of pressure difference for filter element:

30 = Δp 435 PSI
HR = Δp 2320 PSI (rupture strength Δp 3625 PSI)

5 filter element design:

E = single-end open

6 sealing material:

P = Nitrile (NBR)

V = Viton (FPM)

7 filter element specification:

- = standard
VA = stainless steel

8 connection:

UG = thread connection

9 connection size:

3A = -10 SAE

10 filter housing specification:

- = standard

11 clogging indicator or clogging sensor :

- = without
AOR = visual, see sheet-no. 1606
AOC = visual, see sheet-no. 1606
AE = visual-electrical, see sheet-no. 1615
VS1 = electrical, see sheet-no. 1617
VS2 = electrical, see sheet-no. 1618

1.2. Filter element: (ordering example)

01E. 30.10VG.HR.E.P.-

1	2	3	4	5	6	7
---	---	---	---	---	---	---

1 series:

01E. = filter element according to company standard

2 nominal size: 30

3 - 7 see type index-complete filter

2. Accessories:

- measure- and bleeder connection, see sheet-no. 1650

weight: 17.6 lbs.

Changes of measures and design are subject to alteration!

EDV 08/12

3. Spare parts:

item	qty.	designation	dimension	article-no.	
1	2	filter element	01E.30 ...		
2	2	O-ring	12,37 x 2,62	304356 (NBR)	304396 (FPM)
3	2	O-ring	40 x 3	304389 (NBR)	304391 (FPM)
4	2	support ring	48 x 2,6 x 1	305391	
5	2	O-ring	10 x 3	307285 (NBR)	311019 (FPM)
6	2	O-ring	32 x 3	304368 (NBR)	- (FPM)
7	4	screw plug	¼ BSPP	305003	
8	1	clogging indicator, visual	AOR or AOC	see sheet-no. 1606	
9	1	clogging indicator, visual-electrical	AE	see sheet-no. 1615	
10	1	clogging sensor, electronical	VS1	see sheet-no. 1617	
11	1	clogging sensor, electronical	VS2	see sheet-no. 1618	
12	1	O-ring	15 x 1,5	315357 (NBR)	315427 (FPM)
13	1	O-ring	22 x 2	304708 (NBR)	304721 (FPM)
14	1	O-ring	14 x 2	304342 (NBR)	304722 (FPM)
15	1	screw plug	20913-4	309817	
16	1	pressure balance valve			

item 15 execution only without clogging indicator or clogging sensor

4. Description:

Duplex pressure filters with change-over valve type HDD are suitable for a working pressure up to 4568 PSI.

The pressure peaks are absorbed by a sufficient margin of safety. Duplex filters can be serviced without interruption of operation. The upper part has a three-way-change-over valve which allows to change-over the flow from the dirty filter-side to the clean filter-side without interrupting the operation. The change-over procedure does not lead to a cross sectional contraction. Prior to the change-over procedure a built-in pressure balance valve equalizes the housing pressure. After change-over the pressure balance valve has to be closed again. The closed filter-side has to be air-bled by vent III respectively by vent IV. Then change filter element. After screw in the filter bowl the pressure balance has to be opened shortly and the just serviced filter-side has to be air-bled. Filter elements are available down to a filter fineness of 4 µm_(c).

Internormen Product Line filter elements are known as elements with a high intrinsic stability and an excellent filtration capability, a high dirt-retaining capacity and a long service life.

Internormen Product Line filter are suitable for all petroleum based fluids, HW-emulsions, most synthetic hydraulic fluids and lubrication oils.

Internormen Product Line filter elements are available with a pressure difference resistance up to Δp 2320 PSI and a rupture strength up to Δp 3625 PSI.


5. Technical data:

temperature range:	+14°F to +176°F (for a short time +212°F)
operating medium:	mineral oil, other media on request
max. operating pressure:	4568 PSI
test pressure:	5945 PSI
connection system:	thread connection
housing material:	EN-GJS-400-18-LT, C-steel
sealing material:	Nitrile (NBR) or Viton (FPM), other materials on request
installation position:	vertical
air bleeding and mini-measuring connection:	BSPP ¼
volume tank:	2x .02 Gal.

Classified under the Pressure Equipment Directive 97/23/EC for mineral oil (fluid group 2), Article 3, Para. 3.

Classified under ATEX Directive 94/9/EC according to specific application (see questionnaire sheet-no. 34279-4).

6. Symbols:



7. Pressure drop flow curves:

Precise flow rates see 'Interactive Product Specifier', respectively Δp-curves; depending on filter fineness and viscosity.

8. Test methods:

Filter elements are tested according to the following ISO standards:

ISO 2941	Verification of collapse/burst resistance
ISO 2942	Verification of fabrication integrity
ISO 2943	Verification of material compatibility with fluids
ISO 3723	Method for end load test
ISO 3724	Verification of flow fatigue characteristics
ISO 3968	Evaluation of pressure drop versus flow characteristics
ISO 16889	Multi-pass method for evaluating filtration performance