



iProx. The world's
most versatile
proximity sensor.



Powering Business Worldwide

The World's Most Versatile Prox

Eaton's iProx™ is synonymous with high performance and versatility. Just talk to the thousands of satisfied customers who have used iProx to solve their toughest inductive sensing challenges. With a broad product offering of more than 100 catalog models in 4-wire DC and 2-wire AC, different barrel sizes, and a variety of connection options, there's sure to be a perfect iProx solution to your application.

The Features You Want, Right Out of the Box

The iProx family, includes a number of unique features designed to simplify installation, maintenance and troubleshooting. These features come standard, right out of the box.

- Auto-configure outputs are a feature unique to DC-powered iProx models. It auto-detects if the sensor has been wired into inputs requiring NPN (sinking) or PNP (sourcing), and configures the sensor to that mode automatically. Now, one iProx sensor can replace two models, meaning you can stock fewer sensors. Auto-Configure outputs make iProx a “plug and play” sensing solution.

- All iProx models come with extended sensing range. Tubular models with sensing ranges of up to 29 millimeters are available—that's more than twice the range of standard inductive sensors of the same size.
- Only the highest quality materials are used in the construction of iProx sensors. Stainless steel barrels, Ryton® corrosion-resistant face caps, a unique vibration-absorbing potting compound, and temperature ratings all the way down to -40°C make this sensor suitable for operation in the toughest environments.
- A convenient, 360-degree LED indicator on the end-bell of the sensor is visible from any angle. This high-intensity LED is dual-color to indicate both power and output status.

Unleash Advanced Programmable Features—If You Need Them

What makes iProx so different from all those “other” inductive sensors? For starters, it contains an embedded microprocessor that allows it to perform unique sensing functions at extended ranges.

A number of advanced sensing features can be enabled using Eaton's ProxView Windows-based programming software. In fact, using the software, you can fully customize iProx exactly to meet your application needs (see below). Sensor characteristics, such as sensing range or sensing “bands,” can be customized to the nearest tenth of a millimeter. Outputs can be changed from Normally Open (N.O.) to Normally Closed (N.C.). Noise immunity and response time can be adjusted if necessary. And even advanced timing delays and speed detection logic can be enabled through

the software—no PLC programming or external timing relays necessary.



The ProxView software package even includes its own competitor database. Want to replace another manufacturer's sensor with iProx? Just type the model number into the ProxView database and your iProx will be “cloned” to the nearest match.

With an iProx sensor, the ProxView programming software, and a programming cable (E59RP1), you can customize iProx to fit your application—perfectly.

ProxView software for Microsoft Windows provides an easy way to customize your iProx sensors.

Once installed, you can “teach” the sensor to work perfectly in its environment.

Within the programming screen, you can customize the characteristics of your iProx sensor.



Fewer products. Less inventory.


Lean. It's today's manufacturing battle cry, and the iProx can help you get there. With this sensor, you have solutions for thousands of those once unsolvable applications. This means less inventory and less time researching and procuring the right inductive sensor for the job. You save time and money, and your equipment runs longer. That's just what today's manufacturing environment demands.

Feature	Included
Extended Sensing Range	•
360-Degree LED Indicator	•
Stainless Steel Barrel	•
Impact-Absorbing Potting Compound	•
Programmable Output Type (PNP, NPN, Auto Configure)	•
Programmable Output Mode (Normally Open, Normally Closed)	•
Programmable Sensing Range and Band Sensing	•
Programmable Response Time and Noise Immunity (Very Low, Low, Medium, High)	•
Programmable Output On / Off Delay	•
Programmable Over / Under Speed Detection	•
Dual Outputs Optionally Available*	•

*Dual output requires a different part number. PNP/NPN must be identified and cannot be programmed.

Product	Catalog Number	Description
 iProx Programmable Sensor	E59-M...	Free programming software for Microsoft® Windows®, available from www.eaton.com/proxview
 ProxView	E59SW1	Step-by-step programming software for Windows and Windows Mobile® devices; www.eaton.com/proxview
 Remote Programmer	E59RP1	Cable required for computer-to-sensor communications

“Teach” the sensor to trip at a custom point within its sensing field, either laterally or axially.



Set up iProx to ignore nuisance metal objects in the foreground or background.



“Band sensing” mode allows iProx to sense only in a small band within its full sensing range.



Enable advanced timing features such as time delays and speed detection, without using external controls.





With iProx programming tools, it's easy to connect iProx to your computer.



A programming wand enables configuration when the sensor is installed.



A 360-degree LED is visible from all angles.




Unique vibration-absorbing potting compound.

Have It Made To Your Exact Specifications

Intrigued by the features and capabilities of iProx, but don't want to fiddle with the programming software? Likely, there's a standard catalog model that will meet your needs. But if you desire an iProx with special capabilities, such as a unique sensing distance, "band"

sensing, health outputs, timing delays, or even a unique connector cable, Eaton can manufacture iProx to your exact specifications. But we won't stop there. If you wish, our Application and Manufacturing Engineers can create a unique model number, just for your company.

Eaton has a long history of working with large material handling, metalworking, and machinery OEMs to deliver custom-tailored inductive sensors, photoelectric sensors, current sensors and mechanical limit switches. Let us put iProx Sensors to work for you.






Accessorize Your iProx

Simplify your next prox installation with high quality Global Plus connectivity solutions from Eaton. Choose from a wide assortment of single- or double-ended micro connector cables in a

variety of jacket materials and lengths. Quickly wire multiple sensors using our Multi-Connector Blocks, or make your installation perfect with our field wireable connector components.



Eaton's Electrical Sector is a global leader in power distribution, power quality, control and automation, and monitoring products. When combined with Eaton's full-scale engineering services, these products provide customer-driven PowerChain Management® solutions to serve the power system needs of the data center, industrial, institutional, public sector, utility, commercial, residential, IT, mission critical, alternative energy and OEM markets worldwide.

PowerChain Management solutions help enterprises achieve sustainable and competitive advantages through proactive management of the power system as a strategic, integrated asset throughout its life cycle, resulting in enhanced safety, greater reliability and energy efficiency. For more information, visit www.eaton.com/electrical.

Eaton Corporation
Electrical Sector
1111 Superior Ave.
Cleveland, OH 44114
United States
877-ETN-CARE (877-386-2273)
Eaton.com

© 2010 Eaton Corporation
All Rights Reserved
Printed in USA
Publication No. BR05301001E
March 2010



**PowerChain
Management®**

PowerChain Management is a registered trademark of Eaton Corporation.

All other trademarks are property of their respective owners.