
REF. DWG NO 588B360H01

NOTES:

- 1. ALL UNITS ARE DESIGNED IN ACCORDANCE WITH APPLICABLE NEMA, UL, ANSI, AND IEEE STANDARDS.
- 2. DRY-TYPE VENTILATED, CLASS AA, NEMA TYPE 2 ENCLOSURE.
- 3. FOR NEMA 3R OUTDOOR APPLICATION, USE WEATHERSHIELD # WS-31.
- 4. TRANSFORMERS ARE FLOOR MOUNTED.
- 5. 220°C CLASS INSULATION SYSTEM.
- 6. PAINT COLOR IS ANSI #61.
 7. ALUMINUM UNITS HAVE ALUMINUM WINDINGS AND TERMINATIONS. COPPER UNITS HAVE COPPER WINDINGS AND TERMINATIONS.



DIMENSIONS	IN	inches	(mm)
DIMENTOTOTO	11.4	11101100	(,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,

FRAME	APPROX NET ALUMINUM	WT. LBS(KG) COPPER	А	В	С	D	E	F
FR910A	230(104)	300(136)	30.00(762)	20.12(511)	14.12(359)	18.38(467)	11.00(279)	2.08(53)
	•		G	Н	J	K	L	М
			3.92(100)	2.08(53)	3.66(93)	2.29(58)	7.57(192)	6.00(152)
		·			N	0	Р	Q
					2.00(51)	4.13(105)	9.00(229)	2.54(65)

Rev3 - SEP/04

THIS DIMENSION DRAWING IS FOR REFERENCE ONLY. IT IS NOT TO BE REGARDED AS INDICATING THE EXACT DETAILS OF CONSTRUCTION.

		· · ·			
THE INFORMATION ON THIS DOCUMENT IS CREATED BY CUTLER—HAMMER. IT IS DISCLOSED IN CONFIDENCE AND IS ONLY TO BE USED FOR THE PURPOSE IN WHICH IT IS SUPPLIED.		DFTR HEG APPD EER	DATE 12/01/01 DATE 12/01/01	Cutler-Hammer Juarez, Mexico TITLE DRY TYPE TRANSFORMER OUTLINE	
		S.O.		TYPE TRANSFORMER	
FEDERAL ID NO	PRODUCT CODE TRANSFORMER	REVISION 03	DWG SIZE ${ m A}$	G.O. DWG FR910A SHEET O1 OF C	