
NOTES:

- 1. ALL UNITS ARE DESIGNED IN ACCORDANCE WITH APPLICABLE NEMA, UL, ANSI, AND IEEE STANDARDS.

 2. DRY—TYPE VENTILATED, CLASS AA, NEMA TYPE 1 ENCLOSURE.

 3. TRANSFORMERS ARE FLOOR MOUNTED.

- 4. 220°C CLASS INSULATION SYSTEM.
- 5. PAINT COLOR IS ANSI #61.6. COPPER UNITS HAVE COPPER WINDINGS AND TERMINATIONS.



	DIMENSIONS IN INCHES (MM)						
FRAME	APPROX NET WT. LBS(KG) COPPER	Α	В	С	D	E	F
FR964	1220(553)	62.61(1590)	28.03(712)	23.06(586)	26.29(668)	18.82(478)	4.53(115)
		G	Н	J	K	L	М
		5.13(130)	3.66(93)	9.38(238)	3.75(95)	12.75(324)	10.63(270)
		N	Р	Q	R	S	Т
		2.12(54)	4.84(123)	17.25(438)	15.13(384)	14.37(365)	13.40(340)
		U	٧	W	Х	Y	Z
		1.25(32)	11.37(289)	5.25(133)	16.45(418)	6.55(166	3.74(95)

Original - AGO/08

THIS DIMENSION DRAWING IS FOR REFERENCE ONLY. IT IS NOT TO BE REGARDED AS INDICATING THE EXACT DETAILS OF CONSTRUCTION.

THE INFORMATION ON THIS DOCUMENT IS CREATED BY CUTLER—HAMMER.		S.CASTRO	DATE 08/09/08	Cutler-Hammer	Juarez, Mexico
IT IS DISCLOSED IN AND IS ONLY TO B	APPD E.ROBLES	DATE 08/09/08	TITLE DRY TYPE TRANSFORMER OUTLINE		
PURPOSE IN WHICH IT IS SUPPLIED.		S.O		TYPE TRANSFORMER	
FEDERAL ID NO	PRODUCT CODE TRANSFORMER	REVISION 01	DWG SIZE ${ m A}$	o. Dwg FR964	SHEET 01 OF 01