

Specifications



Photo is representative



Eaton LPN-RK-40SP

Eaton Bussmann Series Class RK1 fuse, LPN-RK, time-delay, dual-element, current limiting fuse, 40 A, non-indicating fuse, interrupting rating of 300 kA at 250 Vac and 100 kA at 125 Vdc

General specifications

PRODUCT NAME	Eaton Bussmann series LPN-RK fuse
CATALOG NUMBER	LPN-RK-40SP
UPC	051712538381
PRODUCT LENGTH/DEPTH	3 in
PRODUCT HEIGHT	0.81 in
PRODUCT WIDTH	0.81 in
PRODUCT WEIGHT	0.5 lb
COMPLIANCES	CE Marked

Electrical rating

AMPERAGE RATING	40 A
INTERRUPT RATING	300 kAIC at 250 Vac 100 kAIC at 125 Vdc
RESPONSE TIME	10 sec at 500%
VOLTAGE RATING	250 Vac, 125 Vdc

General information

CLASS	Class RK1
CONNECTION	Ferrule end x ferrule end
FUSE INDICATOR	Non-indicating
QUANTITY	10
SPECIAL FEATURES	Indicating, High in-rush current motor protection

Physical details

FUSE TYPE	Time delay Current-limiting
NUMBER OF ELEMENTS	Dual
PACKAGING TYPE	Standard

Resources

CATALOGS	Bussmann Full Line Catalog Low Voltage Branch Circuit Fuse Chapter
COMPLIANCE INFORMATION	RoHS Search Tool
MULTIMEDIA	Bussmann series Fuseology
TECHNICAL SERVICE BULLETINS	Bussmann series Low-Peak 250 V LPN Class RK1 time-delay fuses, 1/10-60 A data sheet no. 1003

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

