

Visualization solutions
for harsh and
hazardous areas

Crouse-Hinds
by **FAT•N**

The safety you rely on

Delivering world-class reliability and safety in high consequence harsh and hazardous environments

Crouse-Hinds
by **EAT•N**



MTL Azonix is a part of Eaton's Crouse-Hinds business and remains a brand that stands for safety in the harshest of environments. Whilst we began with the MTL100 series zener barrier, MTL Azonix alongside Crouse-Hinds, has grown into the premier name for a comprehensive portfolio of solutions for high-consequence harsh and hazardous environments.

As we continue to evolve, so does our brand. Our products are now united with Eaton's leading range of reliable, efficient and safe electrical power management solutions. MTL Azonix has a new look alongside Crouse-Hinds by Eaton, but the products and technology you trust remain unchanged.

**More protection. More technology.
Expect more.**

Only Eaton's Crouse-Hinds Business can deliver...

- Protection and safety of people and assets around the world with unsurpassed reliability and quality in every product we offer
- Industry leading innovation and product efficiency
- Product solutions designed and certified for global specifications
- Best-in-class, global sales, and customer service teams that provide local support
- Over forty years of industry knowledge and expertise



MTL Azonix has been supplying ruggedized computers and data acquisition systems since 1993 to the oil and gas industry. With over 10,000 systems sold ranging from human machine interface (HMI) displays, data acquisition systems, wireless communication and I/O devices for hazardous environments, MTL Azonix has a strong technical understanding for the demands of outdoor and hazardous area environments. This experience guides us as we develop new and innovative products converging computer technology with application know-how to meet a wide range of customer requirements.

MTL Azonix offers the broadest range of hazardous area HMI products giving you the option of choosing the best solution to meet your technical requirements and business needs. At MTL Azonix, we understand that it is not just about the product but the overall cost of ownership experience. Manufactured in a world class manufacturing facility focusing on quality and on-time delivery and supported by a strong service center focused on customer satisfaction, our products give the best return on investment and help your business grow. We strive to lead the industry with our product innovation and cost effective solutions.

Our Product Value Proposition

- Totally sealed computers and displays that eliminate failures from contamination.
- Lower power designs, ensuring longer product life.
- Rugged electronic package that function over a wide range of temperatures, shocks, vibrations and EMI.
- Intrinsically Safe electrical design enabling small, light weight ease of connectivity HMIs, data acquisition and I/O devices.
- Certification to hazardous area standards by approved agencies.
- Full product support throughout the life of the product.
- Patented IS Ethernet and wireless communications.

Applications for MTL AZONIX Systems

- Directional drilling
- Gas compression stations
- Measurement and logging while drilling (MWD/LWD)
- Casing tools
- Mudlogging
- Blow out preventers
- Coil tubing
- Pressure managed drilling
- Well stimulation
- Geo balance drilling
- Production platforms

www.azonix.com

sales@azonix.com



Our designs push computing capability closer to the process


Making it rugged - design challenges

In order to mitigate the primary cause of all system failures, heat, MTL Azonix engineers specify high efficiency power supplies, low power LED backlit LCD's and low power CPU's. These highly reliable designs are then modeled in thermal management software to ensure the heat dissipation meets all environmental criteria. Our engineers work closely with our customers ensuring all critical requirements are achieved per demand of the rig floor environment.

Our design review process ensures that the materials, tolerances and manufacturing practices will produce the highest reliability in our products as intrinsic safety and ruggedizations is our core competency. This is also validated during our prototype build and test phase. In addition, reliability predictions are made in accordance with MIL-HDBK-217. With a design focus for obsolescence management, our products typically have a field life of eight to ten years. The design teams' focus on low MTBF is critical in the design process. Our product development process includes several levels of reviews where peers scrutinize each other's work and cross-functional teams evaluate the development process in all areas including design margin. Finally, in addition to in-house testing, we utilize certified third-party labs to validate that the components and assembled units are reliable.

Design Capabilities

- Integrated computer and display systems
- Intrinsically safe design
- LCD display design and optics technology
- Extreme ambient temperature design
- Embedded system design
- High speed barrier design
- Electronics packaging
- Thermal management
- FEA analysis
- Wireless communications
- Hazardous Area & MIL certification
- Solid Works / Pro E CAD capabilities
- MTBF Analysis - Mean Time Between Failure
- DFMEA Analysis - Design Failure Mode Effect Ana
- Thermal Analysis for superior thermal management



Process Capabilities

Lean Manufacturing
ISO 9001 and AS 9100 certified
Program Management
Configuration Management
Risk Management
RoHS Compliance
Hazardous Area Certification





Operational philosophy

Operational Excellence

Op-Ex principles are our foundation and our core building blocks in everything we do. Lean Manufacturing principles are used in the entire life cycle of the product from design to order entry to production, shipping and after sales service. We utilize kaizen events as our core methodology for continuous improvements. These events are focused improvement projects with cross functional teams dedicated to developing and implementing a solution to a defined problem in 5 days or less.

Visual Metrics

We utilize Key Performance Indicators (KPIs) to monitor the overall business on a daily basis. We also have KPIs for every key function from design to order entry to a production cell to kanban systems. These metrics are posted prominently and reviewed on a daily basis as an integral part of our PDCA (Plan Do Check Act) based real time quality assessment system. Any deviations from the target are analyzed via Pareto charts and problem solving tools are deployed to drive corrective action and improvement.

Dedicated Production Cells

The production cell is at the core of our Lean Manufacturing System. All materials, information and tools are available at the point of use and dedicated supply chain and engineering resources are assigned to cells to ensure maximum cell uptime.

Quality Management System

MTL Azonix is certified to ISO 9001:2008 and has been certified to ISO 9000 since 1996. We are also certified to AS 9100 at all our locations.

Supplier Quality

As part of our QA system, we have an extensive Supply Chain Management System. Our approach covers:

- Selection of new suppliers
- Supplier scorecards and rating
- Non conforming material review
- Monitoring of OTD and quality levels of existing suppliers.
- First Article Inspection for new suppliers / new part / modification to parts
- Joint continuous improvement initiatives with suppliers

Obsolescence Management

Obsolescence Management is a service we provide to insure that we have a predictable supply of the key components and subassemblies used in our products throughout their life cycle. Through frequent road map reviews between our critical component suppliers and our supply chain team, we are notified in advance of scheduled updates as well as end of life situations. With this information we are able to design for the next generation and secure sufficient inventory to provide a seamless transition with no down time or loss of service to our customers.

Quality Assurance

MTL Azonix customers expect a quality product that performs in harsh and rugged environments. To meet these expectations MTL Azonix has implemented a quality assurance program which includes ISO 9000 and AS 9100. Vendor qualification and regular quality performance monitoring is posted through our visual performance system which includes Key Performance Indicators.



Field proven in oil exploration

New Products

Azonix Barracuda 15" Workstation

The next generation of the most popular hazardous area Zone 2 workstation is about to unfold. This updated platform has the latest in computing technology along with additional features our customers have requested for improved and expanded functionality. The new design is a drop-in replacement for the existing generation of Barracudas in form and fit to enable a smooth transition. The functionality will be equal or better depending upon user requirements. This product update also includes tier touch screen options with the introduction of a more robust glass base projected capacitive screen to improve asset up time. Along with that the unit will operate in broader temperature ranges and have a DC power option.



- Intel® i7 processor platform
- Atex Zone 2 and IECEx Class 1 Zone 2, AEx
- 15" Sunlight viewable screen
- Wide operating temperature -40°C - +60°C
- Sealed system with IP66 rating
- Resistive or Glass based projected capacitive touchscreen

Continuously striving
for asset uptime while
balancing performance
with financial sensitivity

Zone 1 - Azonix Products

ProPanel® PRO4500Z1

- 15" sunlight readable work station
- Projected capacitive glass based touch-screen w/ glove operation
- Intel® Core™ i7 2655 processor
- I.S. wireless 802.11 a/b/g/n protocol
- Universal AC power
- Wide temperature range • Bluetooth connectivity
- Light weight • Multiple mounting options



ProPanel® MP2030Z1

- 15" sunlight viewable work station
- Intel® Pentium M 1.7Ghz processor
- RAM: Up to 2GB
- Storage: hard drive or flash drive up to 16GB
- ATEX Zone 1 certified - purged
- NEMA 4 rated

ProPanel® MP2040Z1

- 15" sunlight viewable work station and data acquisition system
- Intel® Pentium M 1.7GHz
- RAM: Up to 2GB
- Storage: hard drive or flash drive up to 16GB
- ATEX Zone 1 certified - purged
- NEMA 4 rated



MTL Azonix Drilling Unit (ADU)

- MTL Azonix drilling unit intrinsically safe terminal
- Rose dial, azimuth and inclination displays
- ATEX Zone 1 rated
- Single connection - power and data
- Configurable displays
- Light weight / rugged & sealed

Field proven in oil exploration

Zone 2 - Azonix Products

ProPanel® MP2030Z2

- 15" sunlight viewable work station
- Intel® Pentium M 1.7GHz processor
- RAM: up to 2GB
- Storage: hard drive or flash drive up to 16GB
- Fiber network
- ATEX Zone 2
- NEMA 4 rated



ProPanel® MP2100

- 15" sunlight viewable work station
- T7400® Core™ 2 Duo processor (2.16 GHz)
- RAM: up to 2Gb
- Storage: 80GB min hard drive
- ATEX Zone 2 and C1D2
- NEMA 4 / IP65 rated

Barracuda 19" BOP or Barracuda 19" WS

- 19" sunlight viewable work station
- Intel® Core™ 2 Duo 2.2GHz processor
- RAM: up to 4GB
- Storage: 32GB compact flash
- ATEX Zone 2 / CSA Class 1 Zone 2
- IP66 rated



Barracuda 15" WS

- 15" sunlight viewable work station
- Intel® Core 2™ Duo 2.2GHz processor
- RAM: 1GB to 4GB
- Storage: compact flash up to 32GB or 80GB HDD
- ATEX Zone 2 / CSA Class 1 Zone 2
- IP56 rated

Safe Area - Azonix Products

Barracuda Lite 19" WS

- 19" sunlight viewable work station
- Intel® Core™ 2 Duo 2.2GHz processor
- RAM: up to 2GB
- Glass based touch screen
- Storage: 32GB compact flash
- Front panel IP56 back enclosure IP52




Barracuda Lite 15" WS

- 15" sunlight viewable work station
- Intel® Core™ 2 Duo 2.2GHz processor
- RAM: up to 2GB
- Glass based touch screen
- Storage: 32GB compact flash
- Front panel IP56 / rear panel IP52

ProPanel® MP2030SA

- 10" sunlight viewable work station
- Intel® Pentium M 1.7GHz
- RAM: up to 2GB
- Storage: hard drive or flash drive up to 16GB
- Push and hold touchscreen enabler
- NEMA 4 rated



GECMA Remote Terminals and PCs for Hazardous Areas

Challenger remote terminals and Explorer PC's are an optimum solution for even the most demanding of tasks of on-site operation and visualization typically found in Pharmaceutical, Chemical, Petrochemical, Oil & Gas and Off-shore manufacturing. Specifically designed to work within hazardous and industrial environments the Challenger and Explorer HMI's offer great flexibility due to their modular configuration to meet all your plant requirements.

Explorer 15i / 18i PC Terminal

- Modular system
- Certified for Ex Zone 1/2 and Zone 21/22
- Designed for harsh environments
- High reliability
- Non-wearing SSD
- Intel® Atom™ 1.6 GHz processor
- 2GB RAM



GECMA Remote Terminal

- Slimline housing for optimisation of space and application
- Fibre optic or copper data transmission
- Full HD capability, optical bonding, LED backlight
- Specified for use in hazardous areas
- Highest dependability
- Future proof 'transparent' USB interface
- Savings of software licence costs
- Wide range of International Ex approvals

This future proof solution has been designed packed full of features and state of the art technology, all found within a slimline, stainless steel package (mounting options available) and with no hidden extra costs.

A new generation, built on experience



Eaton's Crouse-Hinds

The safety you rely on.

See the complete offering of Hazardous Area Communication Products at www.azonix.com

**U.S. (Global Headquarters):
Eaton's Crouse-Hinds Business**

1201 Wolf Street
Syracuse, NY 13208

(866) 764-5454
FAX: (315) 477-5179
FAX Orders Only:
(866) 653-0640

CrouseCustomerCTR@Eaton.com

For more information:

If further assistance is required, please contact an authorised MTL Distributor, Sales Office, or Customer Service Department

AUSTRALIA

MTL Instruments Pty Ltd,
205-209 Woodpark Road, Smithfield,
New South Wales 2164, Australia

Tel: + 61 1300 308 374 Fax: + 61 1300 308 463
E-mail: mtlsalesanz@eaton.com

BeNeLux

MTL Instruments BV
Terheijdenweg 465, 4825 BK Breda
The Netherlands

Tel: +31 (0) 76 7505360 Fax: +31 (0) 76 7505370
E-mail: mtl.benelux@eaton.com

CHINA

Cooper Electric (Shanghai) Co. Ltd.
Room 2001, China Life Tower, 16 Chao Yang Men Wai Street,
Chao Yang District, Beijing, China 100020

Tel: + 86 10 5980 0231 Fax: + 86 10 8562 5725
E-mail: mtl-cn@eaton.com

FRANCE

MTL Instruments sarl,
7 rue des Rosières, 69410 Champagne au Mont d'Or
France

Tel: + 33 (0)4 37 46 16 70 Fax: +33 (0)4 37 46 17 20
E-mail: mtlfrance@eaton.com

GERMANY

MTL Instruments GmbH,
Heinrich-Hertz-Str. 12, 50170 Kerpen, Germany

Tel: + 49 (0)22 73 98 12 - 0 Fax: + 49 (0)22 73 98 12 - 2 00
E-mail: mtlgmbh@eaton.com

INDIA

MTL India,
No.36, Nehru Street, Off Old Mahabalipuram Road
Sholinganallur, Chennai - 600 119, India

Tel: + 91 (0) 44 24501660 /24501857 Fax: + 91 (0) 44 24501463
E-mail: mtlindiasales@eaton.com

ITALY

MTL Italia srl,
Via A. Meucci, 10, I-20094 Corsico (MI), Italy

Tel: + 39 (0)2 61802011 Fax: + 39 (0)2 61294560
E-mail: chminfo@eaton.com

JAPAN

Cooper Crouse-Hinds Japan KK,
MT Building 3F, 2-7-5 Shiba Daimon, Minato-ku,
Tokyo, Japan 105-0012

Tel: + 81 (0)3 6430 3128 Fax: + 81 (0)3 6430 3129
E-mail: mtl-jp@eaton.com

NORWAY

Norex AS
Fekjan 7c, Postboks 147,
N-1378 Nesbru, Norway

Tel: +47 66 77 43 80 Fax: +47 66 84 55 33
E-mail: info@norex.no

SINGAPORE

Cooper Crouse-Hinds Pte Ltd
No 2 Serangoon North Avenue 5, #06-01 Fu Yu Building
Singapore 554911

Tel: + 65 6 645 9888 Fax: + 65 6 487 7997
E-mail: sales.mtlsing@eaton.com

SOUTH KOREA

Cooper Crouse-Hinds Korea
12F, Vision Tower, 707-2 Yeoksam-Dong Gangnam-Gu,
Seoul 135-080, South Korea.

Tel: +82 2 538 3481 Fax: +82 2 538 3505
E-mail: mtl-korea@eaton.com

UNITED ARAB EMIRATES

Cooper Industries/Eaton Corporation
Office 205/206, 2nd Floor SJ Towers, off. Old Airport Road,
Abu Dhabi, United Arab Emirates

Tel: +971 2 44 66 840 Fax: +971 2 44 66 841
E-mail: mtlgulf@eaton.com

UNITED KINGDOM

Measurement Technology Limited,
Great Marlings, Butterfield, Luton
Beds LU2 8DL

Tel: + 44 (0)1582 723633 Fax: + 44 (0)1582 422283
E-mail: mtlenquiry@eaton.com

AMERICAS

Cooper Crouse-Hinds MTL Inc.
3413 N. Sam Houston Parkway W.
Suite 210, Houston TX 77086, USA

Tel: + 1 281-571-8065 Fax: + 1 281-571-8069
E-mail: mtl-us-info@eaton.com

Azonix Corporation

Eaton Experience Center
3413 North Sam Houston Parkway West
Suite 210
Houston TX 77086, USA

Azonix Business Center Toll Free: +1-866-929-6649
Azonix Business Center: +1-832-251-8800
Azonix Business Center Fax: +1-281-921-8207

www.azonix.com

Crouse-Hinds
by **EATON**

© 2014 Eaton Corporation
All Rights Reserved
Printed in USA
ZL-B-AZONIX-A4UK-1014
October 2014

Measurement Technology Limited

Great Marlings, Butterfield, Luton
Beds LU2 8DL, UK.
Tel: + 44 (0)1582 723633
Fax: + 44 (0)1582 422283
E-mail: mtlenquiry@eaton.com
www.mtl-inst.com

Eaton is a registered trademark.

All other trademarks are property of their respective owners.