HDR48-ES Energy Saver Rectifier



The Eaton[®] HDR48-ES Energy Saver Rectifier is

designed for communications network operators who are striving to cut energy costs across the network, and/or to meet aggressive carbon footprint reduction targets. Its power density is 50% better than existing Eaton rectifiers and its high efficiency means it can produce at least 50% less waste energy than many other modern rectifiers, and with potentially greater savings over much older infrastructure.

The 3 kW Energy Saver Rectifier is the ideal module size for powering access applications within a telecom network such as 5G base stations, VDSL equipment, and fibre nodes.

This rectifier features intelligent digital signal processing for enhanced control, producing peak efficiency approaching 97% for typical operating loads, while also maintaining a very high minimum operating efficiency of 96% over a very wide range of loads (from 30% to 100% of the 3 kW capacity).

The high-power density, short depth and flexible mounting options makes the Energy Saver Rectifier well suited to limited space applications such as ETSI and roadside cabinets.

The Energy Saver Rectifier is fully compatible with existing Eaton 3G systems and it is one of the easiest rectifiers to use, with a simple plugand-go insertion. It operates under a wide range of AC power conditions and in temperatures at up to 70°C (158°F).

Features

- 3000 W output power
- Energy saving efficiency near 97%
- Industry leading power density
- · Fast on-line expansion of rectifiers (hot swap)
- Simple 'plug and go' insert
- Unity power factor
- Digital signal processing for enhanced control
- Wide AC supply conditions
- Wide output voltage range
- Constant power output
- Compliance with international standards



Technical Specifications

Input

-	
AC Supply	120 V/208-240 V, 50/60 Hz (nominal) 185-275 V full output power up to 50°C [122°F] 85-185 V reduced output power @ 25°C
Power Factor	>0.99 (50 – 100% output current)
THD	<5% (50 – 100% output current)
Efficiency	Peak 96.9% >96% (30 – 100% output power)

Output	
DC Output Voltage Range	43 – 57.5 V
DC Output (maximum)	3000 W @ 48 V

Environmental

Operating Temperature	-40°C – +70°C [-40°F – +158°F]
Range	Output power derates above 50°C [122°F]
Cooling	Temperature controlled, variable speed, high reliability fan <50 dBA ambient temperature 25°C

Mechanical

	3U: 133 mm [5.25"], 42 mm [1.65"], 266 mm [10.45"] overall
Weight	2.2 kg [4.8 lb]

Certifications

North America	UL, FCC Verification
Europe	CE

In the interests of continual product improvement all specifications are subject to change without notice. Performance ratings are valid with all other variables at Nominal.

Email: dc.info@eaton.com www.eaton.com/dcpowersolutions



Eaton EMEA Headquarters Route de la Longeraie 7 1110 Morges, Switzerland Eaton.com

© 2023 Eaton All Rights Reserved Publication No. PS154023EN January 2023 Eaton, CellSure, SiteSure, DCTools and PowerManager are trade names, trademarks, and/or service marks of Eaton Corporation or its subsidiaries and affiliates. All other trademarks are property of their respective owners.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

f У in 🖻