



REV	ECO No.	REVISION	DR	CK	AP	AP	DATE
001	074036	ENGINEERING RELEASE	RS				04 DEC 14



## EMI201-10 G3 METERED INPUT

FUNCTIONALITY	INPUT	OUTPUT	ENVIRONMENTAL
CURRENT, POWER AND ENERGY METERING FOR INPUT AND BRANCH	NEMA L14-30 PLUG 10 FT 10AWG / 4C POWERCORD	(24) NEMA 5-20R	32° TO 140° F 0° TO 60° C
MECHANICAL	INPUT RATING	OUTPUT RATING	CERTIFICATIONS
63.15" (1604mm) LENGTH 2.05" (52mm) WIDTH 2.09" (53mm) DEPTH ALUMINIUM CHASSIS, BLACK	120/240V ~ 2W+N+PE 24A 50/60HZ	100-127V ~ 16A MAX PER OUTLET 16A MAX PER SECTION 24A MAX PER PHASE	
CIRCUIT BREAKERS	FILTER & SPIKE/SURGE	ACCESSORIES	CONFIGURATION
(4) 20A 1 POLE LISTED	NONE	INCLUDED SPK012 - INSTALLATION INCLUDED SPK013 - NETWORK OPTIONAL EMP001 - ENVIRONMENTAL PROBE	EMI3NT15EMJ77A1 SERIAL NUMBER B682 _____



METRIC	THIRD ANGLE PROJECTION	EATON CORPORATION, ELECTRICAL		SIZE: D
DESCRIPTION: EPDU G3 SPECIFICATION FOR EMI201-10	MODIFIED BY: R. Sleght	DATE: 16-Dec-2014	UNLESS OTHERWISE SPECIFIED TOLERANCES ON DIMENSIONS ARE: ANGLES: ±1/2° Holes: ±0.13 DIMENSIONS ARE IN MILLIMETERS (INCHES) AND AFTER PLATING	SCALE: 0.400 DO NOT SCALE DRAWING OR CHANGE MANUALLY
ECO: ECO-074036	STATE: Release	PART NAME: EMI3NT15EMJ77A1	REVISION: 001	SHEET: 1 of 1
EATON CORPORATION - CONFIDENTIAL AND PROPRIETARY NOTICE TO PERSONS RECEIVING THIS DOCUMENT AND/OR TECHNICAL INFORMATION THIS DOCUMENT, INCLUDING THE DRAWING AND INFORMATION CONTAINED THEREON, IS CONFIDENTIAL AND IS THE EXCLUSIVE PROPERTY OF EATON CORPORATION, AND IS HEREBY ON LOAN AND SUBJECT TO RECALL BY EATON AT ANY TIME. BY TAKING POSSESSION OF THIS DOCUMENT, THE RECIPIENT ACKNOWLEDGES AND AGREES THAT THIS DOCUMENT CANNOT BE USED IN ANY MANNER ADVERSE TO THE INTERESTS OF EATON, AND THAT NO PORTION OF THIS DOCUMENT MAY BE COPIED OR OTHERWISE REPRODUCED WITHOUT THE PRIOR WRITTEN CONSENT OF EATON. IN THE CASE OF CONFLICTING CONTRACTUAL PROVISIONS, THIS NOTICE SHALL GOVERN THE STATUS OF THIS DOCUMENT. © 2008 Eaton Corporation - All Rights Reserved.				