



LTG	ECN No.	REVISION	DR	CK	AP	AD	DATE
A		ENGINEERING RELEASE	MD				10/24/03
B	011375	UPDATE NOTES & BORDER	JF				16 MAR 10
002	065916	ADD ROHS NOTES	HN				28 MAY 14



1. RACK MOUNTED CHASSIS, BLACK MEDIUM TEXTURE  
19.00" WIDE STANDARD RACK MOUNTING  
1.72" HIGH  
7.00" DEEP  
CHASSIS SUPPORT BRACKETS ARE REQUIRED
2. INPUT: 120 VAC 24A SINGLE PHASE, 50/60 HZ  
POWER CABLE: 15 FOOT 10/3 SOOW CABLE WITH NEMA L5-30 PLUG
3. OUTPUT: 120 VAC 16A AT TWELVE NEMA 5-20 OUTLETS;  
J1 - J2 AND J9 - J12, 16 AMPS MAX  
J3 - J8, 16 AMPS MAX  
24A MAX TOTAL
4. CIRCUIT BREAKER: 1 LISTED, MAGNETIC 2-POLE 20 AMP  
HIGH-INRUSH TIME DELAY
5. INDICATOR LIGHT: 1 BLUE, ON WHEN BREAKER IS ON
6. FILTER:  
COMMON MODE, LINE TO GROUND, NEUTRAL TO GROUND  
DIFFERENTIAL MODE, LINE TO NEUTRAL
7. SPIKE/SURGE SUPPRESSION  
LINE TO NEUTRAL
8. CURRENT MONITOR: NONE
9. U.L./CUL LISTED PRODUCT
10. RoHS COMPLIANT PER DIRECTIVE 2011/65/EU WITH APPLICABLE EXEMPTIONS
11. ALL MATERIALS AND SUB-MATERIALS COMPLY WITH EATON SPECIFICATION 164080496.  
DOCUMENTATION CERTIFYING COMPLIANCE TO EATON SPECIFICATION 164080496 IS  
AVAILABLE UPON REQUEST.

EATON APPROVAL \_\_\_\_\_ DATE \_\_\_\_\_

<b>EATON</b>		3850 Antonio Road, Irvine, California 92618 Phone (949) 412-3800 www.eaton.com	
ENGINEERING NUMBER T982C2-F-SL-015		TITLE ENGINEERING DRAWING FOR T982C2-F-SL-015 ASSY 2988	
REVISIONS	DATE	BY	CHKD
1.1	10/24/03	JF	MD
EATON SPECIFICATION 164080496		EATON SPECIFICATION 164080496	
CASE CODE 31781		D 1 OF 1	

THE INFORMATION AND DESIGN DISCLOSED HEREIN WAS ORIGINATED BY AND IS THE PROPERTY OF EATON CORPORATION. EATON CORPORATION RESERVES ALL PATENT, PROPRIETARY, DESIGN, MANUFACTURING, REPRODUCTION, USE AND SALE RIGHTS THEREIN, AND TO ANY ARTICLE DISCLOSED THEREIN, EXCEPT TO THE EXTENT RIGHTS ARE EXPRESSLY GRANTED TO OTHERS. THE FOREGOING DOES NOT APPLY TO VENDOR PROPRIETARY PARTS. COPYRIGHT 2010 EATON CORP.