



TMC armored cable glands

NEMA 4
IP56
Wet locations

1G

1G

Cable types:

- Metal-clad cable: MC 
- TECK corrugated or interlocked steel or aluminum cable 

Features:

- Stainless steel copper-plated spring provides grounding continuity of cable armor (MC cable only)
- Watertight seal on outer sheath of cable
- Standard neoprene seal suitable for use in operating temperatures -25°C to +60°C
- Cold Shrink™ kit is available for extra protection in aggressive environments (see Section 2G for more information)
- Available with NPT threads

Standard material:

- Body – aluminum

Certifications and compliances:




- UL Listed – UL File No. E36379
- CSA Listed – LR291
- NEMA 4, IP56
- Wet locations
- May be permitted for use in Class I, Division 2 locations, provided there are no arcing and sparking risks in accordance with NEC501.10B

Operating temperature:

- -25°C to +60°C

Options:

Description	Suffix
• Brass construction.....	BR
• Nickel-plated finish	NP



NPT thread size	Cat. #	Armor range (H)		Outer sheath (E)		Across flats	Across corners (G)	Length (L)	Thread length (B)
		Min.	Max.	Min.	Max.				
2 1/2"	TMC7247	1.93	2.47	1.99	2.72	3.75	4.00	4.75	1.44
3"	TMC8302	2.45	3.02	2.52	3.28	4.50	4.88	4.88	1.44
3 1/2"	TMC9352	2.95	3.52	3.02	3.78	5.00	5.38	5.38	1.63
4"	TMC10402	3.50	4.02	3.58	4.28	5.50	5.88	5.50	1.63

All dimensions in inches.