

CERTIFICATE OF COMPLIANCE

Certificate Number 20170202 – E7819
Report Reference E7819 – 19730123
Issue Date 2017-FEBRUARY-02

Issued to: EATON
1000 CHERRINGTON PKWY
MOON TOWNSHIP, PA 15108-4312 USA

**This is to certify that
representative samples of**

Circuit Breakers, Molded Case and Circuit-breaker
Enclosures

Molded case circuit breakers, Class CTL, Quicklag Types
HQP, BQL, QC, QCHW, QPH/QPHW, and QBH/QBHW;
Types BA; Types BR, BRH, , BRO, QPD (duplex), QPQ
(quadplex), BRD (duplex/quadplex), DNPL
(duplex/quadplex), QCF/QCR, QCFH/QCRH and
DNBA(bolt on).

Have been investigated by UL in accordance with the
Standard(s) indicated on this Certificate.

Standard(s) for Safety: ANSI/UL 489, "Molded-Case Circuit Breakers, Molded-
Case Switches and Circuit-Breaker Enclosures."

Additional Information: See the UL Online Certifications Directory at
www.ul.com/database for additional information

Only those products bearing the UL Certification Mark should be considered as being covered by UL's
Certification and Follow-Up Service.

Look for the UL Certification Mark on the product.



Bruce Mahrenholz, Director North American Certification Program
UL LLC

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please
contact a local UL Customer Service Representative at <http://ul.com/aboutul/locations/>



CERTIFICATE OF COMPLIANCE

Certificate Number 20170202 – E7819
Report Reference E7819 – 19730123
Issue Date 2017-FEBRUARY-02

This is to certify that representative samples of the product as specified on this certificate were tested according to the current UL requirements.

Ratings:

These are 1-pole breakers rated 10-100 A and 2-pole circuit breakers rated 10-150 A, 120/240 V ac and switching neutral breakers, 120/240 V ac,

10-60 A. Type QCF/QCR 1 and 2 pole circuit breakers rated 10-60 A, 120/240 V. Type QCF/QCR 2 and 3 pole circuit breakers rated 15-30 A, 240 V.

Type QCFH/QCRH, 1 and 2 pole circuit breakers rated 15-30 A, 120/240 V.

Type	Poles	Interrupting Capacity, A, V ac	Ratings, A
HQP/BR	1	10,000 at 120/240	10-100
HQP/BR	2	10,000 at 120/240	10-150
QC	1	10,000 at 120/240	10-100
QC	2	10,000 at 120/240	10-150
BA/BQL	1	10,000 at 120/240	10-100
BA/BQL	2	10,000 at 120/240	10-150
QPD/BRD/DNPL	2	10,000 at 120/240	10-50
QPQ/BRD/DNPL	4	10,000 at 120/240	10-50
QCF/QCR	1 & 2	10,000 at 120/240	10-60
BRH/QPH/QPHW	1 & 2	22,000 at 120/240	15-125
QCHW	1 & 2	22,000 at 120/240	15-125
QBHW	1 & 2	22,000 at 120/240	15-125
BRO (SN)	1 & 2	10,000 at 120/240	15-60
BRO (WH)	1 & 2	10,000 at 120/240	15-30
HQP/BA/QC (SN)	1 & 2	10,000 at 120/240	10-30
QCFH/QCRH	1 & 2	22,000 at 120/240	15-30
QCF/QCR	2 & 3	10,000 at 240	15-30



Bruce Mahrenholz, Director North American Certification Program

UL LLC

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please contact a local UL Customer Service Representative at <http://ul.com/aboutul/locations/>.

