





4

3

2

1



BC350RNC SPECIFICATIONS

1	FUNCTIONALITY	POWER PROTECTION
2	MECHANICAL	255 X 58 X 180 MM (10.0 X 2.3 X 7.1) INCH
3	UNIT WEIGHT	4.6 lbs
4	INPUT	RATED CURRENT : 3A NOMINAL VOLTAGE : 120V AC I/P CONNECTION TYPE: NEMA 5-15P CIRCUIT BREAKER: 5A INPUT CORD LENGTH: 5ft+
5	OUTPUT	OUTPUT: 350 VA (210 WATTS) NOMINAL OUTPUT: 120V POWER FACTOR: 0.6 FREQUENCY: 50 / 60 Hz RECEPTACLE: 3 X NEMA 5-15R
6	BATTERY	TYPE: SEALED, MAINTENANCE FREE, LEAD ACID DC SYSTEM VOLTAGE: 12VDC BATTERY REPLACEMENT: REPLACABLE INTERNAL BATTERY
7	ENVIRONMENTAL	OPERATING TEMPERATURE RANGE: 32° to 122°F (0° to 50°C) STORAGE TEMPERATURE RANGE: 5° to 122°F (-15° to 50°C)
8	CERTIFICATIONS & COMPLIANCES	CSA C22.2 NO. 107.3 (CAN); UL1778 (US) ; NOM (Mexico) Energy Star; ROHS; FCC Class B, DOE, CEC

METRIC	THIRD ANGLE PROJECTION	NAME (PART NUMBER): 913331	REVISION: A	EAT•N
DESCRIPTION: SUBMITTAL DWG, BC350RNC				
ORIGINATED BY: AMIT J	10-MAY-24	SEE NOTES FOR TOLERANCES DIM ARE IN MM (INCHES) AFTER PLATING INTERPRET DIM AND TOL PER ASME Y14.5-2018	STATE: RELEASED	SCALE: 0.500
MODIFIED BY: -	-	-	ECO: -	SHEET: 1 OF 1
EATON CORPORATION - CONFIDENTIAL AND PROPRIETARY - NOTICE TO PERSONS RECEIVING THIS DOCUMENT AND/OR TECHNICAL INFORMATION: THIS DOCUMENT, INCLUDING THE DRAWING AND INFORMATION CONTAINED THEREIN, IS THE EXCLUSIVE PROPERTY OF EATON CORPORATION, AND IS SUBJECT TO LOSS AND SUBJECT TO RECALL BY EATON AT ANY TIME. BY TAKING POSSESSION OF THIS DOCUMENT, THE RECIPIENT ACKNOWLEDGES AND AGREES THAT THIS DOCUMENT CANNOT BE USED IN ANY MANNER, EITHER TO THE INTERESTS OF EATON OR THAT OF ANY OTHER PARTY, WITHOUT THE WRITTEN CONSENT OF EATON. TO THE EXTENT OF ANY CONFLICTING CONTRACTUAL PROVISIONS, THIS NOTICE SHALL GOVERN THE STATUS OF THIS DOCUMENT. © 2024 Eaton Corporation - All Rights Reserved.				

4

3

2

1