




LTR	ECO No.	REVISION	DR	CK	AP	AP	DATE
A	NONE	ENGINEERING RELEASE	MDR				01/12/94
B	2487	CHANGE 6-GANGS TO 4-GANGS			FVC		02/08/94
C	3375	UPDATE TO SHOW NEW CHASSIS			FVC		02/22/95
D	NONE	UPDATE TO NEW SILKSCREEN	GH				12/10/99
E		OUTLET VIEW CORRECTED	J.O.				13 JAN 00
F	PER MBP	CHG S/S TO SHOW RATINGS	WW				27 JUN 00
G	5789	FRONT SCREENING UPDTE	J.O.		DK		02 OCT 00
H	6443	ADDED CB KICK GUARD	C.L.		DK		30 JUL 01
J	7903	CHG. NOTES 2 & 3, FRT. SS	DK				05/12/04
K	8281	UPDATE DESIGN FOR RoHS	DK				03/08/06
002	062604	ADD ROHS NOTES	HN				20 MAR 14
003	067725	ADD CE NOTE	HN				14 JUL 14
04	181593	DELETE TUV STICKER	J.O.				11 MAR 20



NOTES:

1. RACK MOUNTED STEEL CHASSIS BLACK MEDIUM TEXTURE
19.00" WIDE STANDARD RACK MOUNT
1.72" HIGH
7.00" DEEP
CHASSIS SUPPORT BRACKETS OR SLIDES ARE REQUIRED
2. INPUT: 100-240 VAC 16A 50/60HZ SINGLE PHASE
POWER INLET: IEC C-20 CONNECTOR
3. OUTPUT: 100-240V AT 16 IEC C-13 RECEPTACLES,
10A MAX PER QUAD OUTLET;
16A MAX TOTAL CURRENT
OUTPUT VOLTAGE = INPUT VOLTAGE
4. CIRCUIT BREAKER: 2-POLE 20A UL RECOGNIZED, INERTIAL DELAY
5. INDICATOR LIGHT: ONE GREEN, ON WHEN BREAKER IS ON
6. FILTER: EMI/ RFI 20 AMP RATING
COMMON MODE, LINE TO GROUND, NEUTRAL TO GROUND
DIFFERENTIAL MODE, LINE TO NEUTRAL
7. SPIKE/SURGE PROTECTION: LINE TO NEUTRAL
8. UL/cUL LISTED PRODUCT
9. ALL MATERIALS AND SUB-MATERIALS COMPLY WITH EATON ENVIRONMENTAL
SPECIFICATION 164080496. DOCUMENTATION CERTIFYING COMPLIANCE TO EATON
SPECIFICATION 164080496 IS AVAILABLE UPON REQUEST.
10. CE COMPLIANT

EATON		9650 Jeronimo Road, Irvine, California 92618 Phone (949) 452-9500 www.epdu.com	
THE INFORMATION AND DESIGN DISCLOSED HEREIN WAS ORIGINATED BY AND IS THE PROPERTY OF EATON CORPORATION. EATON CORPORATION RESERVES ALL PATENT, PROPRIETARY, DESIGN, MANUFACTURING, REPRODUCTION, USE AND SALE RIGHTS THERETO, AND TO ANY ARTICLE DISCLOSED THEREIN, EXCEPT TO THE EXTENT RIGHTS ARE EXPRESSLY GRANTED TO OTHERS. THE FOREGOING DOES NOT APPLY TO VENDOR PROPRIETARY PARTS. COPYRIGHT 2010 EATON CORP		TITLE ENGINEERING DRAWING TPC2104 ASSY 2104	
DIMENSIONS IN INCHES TOLERANCES: DECIMALS ANGLES ±.003 ± 0.5° UNLESS OTHERWISE SPECIFIED CAGE CODE 31795	DRAWN BY: MDR SCALE: 1:1	DWG FILENAME: TPC2104_ME.DWG SHEET: 1 OF 1 REV NO. TPC2104_ME	REV 04