Effective April 2020 Supersedes October 2017

22 x 58 mm Modular fuse holders



Product description

Eaton's Bussmann[®] series 22 x 58 mm modular fuse holders are suitable for use with standard cylindrical fuse links and FW type ferrule fuse links.

BUSSMANN

SFRIFS

Their compact dimensions helps reduce space, allows for higher cable bending radius. Low watts loss and wide range of accessories make them ideally suited for most industrial applications.

Standard features

- Compact dimensions
- Ventilation zones optimised for a better heat dissipation
- Inbuilt padlocking facility
- IP20 degree of protection (see page 2)
- Flexiblity to mount on DIN Rail and/or screw mounting
- Toolless DIN-Rail mounting, improves ease of use and reduces installation time and costs



Technical Data 10115

Effective April 2020

Catalogue symbol

- CH221DNXU: neutral fuse holder
- CH22(# of poles)**DU**: standard fuse holder
- CH22(# of poles)**DIU**: fuse holder with neon indicator
- CH221(# of poles)**DNU**: standard fuse holder and neutral
- CH221(# of poles)**DNIU**: standard fuse holder and neutral and neon indicator
- CH221(# of poles)DMSU-F: fuse holder with microswitch (pre-breaking/fuse operation)
- CH221(# of poles)DNMSU-F: fuse holder with neutral and microswitch (pre-breaking/fuse operation)
- CH221DI-48U: fuse holder with LED indicator

Compatible fuse links

- C22G and C22M: 22 x 58 mm gG and gM fuse links
- FWP-A22F, see maximum continuous fuse current below

Table 1. FWP Ferrule fuse links

Catalogue number	Maximum continuous fuse current
FWP-20A22F	20 A
FWP-25A22F	25 A
FWP-32A22F	32 A
FWP-40A22F	38 A
FWP-50A22F	44 A
FWP-63A22F	55 A
FWP-80A22F	73 A
FWP-100A22F	86 A

Technical data

- Number of poles: 1 to 4
- Rated voltage
 - IEC: CH22DU Series 690 V a.c. / 1000 V d.c.
- UL: 700 V a.c.
- Rated current
 - IEC: CH22DU Series 125 A (a.c. and d.c.)
 - UL: 100 A (a.c.)
- SCCR: 120 kA (a.c.) / 50 kA (d.c.)
- Microswitch (IEC): 250 V a.c. / 5 A
- Rated power acceptance: 9.5 W to IEC 60269-2
- Protection index: IP20 Finger-safe
- Rated impulse withstand voltage (Uimp): 6 kV
- Cable size (Copper only): 2.5 mm² 35 mm²
- Torque settings:
 - Recommended torque setting 4 N•m
 - Maximum torque setting: 5 N•m
- Mounting: 35mm DIN-Rail or 2 x M4 Panel mounting screws
- Self-extinguishable UL 94-V0 rated polyester material
- Storage & operating temperature range
 - Storage temperature -40°C to +80°C
 - Operating temperature -20°C to +70°C
- RoHS compliant.

Standards/Approvals

- IEC 60269-1 and 60269-2
- UL listed file number E14853
- CCC

Packaging

- 1-pole: 6 per pack
- 2-pole: 3 per pack
- 3-pole: 2 per pack
- 4-pole: 1 per pack

Table 2. Technical data

Old part number	New part number	Number of poles	Description			
Neutral only						
CH221BNX	CH221DNXU	1	Neutral holder			
Fuse holder only						
CH221B	CH221DU	1	1-pole fuse holder			
CH222B	CH222DU	2	2-pole fuse holder			
CH223B	CH223DU	3	3-pole fuse holder			
CH224B	CH224DU	4	4-pole fuse holder			
Fuse holder with neon indicator						
N/A	CH221DIU	1	1-pole fuse holder with neon indi- cator			
N/A	CH222DIU	2	2-pole fuse holder with neon indi- cator			
N/A	CH223DIU	3	3-pole fuse holder with neon indi- cator			
N/A	CH224DIU	4	4-pole fuse holder with neon indi- cator			
Fuse holder and neutral						
CH221BN	CH221DNU	2	1-pole + neutral fuse holder			
CH223BN	CH223DNU	4	3-pole + neutral fuse holder			
Fuse holder and neutral and neon indicator						
N/A	CH221DNIU	2	1-pole+neutralfuseholder+neon indicator			
N/A	CH223DNIU	4	3-pole+neutralfuseholder+neon indicator			
Fuse holder with microswitch						
CH221BMS	CH221DMSU-F	1	1-polefuseholderwithmicroswitch (pre-breaking/fuse operation)			
CH223BMS	CH223DMSU-F	3	3-polefuseholderwithmicroswitch (pre-breaking/fuse operation)			
Fuse holder with	Fuse holder with neutral and microswitch					
CH223BNMS	CH223DNMSU-F	3	3-pole cylindrical fuse holder + neutral+microswitch(pre-breaking/ fuse operation)			
Fuse holder with LED Indicator						
N/A	CH221DI-48U	1	1-pole fuse holder with LED Indicator			


22 x 58 mm Modular fuse holders


Table 3. Accessories

Part number	Description	Unit packing
JV-L	Multi-poleconnectorkit.Onekitwillgangupto4-poles together	12
CH22-CTP	IP20protectionaccessory, provides IP20protection to terminals with 10mm ² or less cable	12
CH22-SPS	Microswitch to work on CH221D(I)U , 1 n/o + 1 n/c changeover type	3
CH22-TPS	Microswitch to work on CH223D(I)U , 1 n/o + 1 n/c changeover type	3

Technical Data 10115 Effective April 2020

Dimensional data - mm





Eaton EMEA Headquarters Route de la Longeraie 7 1110 Morges, Switzerland

Eaton Electrical Products Limited Unit 1, Hawker Business Park Melton Road Burton-on-the-Wolds Leicestershire, LE12 5TH United Kingdom

© 2020 Eaton All Rights Reserved PDF Only Publication No. 10115 April 2020 Changes to the products, to the information contained in this document, and to prices are reserved; so are errors and omissions. Only order confirmations and technical documentation by Eaton is binding. Photos and pictures also do not warrant a specific layout or functionality. Their use in whatever form is subject to prior approval by Eaton. The same applies to Trademarks (especially Eaton, Moeller, and Cutler-Hammer). The Terms and Conditions of Eaton apply, as referenced on Eaton Internet pages and Eaton order confirmations.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

