





EMI302-06
G3 METERED INPUT

FUNCTIONALITY	INPUT	OUTPUT	OPERATING TEMPERATURE
CURRENT, POWER, AND ENERGY METERING FOR INPUT AND BRANCH	NEMA L21-20P 6FT 12AWG / 5C POWERCORD	(30) IEC 60320 C13 GRIP (6) IEC 60320 C19 GRIP	32° TO 140° F 0° TO 60° C
MECHANICAL	INPUT RATING	OUTPUT RATING	CERTIFICATIONS
66.50" (1689mm) LENGTH 2.05" (52mm) WIDTH 2.09" (53mm) DEPTH ALUMINUM CHASSIS, BLACK	120/208V~ WYE 3W+N+PE 16A 50/60HZ	200-240V~ 15A PER C13 16A PER C19 16A MAX PER SECTION 16A MAX PER PHASE	
CIRCUIT BREAKERS	FILTER AND SPIKE/SURGE	ACCESSORIES	CONFIGURATION
(3) 20A 2-POLE LISTED	NONE	INCLUDED SPK012 - INSTALLATION INCLUDED SPK013 - NETWORK OPTIONAL EMP001 - ENVIRONMENTAL PROBE	EMI3PB13JGJ78A1 SERIAL NUMBER B672_____



TITLE	ePDU G3 SPECIFICATION EMI302-06	DRAW	H. NGUYEN 09 FEB 2015
DWG NO.	EMI3PB13JGJ78A1 REV 002	CHECKED	
MATERIAL		SAFETY	
COATING		APPROVED	
UNITS	in[mm]	SCALE	
SHEET	1/1	A3 1:5	 ELECTRICAL SECTOR