

Eaton's LORN series surge protection devices for marine grade electrical distribution equipment



Contents

Description	Page
Introduction	2
Applications	2
Features	2
Standards and certifications	2
Performance data	2
Technical data	3



Powering Business Worldwide

Introduction

Eaton's LORN series of fused, surge protective devices

Harsh environmental conditions and increasing onboard technology present challenges for maintaining reliable power aboard a vessel or a rig. Whether a modest commercial vessel or a vast, multi-level cruise ship, one small power transient can impact critical safety and navigation equipment.

Applications

Eaton's Innovative Technology LORN series surge protective device (SPD) solutions have been specifically designed and tested for marine environments to protect vital pieces of equipment, safeguard personnel, and minimize downtime. The solution is also easy to install and requires no regular maintenance—providing the highest return on investment of any piece of power quality equipment.

Features

- 20-year replacement warranty
- UL® 1449 4th Edition Listed—E316410-VZCA
- Internally threaded conduit fitting and multi-point mounting feet
- Operating temperature: -40 °F to +185 °F
- Typical 4–6 month return on investment

Standards and certifications

UL 1449 3rd Edition recognized component for the United States and Canada, certified by Underwriters Laboratories certification and follow-up service.

Performance data

Part number	Product type	Voltage (Vac)	Voltage range	Enclosure	Phase ①	Protection modes	VPR (Vpk)	In	MCOV
LORN-1S120A-C-NM	Type 2 SPD	120	100–130	NEMA 4	Split-phase	L-G	700	5 kA	150
	Type 2 SPD	120	100–130	NEMA 4	Split-phase	L-L	700	5 kA	150
LORN-1S120A-C-NMX	Type 2 SPD	120	100–130	NEMA 4X	Split-phase	L-G	700	5 kA	150
	Type 2 SPD	120	100–130	NEMA 4X	Split-phase	L-L	700	5 kA	150
LORN-3Y120/208AC-NM	Type 2 SPD	120/208	174–220	NEMA 4	Three-phase wye	L-L	1200	3 kA	320
	Type 2 SPD	120/208	174–220	NEMA 4	Three-phase wye	L-N	600	3 kA	150
	Type 2 SPD	120/208	174–220	NEMA 4	Three-phase wye	L-G	600	3 kA	150
	Type 2 SPD	120/208	174–220	NEMA 4	Three-phase wye	N-G	700	3 kA	150
LORN-120NNC-NM	Type 2 SPD	120	100–130	NEMA 4	Three-phase delta	L-L	700	5 kA	150
	Type 2 SPD	120	100–130	NEMA 4	Three-phase delta	L-G	700	5 kA	150
LORN-120NNC-NMX	Type 2 SPD	120	100–130	NEMA 4X	Three-phase delta	L-L	700	5 kA	150
	Type 2 SPD	120	100–130	NEMA 4X	Three-phase delta	L-G	700	5 kA	150
LORN-240NNC-NM	Type 2 SPD	240	200–240	NEMA 4	Three-phase delta	L-L	1200	3 kA	320
	Type 2 SPD	240	200–240	NEMA 4	Three-phase delta	L-G	1200	3 kA	320
LORN-1S480C-NM	Type 2 SPD	480	400–480	NEMA 4	Split-phase	L-L	1800	5 kA	552
	Type 2 SPD	480	400–480	NEMA 4	Split-phase	L-G	1800	5 kA	552
LORN-480NNC-NM	Type 2 SPD	480	400–480	NEMA 4	Three-phase delta	L-L	1800	3 kA	552
	Type 2 SPD	480	400–480	NEMA 4	Three-phase delta	L-G	1800	3 kA	552
LORN-480NNC-NMX	Type 2 SPD	480	400–480	NEMA 4X	Three-phase delta	L-L	1800	3 kA	552
	Type 2 SPD	480	400–480	NEMA 4X	Three-phase delta	L-G	1800	3 kA	552

① D = delta, Y = wye, S = split-phase

② L = line, N = neutral, G = ground

Technical data

Description	Specification
Peak surge current	
LORN-1S120A-C-NM	160 kA per phase
LORN-1S120A-C-NMX	160 kA per phase
LORN-1S480C-NM	160 kA per phase
LORN-120NNC-NM	120 kA per phase
LORN-120NNC-NMX	120 kA per phase
LORN-240NNC-NM	120 kA per phase
LORN-480NNC-NM	120 kA per phase
LORN-480NNC-NMX	120 kA per phase
LORN-3Y120-208A-CNM	160 kA per phase
Warranty	20-year replacement
Unit listing	UL 1449 4th Edition and UL 1283 5th Edition
System voltages	
Split-phase	120/240 V
Single-phase	480 V
Three-phase wye	120/208 V
Three-phase delta	120, 240, 480 V
Manufacturer qualifications	ISO 9001 ISO 14001
Input power frequency	10–2240 Hz
Response time	≤1 nanosecond
Protection modes	
Split-phase 120 V	L-G, L-L
Three-phase wye	L-L, L-N, L-G, N-G
Three-phase delta	L-G, L-L
Circuit diagnostics	LED indicator, 1 per phase
Internal protection	Internal, replaceable, 30 A
Operating temperature	–40 °F to +180 °F




Figure 1. LORN dimensions

Eaton
1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com

© 2015 Eaton
All Rights Reserved
Printed in USA
Publication No. TD158028EN / Z16201
March 2015



For additional information, visit
www.itvss.com or call
1-800-809-2772 option 4, option 2.

Eaton is a registered trademark.
All other trademarks are property
of their respective owners.