



## The power of space

Next generation Compact Circuit Protector  
for use with Class CF CUBEFuse™ requires  
up to 69% less space

Available up to 400 A

**EATON**

*Powering Business Worldwide*



**BUSSMANN**  
SERIES

## Compact Circuit Protector - CUBEFuse



The Bussmann series Compact Circuit Protector is a UL 98 Listed disconnect switch and is now available up to 400 amps.

Symbol	Amps	Description
CCP2-(pole)-30CF	30	Switch only
CCP2-(pole)-60CF	60	
CCP2-(pole)-100CF	100	
CCP2-(pole)-200CF	200	
CCP2-(pole)-400CF	400	Switch only*
CCP2R-(pole)-30CF	30	Right front rotary, clockwise operated switch
CCP2R-(pole)-60CF	60	
CCP2R-(pole)-100CF	100	
CCP2RL-(pole)-30CF	30	Left front rotary, clockwise operated switch
CCP2RL-(pole)-60CF	60	
CCP2RL-(pole)-100CF	100	
CCP2S-(pole)-30CF	30	Right side rotary, clockwise operated switch
CCP2S-(pole)-60CF	60	
CCP2S-(pole)-100CF	100	
CCP2SL-(pole)-30CF	30	Left side rotary, counterclockwise operated switch
CCP2SL-(pole)-60CF	60	
CCP2SL-(pole)-100CF	100	

\*Rotary operators for 200 and 400 A CCP are available as accessories, for front or side (left or right) operation. Front rotary operators are available 3-pole switches only, while the side operator may be applied to 1-, 2- or 3-pole units.

The revolutionary Bussmann™ series Compact Circuit Protector (CCP) for Class CF Low-Peak™ CUBEFuse™ delivers the smallest footprint compared to any Class J disconnect solution — requiring up to **69% less space**.

The CCP is a UL® 98 Listed fused, disconnect switch that packs up to a 200 kA short-circuit current rating (SCCR) at 600 V to help increase equipment SCCR. These high ratings and compact design make the CCP ideal for industrial control panels, machinery and HVAC applications.

### Features

- Requires up to 69% less space than traditional fusible switches, which saves valuable panel space
- Rotary operated versions provide through-the-door and through-the-side operation flexibility for enhanced safety
- Multi-wire lug kits with terminal shrouds reduce wire connection and control panel components by allowing for power distribution to multiple loads
- Optional selector and pistol handles available for use with rotary operated versions
- Built-in switch interlock prohibits removing the fuse under load
- Standard open fuse indication light speeds troubleshooting
- 1/4" lockout/tagout provision enhances safety
- Straight voltage rated for application flexibility

69%  
smaller



**Space savings of 69%**  
Footprint of a CCP2-3-200CF compared to the footprint of a traditional, 3-pole Class J disconnect solution.



**BUSSMANN**  
SERIES

## Compact Circuit Protector - CUBEFuse

### Ratings:

#### Volts:

- 600 Vac
- 125 Vdc (up to 100 A)

#### Amps:

- 30 A
- 60 A
- 100 A
- 200 A
- 400 A

#### SCCR:

- 200 kA RMS Sym.
- 100 kA DC (up to 100 A)

Factory configured 1-, 2- and 3-pole

### Agency information:

- UL 98 Listed, Guide WHTY, File E302370
- cULus to Canadian Standard 22.2 No. 4-04, Guide WHTY7, File E302370
- CE
- RoHS compliant
- IEC 60947 AC-21A (up to 30 A)

### Construction:

Finger-safe design

-20°C to 75°C\*

### Mounting:

- Panel mount
- 35 mm DIN-Rail (up to 100 A)

### Accessories:

- Multi-wire lug kits with terminal shrouds
- Selector and pistol handles for use with rotary operated switches
- NFPA 79 compliant handles
- Handle shafts
- Auxiliary contacts




1-, 2-, and 3-pole CCP2-30CF

### Poles:

### Operating temperature:

See data sheet no. [10801](#) (CCP) and [1161](#) (CCPB) for complete technical information.  
Or [click here](#) to go to the product detail webpage.

\* For fuse performance under or above 25°C, consult fuse performance charts in Eaton's Bussmann series Selecting Protective Devices (SPD) handbook (Pub. no. 3002).



Multi-wire lugs mount in switch box lug terminals to provide additional wire ports per pole.



3-pole 60 A CCP shown with left through-the-front rotary operator.



3-pole 60 A CCP shown with right through-the-side rotary operator.



3-pole 200 A CCP shown with right through-the-side rotary operator.



3-pole 200 A CCP shown with front through-the-door rotary operator.



3-pole 400 A CCP shown with front through-the-door rotary operator.

**Eaton**  
1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
[Eaton.com](http://Eaton.com)

Bussmann Division  
114 Old State Road  
Ellisville, MO 63021  
United States  
[Eaton.com/bussmannseries](http://Eaton.com/bussmannseries)

© 2024 Eaton  
All Rights Reserved  
Publication No. 10809  
September 2024

Eaton, Bussmann, CUBEFuse and Low-Peak are valuable trademarks of Eaton in the US and other countries. You are not permitted to use the Eaton trademarks without prior written consent of Eaton.

UL is a registered trademark of the Underwriters Laboratories, Inc.

For Eaton's Bussmann series product information, call **1-855-287-7626** or visit: **[Eaton.com/bussmannseries](http://Eaton.com/bussmannseries)**

Follow us on social media to get the latest product and support information.

