



T CLASS FUSEHOLDER
CAT. NO. TM30200-XCR
200A 300V

NOTES:

- AGENCY INFORMATION:
UL FILE NO. E14853
CSA CERTIFIED
- MATERIAL:
INSULATOR - PHENOLIC LAMINATE
TEMP. RATINGS 150°C (302°F)
CONNECTOR - PLATED ALUMINUM
BOLT - PLATED STEEL
WASHER- PLATED STEEL
MOUNTING SCREW - PLATED STEEL
SET SCREW - PLATED ALUMINUM
- TERMINATION:
250 KCMIL - 6 CU AL
- RATINGS:
MAXIMUM AMP PER POLE - 200A
BASED ON NEC WIRE RATINGS CODE, 75°C

DRAWING REVISION A	REVISION BY TTM	REV DATE/© DATE 5/25/20	TOLERANCES (EXCEPT AS NOTED): DEC. INCH mm ANGLE .X ±0.1 [±3] ±7° 30" .XX ±0.03 [±0.8] .XXX ±0.015 [±0.38] .XXXX ±0.0005 [±0.013] REMOVE BURRS & BREAK SHARP EDGES: .003/.015 [0.08/.38] X 45° CORNER FILLETS: R.02 [.5] MACHINED SURFACES: 200 INCH 5.1 mm mm DIMENSIONS IN [BRACKETS] ARE FOR REFERENCE ONLY	DRAWN BY T. MINNICK	<div>EACONBUSSMANN SERIES</div>				
ECO ECO-0183923	APPROVED BY	DATE		DATE 5/25/20	DESCRIPTION TM30200-XCR				
ECO DESCRIPTION AS RELEASED				APPROVED BY					
COPYRIGHT (PER REVISION DATE) REGAL BELOIT AMERICA, INC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF REGAL BELOIT AMERICA, INC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.				DATE	REFERENCE		MATERIAL	PROCESS/FINISH	
					THIRD ANGLE PROJECTION		SIZE B	DRAWING NUMBER 722X200	SHEET 2 OF 2