


# STN254050UL50 and STN254050UL50H TVS Diode array ESD suppressor



### Product features

- Solid-state silicon-avalanche technology
- Up to four I/O lines of protection
- Low operating voltage
- Ultra low capacitance: 0.25 pF typical (I/O to I/O)
- Low operating and clamping voltage
- Low leakage current
- High ESD withstand option available
- Meets moisture sensitivity level (MSL) 3
- Molding compound flammability rating: UL 94V-0
- Termination finish: Ni/Pd/Au

### Applications


- Digital visual interface (DVI)
- Display port TM interface
- MDDI ports
- PCI express
- SATA interfaces
- High definition multi-media interface (HDMI)

### Environmental compliance and general specifications


- IEC61000-4-2 (ESD)
  - Up to ±20 kV (air)
  - Up to ±20 kV (contact)
- IEC61000-4-5 (Lightning) 5 A (8/20 μs)




### Ordering part number




### Pin out/functional diagram



DFN2510-10L



Pin configuration



Top view

### Absolute maximum ratings

(+25 °C, RH=45%-75%, unless otherwise noted)

Parameter	Symbol	Value		Unit
		STN254050UL50H	STN254050UL50	
Peak pulse power dissipation on 8/20 μs waveform	P <sub>pp</sub>	100	100	W
ESD per IEC 61000-4-2 (Air)	V <sub>ESD</sub>	+/-20	+/-15	kV
ESD per IEC 61000-4-2 (Contact)		+/-20	+/-8	
Lead soldering temperature	T <sub>L</sub>	+260 (10 seconds)	+260 (10 seconds)	°C
Operating junction temperature range	T <sub>J</sub>	-55 to +125	-55 to +125	°C
Storage temperature range	T <sub>STG</sub>	-55 to +150	-55 to +150	°C

### Electrical characteristics

(+25 °C)

#### STN254050UL50H


Parameter	Test condition	Minimum	Typical	Maximum	Symbol (Units)
Reverse working voltage	I/O to GND	-	-	5	V <sub>RWM</sub> (V)
Reverse breakdown voltage	I/O to GND I <sub>T</sub> = 1 mA	6.0	-	8.5	V <sub>BR</sub> (V)
Reverse leakage current	I/O to GND V <sub>RWM</sub> = 5 V	-	-	0.5	I <sub>R</sub> (μA)
Clamping voltage*	I <sub>pp</sub> = 1 A, t <sub>p</sub> = 8/20 μs	-	9.5	10.5	V <sub>C</sub> (V)
	I <sub>pp</sub> = 5 A, t <sub>p</sub> = 8/20 μs	-	13	15	V <sub>C</sub> (V)
	-	-	-	-	-
Junction capacitance	V <sub>RWM</sub> = 0 V, f = 1 MHz I/O pin to GND	-	0.5	0.65	C <sub>J</sub> (pF)
	V <sub>RWM</sub> = 0 V, f = 1 MHz Between I/O pins	-	0.25	0.35	C <sub>J</sub> (pF)

#### STN254050UL50

Parameter	Test condition	Minimum	Typical	Maximum	Symbol (Units)
Reverse working voltage	I/O to GND	-	-	5.0	V <sub>RWM</sub> (V)
Reverse breakdown voltage	I/O to GND I <sub>T</sub> = 1 mA	6.0	-	9.0	V <sub>BR</sub> (V)
Reverse leakage current	I/O to GND V <sub>RWM</sub> = 5.0 V	-	0.1-	1.0-	I <sub>R</sub> (μA)
Clamping voltage*	I <sub>pp</sub> = 1 A, t <sub>p</sub> = 8/20 μs	-	9.0	6.5	V <sub>C</sub> (V)
	I <sub>pp</sub> = 3.5 A, t <sub>p</sub> = 8/20 μs	-	11	12	V <sub>C</sub> (V)
Junction capacitance	V <sub>RWM</sub> = 0 V, f = 1 MHz I/O pin to GND	-	0.5	0.65	C <sub>J</sub> (pF)
	V <sub>RWM</sub> = 0 V, f = 1 MHz Between I/O pins	-	0.25	0.4	C <sub>J</sub> (pF)

\* Non-repetitive current pulse, according to IEC61000-4-5.

**Mechanical parameters, pad layout- mm**



Dimension	Millimeters			Inches		
	Minimum	Typical	Maximum	Minimum	Typical	Maximum
A	0.45	-	0.65	0.018	-	0.026
A1	0.00	-	0.05	0.000	-	0.002
A2		0.150 REF			0.006 REF	
b	0.15	0.20	0.25	0.006	0.008	0.010
b1	0.35	0.40	0.45	0.014	0.016	0.018
D	2.45	2.50	2.55	0.096	0.098	0.100
E	0.95	1.00	1.05	0.037	0.039	0.041
E1	0.30	0.455	0.61	0.012	0.018	0.024
e		0.50 BSC			0.020 BSC	
L	0.33	-	0.45	0.013	-	0.018

**Part marking**



(STN254050UL50H)




(STN254050UL50)

**Packaging information mm/inches**

Drawing not to scale.


Supplied in tape and reel packaging, 3,000 parts per 7" EIA-481 diameter reel




Symbol	Dimensions	
	Millimeters	Inches
A0	1.15±0.05	0.045±0.002
B0	2.70±0.05	0.106±0.002
K0	0.59±0.05	0.023±0.002
P0	4.00±0.10	0.157±0.004
P1	4.00±0.10	0.157±0.004
P2	2.00±0.05	0.079±0.002
T	0.20±0.02	0.008±0.001
E	1.75±0.10	0.069±0.004
F	3.50±0.05	0.138±0.002
D0	1.55±0.05	0.061±0.002
D1	0.60±0.10	0.024±0.004
W	8.0±0.10	0.315±0.004
B	2.0±0.5	0.079±0.020
H	4.0±0.5	0.157±0.020
C	13.0±0.5	0.512±0.020
G	8.4±1.5	0.331±0.059
T1	14.9(max)	0.587(max)
N	60	2.362
D	178±2.0	7±0.079

**Ratings and V-I characteristic curves** (+25 °C unless otherwise noted)


**V- I curve characteristics (Uni-directional)**




**Pulse waveform (8/20  $\mu$ s)**




**Pulse derating curve**



**ESD waveform**



**Solder reflow profile**



**Table 1 - Standard SnPb solder ( $T_c$ )**

Package thickness	Volume mm <sup>3</sup> <350	Volume mm <sup>3</sup> ≥350
<2.5 mm	235 °C	220 °C
≥2.5 mm	220 °C	220 °C

**Table 2 - Lead (Pb) free solder ( $T_c$ )**

Package thickness	Volume mm <sup>3</sup> <350	Volume mm <sup>3</sup> 350 - 2000	Volume mm <sup>3</sup> >2000
<1.6 mm	260 °C	260 °C	260 °C
1.6 – 2.5 mm	260 °C	250 °C	245 °C
>2.5 mm	250 °C	245 °C	245 °C

**Reference J-STD-020**

Profile feature	Standard SnPb solder	Lead (Pb) free solder
Preheat and soak	<ul style="list-style-type: none"> <li>Temperature min. (<math>T_{smin}</math>)</li> <li>Temperature max. (<math>T_{smax}</math>)</li> <li>Time (<math>T_{smin}</math> to <math>T_{smax}</math>) (<math>t_s</math>)</li> </ul>	<ul style="list-style-type: none"> <li>100 °C</li> <li>150 °C</li> <li>60-120 seconds</li> </ul>
Ramp up rate $T_L$ to $T_p$	3 °C/ second max.	3 °C/ second max.
Liquidous temperature ( $T_L$ ) Time ( $t_L$ ) maintained above $T_L$	<ul style="list-style-type: none"> <li>183 °C</li> <li>60-150 seconds</li> </ul>	<ul style="list-style-type: none"> <li>217 °C</li> <li>60-150 seconds</li> </ul>
Peak package body temperature ( $T_p$ )*	Table 1	Table 2
Time ( $t_p$ )* within 5 °C of the specified classification temperature ( $T_c$ )	20 seconds*	30 seconds*
Ramp-down rate ( $T_p$ to $T_L$ )	6 °C/ second max.	6 °C/ second max.
Time 25 °C to peak temperature	6 minutes max.	8 minutes max.

\* Tolerance for peak profile temperature ( $T_p$ ) is defined as a supplier minimum and a user maximum.

Life Support Policy: Eaton does not authorize the use of any of its products for use in life support devices or systems without the express written approval of an officer of the Company. Life support systems are devices which support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin.

**Eaton**  
Electronics Division  
1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
Eaton.com/electronics

© 2020 Eaton  
All Rights Reserved  
Printed in USA  
Publication No. 11143 BU-MC20125  
September 2020

Eaton is a registered trademark.  
All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

