





TVS diode

DR inductor	HCM1A inductor
A.	

PTSA restttable fuse

High-power LEDs are an efficient and reliable source of light; however, until recently, LED lighting was mainly used on rear vehicle and passenger compartment lighting, as LED drivers were not able to handle the high lumens required for headlights and running lights. Moreover, these drivers did not support ambient temperatures exceeding +125 °C.

Eaton's portfolio of automotivegrade components for highpower LED lighting, including the DRA/DRAP/DRAQ, HCM1A/ HCM1AV2, HCSA inductors, and CSR resistors, provide a higher luminescence for safety and improved energy efficiency at lower costs. These products enable manufacturers to develop higher-power LED headlight clusters that perform well at higher currents in a smaller package.

Eaton lights the way for the automobile industry

Eaton's PTSA(HT) resettable fuses and TVS diodes are ideal for high-performance, low-cost overcurrent, and overvoltage protection respectively in automotive LED modules in the event of short circuiting and transient voltage or ESD events. The PTSA(HT) is AEC-Q200 qualified and suitable for use in operating temperatures up to 125°C.

DRA/DRAP/DRAQ inductors

Eaton's DRA product line offers automotive electronics engineers one of the industry's most robust selections of automotive-grade inductors with five different mechanical sizes and high inductance/current ranges. DRA inductors can be utilized in both exterior and interior LED lighting applications. The DRAQ automotive inductor features coupled windings (single/dual) with a high-power density shielded drum core. The DRAP is suitable for applications beyond AEC-Q200 standards and rated for 30G in a

4-terminal solution for enhanced reliability. LED applications include headlamps, tail lamps, and interior lighting. DRA/DRAQ inductors are AEC-Q200 qualified with maximum operating temperatures of +165 °C.

HCM1A/HCM1AV2 inductors

Eaton's HCM1A and HCM1AV2 inductors have tight thermal coupling that ensures efficient heat dissipation under high current conditions. They are available in a variety of sizes and higher inductance values, allowing automotive designers to utilize higher voltages needed to drive multiple high-power LED arrays for headlights and daytime running lights. These highcurrent power inductors have rugged durability to withstand harsh environmental, electrical, and mechanical conditions. They are suitable for use in headlamps, tail lamps, interior lighting, and LED lighting.

HCSA inductors

Eaton's HCSA is a high-current

molded coupled inductor suitable for high-performance, higher power automotive SEPIC applications. Its unique molded construction provides high inductance and high operating current capability over a wide operating temperature range from -55 °C to +155 °C. This inductor offers a soft roll-off essential to maintain the highest inductance under high current and temperature conditions.

Eaton's HCSA inductors come in a 10 mm x 10 mm x 8 mm footprint and three popular inductance values: 10 μ H, 15 μ H, and 22 μ H. HCSA1V supports high-current SEPIC applications in LEDs up to 11 A, which is desirable for next-generation automotive headlamps.

MPIAV2 inductors

Eaton MPIAV2 automotive inductors are AEC-Q200 qualified products ideal for interior and exterior body electronics and lighting systems (e.g., headlamps, tail lamps, interior lighting, and LED lighting). They feature an



advanced molded construction with high current handling, improved heat dissipation, rugged durability, and excellent temperature resistance. Eaton's automotive-grade products provide the automotive engineer with added flexibility to design, enabling new vehicle features and enhancing the driving experience.

TVS diodes | ESD suppressors

Eaton's TVS Diode ESD Suppressors provide overvoltage protection with very fast response times, low clamping voltage, and high peak current capability for a wide range of automotive applications. A key application is load dump transient protection where a battery becomes disconnected while being charged by the alternator, creating a pulse as high as 120 V with a decay of up to 400ms. With ultra-fast response times, Eaton's TVS diode will instantaneously clamp the transient voltage to a suitable level to prevent damage to sensitive electronics. Crucially, Eaton's TVS diodes are AEC-Q101 qualified and available in surface mount as well as radial/through-hole footprints. Eaton TVS diodes utilize silicon avalanche technology for excellent protection against damaging transients, from ESD up to induced lightning.

PTSA(HT) resettable fuses

Eaton Bussmann series PTSA and PTSA(HT) positive temperature coefficient (PPTC) fuses provide resettable overcurrent protection to minimize the need for the replacement of one-time fuses. These fuses are offered in multiple surface-mount industry footprints ranging from 0805 to 1812. With a very fast time-to-trip, these products provide designers the flexibility to address various circuit protection needs. Eaton's PTSA and PTSA(HT) resettable fuses meet AEC-Q200 gualifications for use in diverse automotive applications with the PTSA(HT) rated up to 125°C for high-temperature operation. They offer low resistance for reduced power dissipation and voltage ratings above 16 V to address typical requirements in infotainment, telematics, lighting, body control, and other automotive applications.

CSR resistors

Eaton's current sense resistors (CSR) are offered in Metal film, foil, and plate constructions. Many families are AEC-Q200 qualified for automotive applications such as high-power LED lighting. Eaton's metal film resistors are constructed using high accuracy foil on a substrate to ensure high thermal conductivity, low inductance, and low noise. They are offered in 0603 to 2512 EIA footprints with short and wide terminal configurations as well as power ratings up to 3 W and resistances up to nearly 1 ohm.

Eaton's metal plate CSR resistors are designed using a metal plate with epoxy overcoat and end terminations for a low-temperature coefficient of resistance (TCR), low resistance, and high power capability. These products are offered in 0603 to 2512 EIA footprints with short and wide terminal configurations as well as power ratings up to 3W and resistances down to 1 m Ω .

Eaton 1000 Eaton Boulevard Cleveland, OH 44122 United States Faton com

© 2022 Eaton All Rights Reserved Printed in USA Publication No. 10754 BU-ELX22094 June 2022

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

www.eaton.com/electronics

Follow us on social media to get the latest product and support information



Powering Business Worldwide