

Regeneration Instructions for Filter Cartridges

BECO® MEMBRAN PS Wine and BECO® MEMBRAN PS Pure

Membrane Filter Cartridges

Regeneration

As a basic rule, the BECO MEMBRAN PS Wine and Pure filter cartridges should be regenerated at a differential pressure of < 7.3 psi, 50 kPa, 0.5 bar and in all cases after each filtration:

- Empty the filter cartridge housing.
- Cold water rinsing:

Rinse with cold water in filtration direction for at least 2 minutes. The throughput should be set to 1 – 1.5 times the value for the preceding filtration, if possible. The counter pressure should be set to 7.3 psi, 50 kPa, 0.5 bar.

- Empty the cartridge housing.
- Hot water rinsing:

Rinse with hot water (176 °F (80 °C)) in filtration direction for at least 5 minutes in channel. Here too, the throughput should be set to 1 – 1.5 times the value for the preceding filtration.

Then operate the system in circulation mode for 10 – 15 minutes. The counter pressure should be set to 7.3 psi, 50 kPa, 0.5 bar.

Leave hot water in the housing overnight. Next morning rinse again the filter shortly with hot and cold water.

Note

The best regeneration success is achieved if the filter cartridges are left overnight in hot water after rinsing.

The rinsing water must be free from rust, lime, or other contamination.

Eaton recommends that the rinsing water should be filtered. The filter fineness should be based on the filter to be rinsed.

If the filter cartridges are sterilized with steam, the steam should also be filtered. Sintered stainless steel filter cartridges with a retention rating of 10 µm are suitable for this purpose.

Eaton will be glad to answer any further questions you might have. You can call either the sales manager in your area or contact the application technology department at Eaton directly at: +49 6704 204-0.

Special Cleaning Procedure if Rinsing with Hot Water is no Longer Sufficient (Differential Pressure > 7.3 psi, 50 kPa, 0.5 bar)

The special cleaning procedure should be used in the following cases:

- The filter cartridges can no longer be regenerated with cold and hot water
- Products that are difficult to filter have placed a heavy strain on the filter cartridges
- Increased differential pressure during rinsing of the filter cartridges

We are unable to offer a guarantee for the success of the special cleaning procedure or for any damage to the filter cartridges!

Special Cleaning Procedure with Caustic Soda (NaOH) and Hydrogen Peroxide (H₂O₂)

1. Rinse BECO MEMBRAN PS Wine and Pure filter cartridges in the direction of the flow (Important!). Install pump, hoses and dosing tanks such that recirculation is ensured.
2. First rinse the filter cartridges with cold water and subsequently with warm water (122 °F (50 °C)), like for normal rinsing.
3. This is followed by a caustic rinse with 1% NaOH at a temperature of 122 °F (50 °C).
4. In cases with strong contamination, Eaton recommends discarding the first few liters that are discharged from the filter housing during the caustic rinse, since they usually contain a large amount of impurities. Continue the cleaning process in circulation mode for about 5 – 10 minutes at an intake pressure of approx. 14.5 psi, 100 kPa, 1.0 bar.
5. Then carefully add 0.5% H₂O₂ and continue to circulate for a further 30 minutes.
6. After the cleaning process rinse with cold water until no more caustic solution is present (test using a pH strip).
7. For neutralization, circulate 0.5 – 1% citric acid solution for 5 minutes at approx. 86 °F (30 °C).
8. Then rinse again with water until the pH is neutral.





Powering Business Worldwide

North America

44 Apple Street
Tinton Falls, NJ 07724
Toll Free: 800 656-3344
(North America only)
Tel: +1 732 212-4700

Europe/Africa/Middle East

Auf der Heide 2
53947 Nettersheim, Germany
Tel: +49 2486 809-0

Friedensstraße 41
68804 Altlufzheim, Germany
Tel: +49 6205 2094-0

An den Nahewiesen 24
55450 Langenlonsheim, Germany
Tel: +49 6704 204-0

China

No. 3, Lane 280,
Linhong Road
Changning District, 200335
Shanghai, P.R. China
Tel: +86 21 5200-0099

Singapore

4 Loyang Lane #04-01/02
Singapore 508914
Tel: +65 6825-1668

Brazil

Rua Clark, 2061 - Macuco
13279-400 - Valinhos, Brazil
Tel: +55 11 3616-8400

**For more information, please
email us at filtration@eaton.com
or visit www.eaton.com/filtration**

EN
1A4.35.1
12-2016

© 2016 Eaton. All rights reserved. All trademarks and registered trademarks are the property of their respective owners. All information and recommendations appearing in this brochure concerning the use of products described herein are based on tests believed to be reliable. However, it is the user's responsibility to determine the suitability for his own use of such products. Since the actual use by others is beyond our control, no guarantee, expressed or implied, is made by Eaton as to the effects of such use or the results to be obtained. Eaton assumes no liability arising out of the use by others of such products. Nor is the information herein to be construed as absolutely complete, since additional information may be necessary or desirable when particular or exceptional conditions or circumstances exist or because of applicable laws or government regulations.