



## LOFMEM™ TFA Fluoropolymer Pleated Cartridge Filter

Eaton's LOFMEM TFA filters are designed to resist the most severe chemical exposure environments, making them the preferred choice for demanding high temperature and chemical process applications. LOFMEM TFA is designed for use with strong acids, bases, organic chemicals and oxidizers.

LOFMEM TFA membrane filter cartridges use absolute rated PTFE membrane combined with PTFE support layers and PFA hardware to create a fluoropolymer pleated cartridge filter suitable for use in the most demanding environments. LOFMEM TFA is manufactured without the use of glues, adhesives or wetting agents, ensuring high purity in every application.

### Features and benefits

- PTFE membrane
- Superior chemical resistance
- Absolute rated filtration
- All-thermal bonded construction, no adhesives
- No wetting agents
- Available in multiple configurations

### Design

**Filter material**  
PTFE membrane

**Inner core, cage, end caps**  
PFA

**Support layers**  
PTFE

**Gaskets/O-rings**  
FEP encapsulated (O-Rings only), FPM

**End Adapter**  
222/Flat single open end

**Retention ratings**  
0.1, 0.2, 0.45, 1 µm

### Technical data

**Nominal lengths**  
10", 20", 30", 40"  
(254, 508, 762, 1016 mm)

**Outside diameter**  
2.7" (69 mm)

**Inside diameter**  
1.1" (27.9 mm)

**Surface area**  
5.2 ft<sup>2</sup> (0.48 m<sup>2</sup>) per 10" element

**Max. operating temperature**  
338 °F (170 °C)




Powering Business Worldwide

# LOFMEM TFA membrane filter cartridges

## Flow rate\*

(68°F/20 °C per 10" filter cartridge for water)



\* For liquids other than water, multiply pressure drop by fluid viscosity in centipoise.

## Performance specifications

### Steam/autoclave


Filter cartridges will withstand at least 50 steam/autoclave 1 hour cycles @ 275 °F (135 °C)

### Integrity test values per 10" filter cartridge

Air Diffusion per 10-inch filter cartridge wet with 60/40 IPA/water. Contact Eaton for specific method.

Pore size	Specification
0.1 µm:	≤ 50 cc/min @ 18 psig (1.2 bar)
0.2 µm:	≤ 20 cc/min @ 12 psig (0.8 bar)
0.45 µm:	≤ 15 cc/min @ 5 psig (0.34 bar)
1 µm:	≤ 15 cc/min @ 3 psig (0.2 bar)

## Ordering code



### North America

44 Apple Street  
Tinton Falls, NJ 07724  
Toll Free: 800 656-3344  
(North America only)  
Tel: +1 732 212-4700

### Europe/Africa/Middle East

Auf der Heide 2  
53947 Nettersheim, Germany  
Tel: +49 2486 809-0

Friedensstraße 41  
68804 Altlußheim, Germany  
Tel: +49 6205 2094-0

An den Nahewiesen 24  
55450 Langenlonsheim, Germany  
Tel: +49 6704 204-0

### China

No. 3, Lane 280,  
Linhong Road  
Changning District, 200335  
Shanghai, P.R. China  
Tel: +86 21 5200-0099

### Singapore

100G Pasir Panjang Road #07-08  
Singapore 118523  
Tel: +65 6825-1668

### Brazil

Rua Clark, 2061 - Macuco  
13279-400 - Valinhos, Brazil  
Tel: +55 11 3616-8400

## For more information, please

email us at [filtration@eaton.com](mailto:filtration@eaton.com)  
or visit [www.eaton.com/filtration](http://www.eaton.com/filtration)

© 2018 Eaton. All rights reserved. All trademarks and registered trademarks are the property of their respective owners. All information and recommendations appearing in this brochure concerning the use of products described herein are based on tests believed to be reliable. However, it is the user's responsibility to determine the suitability for his own use of such products. Since the actual use by others is beyond our control, no guarantee, expressed or implied, is made by Eaton as to the effects of such use or the results to be obtained. Eaton assumes no liability arising out of the use by others of such products. Nor is the information herein to be construed as absolutely complete, since additional information may be necessary or desirable when particular or exceptional conditions or circumstances exist or because of applicable laws or government regulations.

US  
EF-LMTFA  
05-2018



Powering Business Worldwide

