



## LOFPLEAT™ GG micro fiberglass filter cartridges

Eaton's LOFPLEAT GG filter cartridges are suitable for the filtration of magnetic tape coatings and as a blowdown post filter. They are also widely used in the chemical, ink, and oil and gas industries.

The pleated borosilicate micro fiberglass filter cartridges are highly efficient and can be effectively used in a variety of industrial applications. They offer a high surface area for high flow rates.

### Features and benefits

- High-efficiency cartridge offering standardized pore size
- High dirt-holding and flow capability
- Reduced labor costs due to less change-outs
- Fixed pore structure prevents dirt unloading even at maximum differential pressure

### Specifications

#### Filter material

Borosilicate micro fiberglass with acrylic binder

#### Inner core, cage, end caps

Polypropylene

#### Gaskets/O-rings

Silicone (standard), EPDM, FKM, FEP/FKM (O-rings only)

#### Support layers

Polyester

#### Retention ratings

0.45, 1, 3, 10 μm  
@ 90% efficiency

### Technical data

#### Nominal lengths

10", 20", 30", 40"  
(254, 508, 762, 1016 mm)

#### Outside diameter

2.7" (69 mm)

#### Inside diameter

1" (25 mm)

#### Surface area

5.1 ft<sup>2</sup> (0.47 m<sup>2</sup>) per 10" element

#### Max. operating temperature

176 °F (80 °C)

#### Max. differential pressure

75 psid @ 70 °F (5.2 bar @ 21 °C)  
30 psid @ 176 °F (2.1 bar @ 80 °C)

#### Maximum reverse differential pressure

2.8 bar @ 21 °C

#### Recommended differential change-out pressure for disposal

35 psid (2.4 bar)




Powering Business Worldwide

# LOFPLEAT GG micro fiberglass filter cartridges

## Flow rate\*

(70°F/21°C per 10" element for water)



LOFPLEAT GG filter cartridges are available with a variety of gasket, O-ring and end cap configurations.

\* For liquids other than water, multiply pressure drop by fluid viscosity in centipoise.

## Ordering code

### Nominal lengths

- 10: 10"
- 20: 20"
- 30: 30"
- 40: 40"

### Gaskets/O-rings

- S: Silicone
- E: EPDM
- V: FKM
- T: FEP/FKM (O-rings only)



### Filter type

LPPGG:  
LOFPLEAT GG

### Retention ratings

- 0.45: 0.45 µm
- 1: 1 µm
- 3: 3 µm
- 10: 10 µm

### Adapter codes

- DOE: Double open end
- 1: SOE 226 O-rings, bayonet/flat
- 2: SOE 222 O-rings, spear
- 3: SOE 226 O-rings, bayonet/spear
- 4: SOE 222 O-rings, flat

### North America

44 Apple Street  
Tinton Falls, NJ 07724  
Toll Free: 800 656-3344  
(North America only)  
Tel: +1 732 212-4700

### Europe/Africa/Middle East

Auf der Heide 2  
53947 Nettersheim, Germany  
Tel: +49 2486 809-0

Friedensstraße 41  
68804 Altlufßheim, Germany  
Tel: +49 6205 2094-0

An den Nahewiesen 24  
55450 Langenlonsheim, Germany  
Tel: +49 6704 204-0

### China

No. 3, Lane 280,  
Linhong Road  
Changning District, 200335  
Shanghai, P.R. China  
Tel: +86 21 5200-0099

### Singapore

100G Pasir Panjang Road #07-08  
Singapore 118523  
Tel: +65 6825-1668

### Brazil

Av. Ermano Marchetti, 1435 -  
Água Branca, São Paulo - SP,  
05038-001, Brasil  
Tel: +55 11 3616-8461

For more information, please  
email us at [filtration@eaton.com](mailto:filtration@eaton.com)  
or visit [www.eaton.com/filtration](http://www.eaton.com/filtration)

© 2020 Eaton. All rights reserved. All trademarks and registered trademarks are the property of their respective owners. All information and recommendations appearing in this brochure concerning the use of products described herein are based on tests believed to be reliable. However, it is the user's responsibility to determine the suitability for his own use of such products. Since the actual use by others is beyond our control, no guarantee, expressed or implied, is made by Eaton as to the effects of such use or the results to be obtained. Eaton assumes no liability arising out of the use by others of such products. Nor is the information herein to be construed as absolutely complete, since additional information may be necessary or desirable when particular or exceptional conditions or circumstances exist or because of applicable laws or government regulations.

US  
EF-LPGG  
06-2020



Powering Business Worldwide

