



		DIM 'A'	DIM 'B'	DIM 'C'	DIM 'D'	DIM 'E'
NUMBER OF STATIONS	2	38" [965]	24" [610]	6" [152]	N/A	9-7/8" [250]
	3	40" [1016]	12" [605]	15" [381]	N/A	4-7/8" [123]
	4	52" [1321]	24" [610]	15" [381]	N/A	4-7/8" [123]
	5	64" [1626]	36" [914]	15" [381]	N/A	4-7/8" [123]
	6	76" [1930]	48" [1219]	15" [381]	24" [610]	4-7/8" [123]

REFERENCE ONLY

		BUNA-N (BUN)	NEOPRENE (FGL) (FOOD)	NORDEL (EPT)	VITON (VT)	TEFLON (TFE)	SILICONE (SIL)
UNIT TYPE	STANDARD	150 PSI [10 BAR] 225F [107°C]	150 PSI [10 BAR] 225F [107°C]	150 PSI [10 BAR] 300F [149°C]	150 PSI [10 BAR] 350F [176°C]	80 PSI [5 BAR] 350F [176°C]	150 PSI [10 BAR] 450F [232°C]



EATON FILTRATION, LLC  
 RONNINGEN-PETTER PRODUCTS  
 9151 SHAVER ROAD  
 PORTAGE, MICHIGAN 49024-6798 USA

THIS DRAWING AND ALL INFORMATION THEREON IS THE PROPERTY OF EATON CORPORATION. IT IS CONFIDENTIAL AND MUST NOT BE MADE PUBLIC. THIS DRAWING IS LOANED SUBJECT TO RETURN ON DEMAND, AND IS NOT TO BE USED DIRECTLY OR INDIRECTLY, IN ANY WAY DETRIMENTAL TO THE INTERESTS OF EATON FILTRATION, LLC.

ENGINEERING APPROVAL .	DRAWN BY R. BUFFA	TITLE AFC1100IB AFC SERIES INTERNAL BACKWASHING INLINE MULTIPLEX FILTER UNIT			
SALES/MKTG APPROVAL .	SCALE NONE				
	ENGINEERING SPECIFICATION .	DATE 05/10/05	SIZE A	DWG FILENAME AFC-1100-IB-DT001	REV A