

C310FH

3.1 mm x 10 mm Fast-acting, axial lead ceramic tube fuses



Applications

Primary circuit protection:

- Power supplies
- LED and general lighting
- Consumer electronics
- Desktop, laptop and notebook
- Test equipment

Agency information

- cURus Recognition file number: E19180, Guide JDYX2/JDYX8
- CCC: 2019010207248424
- KC-Mark: File SU05030-14001
- TUV: R50278944

Product features

- Fast-acting
- High breaking capacity
- Designed to IEC60127-3/-7
- Nickel-plated brass single end cap construction
- 3.1 mm x 10 mm compact design utilizes less board space
- Epoxy coated option available

Ordering

- Use ordering number (see page 4 for details)

Packaging suffixes

- -TR1 (1500 parts on tape and reel, tape width 60 mm)
- -TR2 (1500 parts on tape and reel, tape width 52 mm)
- E-TR1 (Epoxy coated fuse, 1500 parts on tape and reel, tape width 60 mm)

Option code

- Blank (Standard fuse)
- E (Epoxy coated)

*Discontinued effective
6/17/24 or until inventory
is depleted*



Powering Business Worldwide

Electrical characteristics

I_n	$1.5I_n$ min hours	$2.1I_n$ max minute	$2.75I_n$ min ms	max s	$4I_n$ min ms	max ms	$10I_n$ max ms
1.25 A- 2.0 A	1.0	30	10	3.0	3.0	300	20


Product specifications

Part number ¹	Current rating (A)	Voltage rating (V _{AC})	Interuppting rating at rated voltage (A)	Typical DC cold resistance (mΩ)	Typical melting I ² t (A ² s)	Maximum voltage drop (mV)	Color code band 1	Color code band 2	Color code band 3
C310FH-1.25-R	1.25	250	150	60	2.7	120	Brown	Red	Red
C310FH-1.6-R	1.6	250	150	55	3.0	120	Brown	Blue	Red
C310FH-2-R	2.0	250	150	30	4.9	120	Red	Black	Red


1. Part Number Definition: C310FH-xxx-R
C310FH = Product code
xxx = Ampere rating
-R suffix = RoHS compliant

Discontinued effective
6/17/24 or until inventory
is depleted


Dimensions–mm



Time vs. current curve



Temperature derating curve



General specifications

Terminal strength: MIL-STD-202G, Method 211A, test condition A
Thermal shock: MIL-STD- 202G, Method 107G, test condition (5 cycles -40 °C to +85 °C)
Vibration: MIL-STD- 202G, Method 201A
Life: MIL-STD- 202G, Method 108, (+70 °C at 60% rated current, 1000 hours)

Ordering codes

The ordering code is the part number replacing the “.” with a “-” plus adding the packaging suffix.

Packaging suffixes


- -TR1 (1500 parts on tape and reel, tape width 60 mm)
- -TR2 (1500 parts on tape and reel, tape width 52 mm)
- E-TR1 (Epoxy coated fuse, 1500 parts on tape and reel, tape width 60 mm)

Option code

- Blank (Standard fuse)
- E (Epoxy coated)

Part number	Ordering codes		
	-TR1 option	-TR2 option	E-TR1 option
C310FH-1.25-R	C310FH-1-25-R-TR1	C310FH-1-25-R-TR2	C310FH-1-25-RE-TR1
C310FH-1.6-R	C310FH-1-6-R-TR1	C310FH-1-6-R-TR2	C310FH-1-6-RE-TR1
C310FH-2-R	C310FH-2-R-TR1	C310FH-2-R-TR2	C310FH-2-RE-TR1

Wave solder profile



Reference EN 61760-1:2006

Profile feature		Standard SnPb solder	Lead (Pb) free solder
Preheat	• Temperature min. (T_{smin})	100 °C	100 °C
	• Temperature typ. (T_{styp})	120 °C	120 °C
	• Temperature max. (T_{smax})	130 °C	130 °C
	• Time (T_{smin} to T_{smax}) (t_s)	70 seconds	70 seconds
Δ preheat to max Temperature		150 °C max.	150 °C max.
Peak temperature (T_p)*		235 °C – 260 °C	250 °C – 260 °C
Time at peak temperature (t_p)		10 seconds max 5 seconds max each wave	10 seconds max 5 seconds max each wave
Ramp-down rate		~ 2 K/s min ~3.5 K/s typ ~5 K/s max	~ 2 K/s min ~3.5 K/s typ ~5 K/s max
Time 25 °C to 25 °C		4 minutes	4 minutes

Manual solder

+350 °C (4-5 seconds by soldering iron), generally manual/hand soldering is not recommended

Life Support Policy: Eaton does not authorize the use of any of its products for use in life support devices or systems without the express written approval of an officer of the Company. Life support systems are devices which support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin.

Eaton
Electronics Division
1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com/electronics

© 2024 Eaton
All Rights Reserved
Printed in USA
Publication No. 10405 PCN24016
June 2024

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

