


FOR DIMENSION TABLES SEE AFC-1100-IB-DT-001



SEE AFC-1100-IB-RE001 FOR RIGHT SIDE VIEW

SEE AFC-1100-IB-GA001 FOR FRONT VIEW

NOTES:

1. ALL FLANGED PROCESS CONNECTIONS ARE LAP JOINT TYPE, ZINC PLATED CARBON STEEL.
2. PROCESS FLANGE CONNECTIONS ARE DRILLED TO ANSI, CLASS 150 OR DIN ND16.
3. HEADERS MAY BE PIPED AT EITHER END; BLIND FLANGES (PURCHASER SUPPLIED) REQUIRED FOR OPPOSITE END.
4. CONTROL PANEL IS EXCLUSIVE TO AUTOMATED UNITS.
5. 1/4" VALVES (ON INLET/OUTLET HEADERS) ARE EXCLUSIVE TO AUTOMATED UNITS. MANUAL UNITS ARE EQUIPPED WITH GAUGES (1/4" NPT) AT THESE POSITIONS.
6. HANDLE EXTENSIONS ARE PROVIDED AT EACH STATION ON MANUAL UNITS.
7. ALL METALLIC WETTED PARTS ARE 316 STAINLESS STEEL.
8. AUTOMATION AIR REQUIREMENTS: 5 SCFM [142 LITERS/MIN] MAXIMUM DEMAND AT 60 PSI [4.1 BAR] MIN, 120 PSI [8.2 BAR] MAX.
9. ALL DIMENSIONS ARE IN INCHES WITH METRIC EQUIVALENTS IN BRACKETS [ ].
10. FILTER ELEMENTS ARE DESIGNED TO WITHSTAND 150 PSI [10.3 BAR] DIFFERENTIAL PRESSURE.
11. OPERATING PRESSURE IS (SEE SHEET AFC1100IB-4). HYDROSTATIC TEST PRESSURE IS (SEE SHEET AFC1100IB-4).
12. EXTERIOR FINISH:  
TOP COAT: 1 MIL MINIMUM.  
COLOR: SILVER.

ENGINEERING APPROVAL	DRAWN BY R. BUFFA	TITLE AFC1100IB AFC SERIES INTERNAL BACKWASHING INLINE MULTIPLEX FILTER UNIT			
SALES/MKTG APPROVAL	SCALE NONE				
	ENGINEERING SPECIFICATION	DATE 05/10/05	SIZE A	DWG FILENAME AFC-1100-IB-FP001	REV A

**EATON** EATON FILTRATION, LLC  
RONNINGEN-PETTER PRODUCTS  
9151 SHAVER ROAD  
PORTAGE, MICHIGAN 49024-6798 USA

THIS DRAWING AND ALL INFORMATION THEREON IS THE PROPERTY OF EATON CORPORATION. IT IS CONFIDENTIAL AND MUST NOT BE MADE PUBLIC. THIS DRAWING IS LOANED SUBJECT TO RETURN ON DEMAND, AND IS NOT TO BE USED DIRECTLY OR INDIRECTLY, IN ANY WAY DETRIMENTAL TO THE INTERESTS OF EATON FILTRATION, LLC.