



REFERENCE ONLY

NOTES:

1. DIMENSIONS 'H' AND 'W' ARE LESS PRESSURE GAUGES, BUT WITH 1/4" NPT PIPE PLUGS.
2. THE FOLLOWING METALLURGY IS AVAILABLE FOR STANDARD FILTERS: BRONZE, STEEL, AND STAINLESS STEEL.
3. 1" NPTI DRAIN VALVE IS OPTIONAL; SHOWN IN SIDE VIEW ONLY 1" PIPE CAP SUPPLIED STANDARD.
4. OPTIONAL GAUGES AVAILABLE WITH 0-200 PSI [0-13.8 BAR] STANDARD PRESSURE RANGE; OTHER PRESSURE RANGES AVAILABLE.
5. FILTER SERVICE CONNECTIONS ARE QUICK-COUPLING TYPE.
6. FILTER ELEMENTS ARE DESIGNED TO WITHSTAND 150 PSI [10.3 BAR] DIFFERENTIAL PRESSURE.
7. DESIGN PRESSURE OF UNIT IS 200 PSI [13.8 BAR].
8. ALL DIMENSIONS SHOWN IN INCHES WITH MILLIMETER EQUIVALENTS IN BRACKETS [].
9. MODEL SS-1524-STD IS SHOWN.

DIMENSIONS						
MODEL	SCREEN SIZE (DIA X LENGTH)	'H'	'H2'	'H3'	'W'	'W2'
1524-STD	2 X 24 [51 X 609]	32 3/4 [832]	35 3/4 [908]	37 1/8 [964]	7 3/4 [197]	9 1/2 [241]
1536-STD	2 X 36 [51 X 914]	54 3/4 [1391]	57 3/4 [1467]	59 15/16 [1522]	7 3/4 [197]	9 1/2 [241]

	EATON FILTRATION, LLC RONNINGEN-PETTER PRODUCTS 9151 SHAVER ROAD PORTAGE, MICHIGAN 49024-6798 USA		THIS DRAWING AND ALL INFORMATION THEREON IS THE PROPERTY OF EATON CORPORATION. IT IS CONFIDENTIAL AND MUST NOT BE MADE PUBLIC. THIS DRAWING IS LOANED SUBJECT TO RETURN ON DEMAND, AND IS NOT TO BE USED DIRECTLY OR INDIRECTLY, IN ANY WAY DETRIMENTAL TO THE INTERESTS OF EATON FILTRATION, LLC.			
	DRAWN BY R. BUFFA	TITLE 1524/1536-STD STANDARD FILTER DATA				
ENGINEERING APPROVAL .	SALES/MKTG APPROVAL .	ENGINEERING SPECIFICATION .	DATE 05/10/05	SIZE A	DWG FILENAME SNG-1500-SSTD-GA001	REV A