



ITEM	PART NAME	MATERIAL
1	BODY	SA240 304/304L
2	COVER	SA240 304/304L
3	O-RING	BUNA-N
4	PIN	SA193 B7 ZINC PL
5	SNAP RING	STEEL ZINC PL
6	BASKET RESTRAINER	304 SS
7	FILTER BAG RETAINER	316 SS
8	EYE BOLT	SA193 B7 ZINC PL
9	HEX NUT	SA194 2H ZINC PL
10	WASHER	STEEL ZINC PL
11	DAVIT ASSEMBLY	CARBON STEEL

- NOTES:**
1. UNITS ARE TO BE DESIGNED, FABRICATED & "U" STAMPED IN ACCORDANCE WITH ASME SECT. VIII, DIV. 1 BOILER & PRESSURE VESSEL CODE, IN COMPLIANCE TO LATEST ADDENDA.
 2. INLET / OUTLET FLANGE CONNECTIONS PER ANSI B 16.5.
 3. DESIGN PRESSURE: 150 PSI (MAWP)
DESIGN TEMPERATURE 250° F.
MDMT - -20° F @ 150 PSI.
 4. ALL DIMENSIONS ARE IN INCHES / (MM).
 5. ALL BOLT HOLES ARE TO STRADDLE NATURAL CENTERLINES.
 6. APPROX. WEIGHT (DRY) 2730 LB. (1238 KG.)

CERTIFIED FOR:
P.O. NO.:
SALES ORDER NO.:
QUOTE NO.:
TAG NO.:
VESSEL CODE: MBF-2402-BB10-140A-UT-11HD
PART NUMBER: F3AV2400003-304

EATON		EATON FILTRATION, LLC	
		900 FAIRMOUNT AVENUE, ELIZABETH, NEW JERSEY 07207	
		NAME MAXILINE MBF2402HD FILTER VESSEL	
		14" 150# RF INLET / TANGENTIAL OUTLET	
		STAINLESS STEEL-304	
DRAWN	FJM	DATE	12/13/06
CERT.	LH	DATE	12/13/06
SIZE	DWG NO	REV	
A		HD2414TS-304	
		B	

ELECTRONIC FILE NAME: HD2414TS-304.DWG
REF. ECR E840 DATE 10/09/07

UNAUTHORIZED USE, MANUFACTURE OR REPRODUCTION IN WHOLE OR IN PART IS PROHIBITED. DRAWING, DESIGN AND OTHER DISCLOSURES PROPERTY OF EATON FILTRATION, LLC