



Synflex Eclipse Air Brake Tubing

Product Details



Synflex Eclipse Air Brake Tubing Overshadows the Competition

Applications

- Truck Air Brake Systems
- Trailer Air Brake Systems
- Auxiliary Air Systems
- Formed Tubes
- Formed and Straight Air Brake Harness Assemblies

Construction

- Distinctive patented construction (Pat. No. 6,670,004)
- 100% polyamide construction with polyester yarn reinforcement
- UV Stabilized
- Thermoformable
- Available in standard and custom colors
- Available in all standard sizes

Temperature Range

Synflex® Eclipse™ Air Brake Tubing is designed for a wider operating temperature range than traditional nylon tubing: -65°F to 200°F (-54°C to 93°C).

Standard Compliance

Meets SAE J844, J1131, J2494-3 and DOT-FMVSS 106

Features / Benefits

- **Superior Abrasion Resistance**
Synflex Eclipse significantly outperforms rubber and Nylon11. As a result, Synflex Eclipse tubing has a longer service life in the harshest environments.
- **Enhanced Flexibility and Extension**
Synflex Eclipse tubing has improved flexibility over other nylon tubing. This translates into easier installation and handling at low temperatures.
- **Flow Performance**
With improved flow performance over traditional rubber and nylon, Synflex Eclipse Air Brake Tubing enhances brake timing performance.
- **Ease of Cutting**
The unique construction of Synflex Eclipse tubing promotes burr free cuts, which yields improved assemblies with either push-to-connect or compression fittings.




Synflex Eclipse Air Brake Tubing

Performance Comparison Data

Abrasion Resistance Test Results – Synflex Eclipse significantly outperforms rubber and Nylon11



Rubber Synflex Eclipse Nylon11



■ Rubber - FAILED @ 3,050 cycles
 ■ PA11 - FAILED @ 8,225 cycles
 ■ Synflex Eclipse - NO FAILURE @125,000+ cycles

Product Specifications

Synflex Eclipse Type A Air Brake Tubing

# PART NUMBER	NOMINAL O.D.		NOMINAL I.D.		MINIMUM BEND RADIUS		NOMINAL WALL THICKNESS		MINIMUM BURST PRESSURE		WEIGHT	
	mm	in	mm	in	mm	in	mm	in	kpa	psi	100m KG	100ft LBS
4245-022	3.18	1/8	2.01	.079	6.35	1/4	0.58	.023	6,900	1,000	.49	.33
4245-025	3.96	5/32	2.34	.092	12.70	1/2	0.79	.031	8,300	1,200	.83	.56
4245-033	4.77	3/16	2.97	.117	19.05	3/4	0.89	.035	8,300	1,200	1.06	.71
4245-041	6.35	1/4	4.32	.170	25.40	1	1.02	.040	8,300	1,200	1.77	1.19
4245-052	7.95	5/16	5.89	.232	28.58	1-1/8	1.02	.040	6,900	1,000	2.29	1.54

Synflex Eclipse Type B Air Brake Tubing

# PART NUMBER	NOMINAL O.D.		NOMINAL I.D.		MINIMUM BEND RADIUS		NOMINAL WALL THICKNESS		MINIMUM BURST PRESSURE		WEIGHT	
	mm	in	mm	in	mm	in	mm	in	kpa	psi	100m KG	100ft LBS
3270-06	9.53	3/8	6.38	.251	38.10	1.5	1.57	.062	9,700	1,400	4.2	2.8
3270-08	12.70	1/2	9.55	.376	50.80	2.0	1.57	.062	6,600	950	5.8	3.8
3270-10	15.88	5/8	11.20	.441	63.50	2.5	2.34	.092	6,200	900	10.4	7.0
3270-12	19.05	3/4	14.38	.566	76.20	3.0	2.34	.092	5,500	800	12.8	8.6

Eaton

Hydraulics Operations USA
 115 Lena Dr.
 Aurora, OH 44202
 USA
 Tel: 330-562-9111 / 800-837-1467
 Fax: 330-274-0473

Eaton

Hydraulics Operations USA
 14615 Lone Oak Road
 Eden Prairie, MN 55344
 USA
 Tel: 952-937-9800
 Fax: 952-294-7722
www.hydraulics.eaton.com

Eaton

Hydraulics Operations Europe
 Route de la Longeraie 7
 1110 Morges
 Switzerland
 Tel: +41 (0) 21 811 4600
 Fax: +41 (0) 21 811 4601

Eaton

Hydraulic Operations Asia Pacific
 11th Floor Hong Kong New World Tower
 300 Huaihai Zhong Road
 Shanghai 200021
 China
 Tel: 86-21-6387-9988
 Fax: 86-21-6335-3912