



**EATON**

TIME-CURRENT CHARACTERISTIC CURVES

MINIMUM MELT 15.5V MINI-MID RANGE, AMULTI-COIL ELSP  
BACKUP TYPE OIL IMMERSIBLE CURRENT LIMITING FUSE

DRAWN BY ALJ CHK'D GTB  
DATE 02/14/03 DATE 02/19/03  
REPLACES [REV 0] REQ NO. 21537  
DWG NO. 42 39732 B 00

Tests made at LOW Volts or at HIGH pf at 25°C with no initial load  
Standards used as basis for data: ANSI C37.47-1991 [R1992]  
MINIMUM TEST POINTS PLOTTED SO VARIATIONS SHOULD BE PLUS

THIS DRAWING WAS PRODUCED ON A CAD SYSTEM, ANY MANUAL REVISION WILL VOID IT.

Reference Data  
R240-91-72  
Page 1 of 2

**EATON**

TIME-CURRENT CHARACTERISTIC CURVES

MAXIMUM CLEAR 15.5V MINI-MID RANGE, AMULTI-COIL ELSP  
BACKUP TYPE OIL IMMERSIBLE CURRENT LIMITING FUSE

DRAWN BY ALJ CHK'D GTB  
DATE 02/14/03 DATE 02/19/03  
REPLACES [REV 0] REQ NO. 21537  
DWG NO. 42 39732 B 00

Tests made at RATED Volts or at LOW pf at 25°C with no initial load  
Standards used as basis for data: ANSI C37.47-1991 [R1992]  
MINIMUM TEST POINTS PLOTTED SO VARIATIONS SHOULD BE MINUS

THIS DRAWING WAS PRODUCED ON A CAD SYSTEM, ANY MANUAL REVISION WILL VOID IT.

Reference Data  
R240-91-72  
Page 2 of 2