



## Bag filtration that requires no bag filter housing

Eaton's BANDSEAL filter bags are suitable for low pressure and non-critical open filtration applications.

BANDSEAL monofilament filter bags feature a wide range of retention ratings. They are designed for open surface filtration without a bag filter housing to retain particles that are larger than the respective pore size.

### Features and Benefits

- Non-deformable monofilament material is woven into a specific pattern with fusion-welded intersections for extra strength
- All nylon monofilament grades < 125 µm are manufactured with a twill-tape envelope on the side seam and bottom seam
- Drawstring permits installation directly on the end of a pipe or outlet, without an adapter
- Material is free from silicone and crater-forming substances<sup>1</sup>

### Filter Specifications

**Material**  
Monofilament nylon

**Drawstring**  
Polyester

**Retention ratings**  
25, 50, 80, 100, 125, 150, 200, 250, 300, 400, 600, 800 µm

### Dimensions/Parameters

**Sizes**  
01: Ø 180 x 430 mm L  
43: Width: 140 x 305 mm L  
45: Width: 140 x 508 mm L

**Filter area**  
01: 0.24 m<sup>2</sup>  
43: 0.08 m<sup>2</sup>  
45: 0.14 m<sup>2</sup>

**Max. operating temperature**  
190 °C

**Max. flow rates<sup>2</sup>**  
01: 20 m<sup>3</sup>/h  
43: 6 m<sup>3</sup>/h  
45: 12 m<sup>3</sup>/h




Powering Business Worldwide

# BANDSEAL Filter Bag Range

## Retention Ratings

Material	Code	Retention ratings (in µm)											Max. operating temperature (°C)	Sizes				
		25	50	80	100	125	150	200	250	300	400	600		800	01	43	45	
Nylon monofilament mesh	NMO	■	■	■	■	■	■	■	■	■	■	■	■	■	190	■	■	■

## Ordering Information



<sup>1</sup> Based on an accepted paint compatibility test (see document QUC-STA-10).

<sup>2</sup> For liquids with a dynamic viscosity of 1 mPa·s @ 20 °C.

**North America**  
44 Apple Street  
Tinton Falls, NJ 07724  
Toll Free: 800 656-3344  
(North America only)  
Tel: +1 732 212-4700

**Europe/Africa/Middle East**  
Auf der Heide 2  
53947 Nettersheim, Germany  
Tel: +49 2486 809-0

Friedensstraße 41  
68804 Altlußheim, Germany  
Tel: +49 6205 2094-0  
An den Nahewiesen 24  
55450 Langenlonsheim, Germany  
Tel: +49 6704 204-0

**China**  
No. 3, Lane 280,  
Linhong Road  
Changning District, 200335  
Shanghai, P.R. China  
Tel: +86 21 5200-0099

**Singapore**  
100G Pasir Panjang Road #07-08  
Singapore 118523  
Tel: +65 6825-1668

**Brazil**  
Rua Clark, 2061 - Macuco  
13279-400 - Valinhos, Brazil  
Tel: +55 11 3616-8400

**For more information, please email us at [filtration@eaton.com](mailto:filtration@eaton.com) or visit [www.eaton.com/filtration](http://www.eaton.com/filtration)**

© 2018 Eaton. All rights reserved. All trademarks and registered trademarks are the property of their respective owners. All information and recommendations appearing in this brochure concerning the use of products described herein are based on tests believed to be reliable. However, it is the user's responsibility to determine the suitability for his own use of such products. Since the actual use by others is beyond our control, no guarantee, expressed or implied, is made by Eaton as to the effects of such use or the results to be obtained. Eaton assumes no liability arising out of the use by others of such products. Nor is the information herein to be construed as absolutely complete, since additional information may be necessary or desirable when particular or exceptional conditions or circumstances exist or because of applicable laws or government regulations.

EN  
EF-FTB-11  
03-2018