



Models 128, 129, 130, 135: High-performance filter bags for paints and coatings

Eaton's LOFCLEAR 100 models LCR-128, 129, 130 and 135 are specially developed for the filtration of paints and varnishes in the automotive industry and provide reliable solutions for the removal of solids and oils.

Each of these four LOFCLEAR 100 filter bag models has a special function for paint and varnish applications in the automotive industry.

LCR-128

Consists of an electrostatically charged medium and is suitable for the adsorption of particles and oils in e-coat and other paint systems.

LCR-129

Made from double-layer material and suitable for oil adsorption. Ensures cost-effective, excellent performance and long service life during e-coat processes.

LCR-130

The multi-layer construction offers high particle removal efficiency and optimized oil adsorption capacity fulfilling the requirements for coating applications.

LCR-135

An especially thick melt-blown polypropylene material delivers high particle and oil removal for clearcoat applications where pigment removal is not an issue.

Features and benefits

- High-strength sewn multi-layer filter bag construction with welded SENTINEL® seal ring
- Layers of melt-blown polypropylene filter material help to clean fluid gradually and reliably
- Patented SENTINEL seal ring provides 100% bypass-free filtration
- Spunbond cover layer virtually eliminates fiber release and migration
- Material is free from silicone and crater-forming substances¹
- Eaton strongly recommends the use of an insertion tool that facilitates the insertion of the filter bag into the bag filter housing and ensures the correct alignment of the filter bag inside the restrainer basket

Filter specifications

Material

Melt-blown polypropylene

Cover layer

Spunbond polypropylene

Seal ring

Welded polypropylene SENTINEL seal ring

Retention ratings²

10, 20, 30, 40 µm
@ > 99% efficiency

Dimensions/Parameters

Sizes

01: Ø 7 x 17" L (180 x 430 mm)
02: Ø 7 x 32" L (180 x 810 mm)

Filter area

01: 2.6 ft² (0.24 m²)
02: 5.2 ft² (0.48 m²)

Max. operating temperature

194 °F (90 °C)

Max. differential pressure

36.2 psi (2.5 bar)

Recommended change-out pressure for disposal³

11.6 – 21.7 psi (0.8 – 1.5 bar)

Max. flow rates⁴

01: 35 GPM (8 m³/h)
02: 66 GPM (15 m³/h)



Powering Business Worldwide

LOFCLEAR 100 Automotive Filter Bag Range


Filter removal efficiency

Models size 01/02	Particle sizes (µm) at common removal efficiencies (%)				Δp psi (bar) size 02 @ 44 GPM (10 m³/h)	Max. operating temperature °F (°C)
	> 60%	> 90%	> 95%	> 99%		
118/128	25	35	37	40	< 0.2 (0.01)	194 (90)
119/129	15	25	27	30	< 0.2 (0.01)	194 (90)
130	6	14	15	20	0.7 (0.05)	194 (90)
135	1	6	8	10	0.3 (0.02)	194 (90)

Welded SENTINEL seal ring



Ordering information



¹ Based on an accepted paint compatibility test (see document QUC-STA-10).

² Reference values based on single pass tests in ambient lab conditions with ISO test dust in water at 44 GPM (10 m³/h)/size 02.

³ Depending on the respective application requirements.

⁴ For liquids with a dynamic viscosity of 1 mPa·s @ 68 °F (20 °C).

North America

44 Apple Street
 Tinton Falls, NJ 07724
 Toll Free: 800 656-3344
 (North America only)
 Tel: +49 2486 809-0

Europe/Africa/Middle East

Auf der Heide 2
 53947 Nettersheim, Germany
 Tel: +49 2486 809-0

Friedensstraße 41
 68804 Altlußheim, Germany
 Tel: +49 6205 2094-0

An den Nahewiesen 24
 55450 Langenlonsheim, Germany
 Tel: +49 6704 204-0

China

No. 3, Lane 280,
 Linhong Road
 Changning District, 200335
 Shanghai, P.R. China
 Tel: +86 21 5200-0099

Singapore

4 Loyang Lane #04-01/02
 Singapore 508914
 Tel: +65 6825-1668

Brazil

Av. Julia Gaioli, 474 – Bonsucesso
 07251-500 – Guarulhos, Brazil
 Tel: +55 11 2465-8822

For more information, please
 email us at filtration@eaton.com
 or visit www.eaton.com/filtration

© 2016 Eaton. All rights reserved. All trademarks and registered trademarks are the property of their respective owners. All information and recommendations appearing in this brochure concerning the use of products described herein are based on tests believed to be reliable. However, it is the user's responsibility to determine the suitability for his own use of such products. Since the actual use by others is beyond our control, no guarantee, expressed or implied, is made by Eaton as to the effects of such use or the results to be obtained. Eaton assumes no liability arising out of the use by others of such products. Nor is the information herein to be construed as absolutely complete, since additional information may be necessary or desirable when particular or exceptional conditions or circumstances exist or because of applicable laws or government regulations.

US
 EF-FTB-05b
 06-2016



Powering Business Worldwide

