

Industrial process filter cartridges



EATON

Powering Business Worldwide

Wide range of filter cartridges offer complete filtration solutions for industrial processes

Cartridge filters can be the logical choice for a variety of applications. Eaton provides high quality depth, pleated and membrane filter cartridges with retention ratings ranging from 0.05 μm and 150 μm with outstanding dirt-holding capacity.

In addition to a wide range of sizes and various adapter codes, Eaton offers cartridges with different filter materials such as polypropylene, nylon, PTFE and more.

Eaton's industrial process filter cartridges provide consistent, high performance and cost-effective solutions for both common and more challenging industrial applications, varying from pre-filter for high purity water up to final filtration for paints and lacquers, or total filtration for various chemicals. The product range contains many single and multi-cartridge filter housings made of stainless steel and plastic designed for ease-of-use, even in the most demanding industries and filtration applications. Eaton also supplies a wide range of customized filtration and separation solutions.

Markets

- Chemical
- Oil & Gas
- Cosmetics
- Power
- Electronics
- Pulp & Paper
- Metals
- Water/Wastewater



Industrial Process Filter Cartridges

Selection guide

DEPTH FILTER CARTRIDGES



LOFTREX™ / LOFTREX™ Nylon

Nominal rated filter cartridges are manufactured from meltblown polypropylene or nylon microfibers for general industrial applications.



LOFTREX™ M

95% nominal rated filter cartridges are manufactured from high purity polypropylene microfibers. Available with support core and various end caps for a wide range of applications.



LOFTOP™

99.98% absolute rated filter cartridges made of polypropylene microfibers. Available with support core and various end caps for the most demanding applications requiring high efficiency and performance.



LOFMET™

Porous titanium or stainless steel 316 filter cartridges are designed for applications involving extreme operating conditions and aggressive fluids and gases.

PLEATED FILTER CARTRIDGES



LOFPLEAT™ EE

Pleated polypropylene filter media provides a high filtration surface area for nominal rated filtration performance in a wide range of applications.



LOFPLEAT™ AG

Pleated polypropylene filter media provides an absolute filtration in a wide range of applications.



LOFPLEAT™ GG

Features high efficiency micro fiberglass media for a wide variety of industrial applications requiring chemical resistance and long life.



LOFPLEAT™ HF and HF-G

Large diameter cartridges designed with pleated media construction in polypropylene or micro fiberglass combines high surface area with an inside-out filtration flow. Suitable for use in high flow filter housings as well as bag filter housings (with conversion kit).

MEMBRANE FILTER CARTRIDGES



LOFPLEAT™ CP

Large diameter cartridges combine high efficiency with extreme surface area for retrofitting in specific filtration systems.



LOFMEM™ W and N

Industrial grade PES and Nylon 66 membrane filter cartridges offer high efficiencies combined with large filtration area for general and specialized industrial applications.



LOFMEM™ T and TFA

Industrial grade PTFE membrane filter cartridges offer precision filtration under harsh, corrosive environments and are commonly applicable in various tank venting applications. Available with polypropylene components (LOFMEM T) or all fluoropolymer construction (LOFMEM TFA).

Overview of available adapter codes

ADAPTER CODES




Code (): Double open end (DOE) without end caps (only LOFTREX and LOFTOP)



Code G: Double open end (DOE) with foamed Polypropylene flat gaskets (only LOFTREX and LOFTOP)



Code DOE: Double open end (DOE) with flat gaskets (only LOFPLEAT, LOFMEM and LOFMET)



Code 1: Single open end (SOE) with double bayonet adapter (2-226 O-ring) and flat end cap



Code 2: Single open end (SOE) with adapter (2-222 O-ring) and end cap with fin

ADAPTER CODES



Code 3: Single open end (SOE) with double bayonet adapter (2-226 O-ring) and end cap with fin



Code 4: Single open end (SOE) with adapter (2-222 O-ring) and flat end cap



Code M1 and M2: Single open end (SOE) with 3/4" male NPT threaded end (Code M1) respectively 1" male NPT threaded end (Code M2) (only LOFMET)



Code 10 and 20: Double open end (DOE) with internal O-ring (Code 10); Single open end (SOE) with internal O-ring (Code 20)

Technical data

Filter cartridge type	LOFTREX	LOFTREX Nylon	LOFTREX M	LOFTOP	LOFMET
Filter material	Polypropylene	Polyamide 6.6	Polypropylene	Polypropylene	Titanium and stainless steel 316
Retention rating (µm)	1, 3, 5, 10, 20, 50, 75	1, 5, 10, 25, 50, 100	1, 3, 5, 10, 20, 50, 150	0.5, 1, 3, 5, 10, 20, 50, 120	0.5, 1, 5, 10, 15, 35, 50, 100
Retention efficiency	80%	90%	95%	99.98%	99.5%
Lengths (nominal)	9.75", 10", 20", 29.25", 30", 40"	9.75"; 19.25", 20"; 29.25", 30"; 40"	10", 20", 29.25", 30", 39", 40"	9.75", 10", 19.5", 20", 29.25", 30", 39", 40"	5", 9.75", 10", 20", 30", 40"
Adapter code	()	–	(), G, 1, 2, 3, 4	(), G, 1, 2, 3, 4	DOE, 1, 4, M1, M2
Inner core	–	–	Polypropylene	Polypropylene (optional: stainless steel)	–
End caps	–	–	Polypropylene	Polypropylene	Titanium and stainless steel 316
Cages	–	–	–	–	–
Max. operating temperature	149 °F (65 °C)	248 °F (120 °C)	149 °F (65 °C)	176 °F (80 °C)	700 °F (371 °C)
Max. pressure difference in flow direction	36 psid at 77 °F (2.5 bar at 25 °C)	36 psid at 70 °F (2.5 bar at 21 °C)	58 psid at 77 °F (4.0 bar at 25 °C)	58 psid at 77 °F (4.0 bar at 25 °C)	250 psid (17.4 bar)

Technical data

Filter cartridge type	LOFPLEAT EE	LOFPLEAT AG	LOFPLEAT GG	LOFPLEAT HF	LOFPLEAT HF-G	LOFPLEAT CP
Filter material	Polypropylene	Polypropylene	Fiberglass	Polypropylene	Fiberglass	Polypropylene
Retention rating (µm)	0.2, 0.45, 1, 5, 10, 25	0.2, 0.45, 1, 5, 10, 25, 50	0.45, 1, 3, 10	1, 5, 10, 20	1, 2.5, 4.5, 10, 20	1, 5, 10, 20, 40, 70
Retention efficiency	90%	99.98%	90%	99.9%	99.9%	99.98%
Lengths (nominal)	10", 20", 30", 40"	10", 20", 30", 40"	10", 20", 30", 40"	20", 40", 60"	20", 40", 60"	40", 60"
Adapter code	DOE, 1, 2, 3, 4, 10, 20	DOE, 1, 2, 3, 4, 10, 20	DOE, 1, 2, 3, 4, 10, 20	–	–	–
Inner core	Polypropylene	Polypropylene	Polypropylene	–	–	Polypropylene
End caps	Polypropylene	Polypropylene	Polypropylene	Polypropylene	Polypropylene or polyacetal	Polypropylene
Cages	Polypropylene	Polypropylene	Polypropylene	Polypropylene	Polypropylene or polyester	Polypropylene
Max. operating temperature	176 °F (80 °C)	176 °F (80 °C)	176 °F (80 °C)	176 °F (80 °C)	Polypropylene: 180 °F (82 °C) Polyacetal: 230 °F (110 °C)	176 °F (80 °C)
Max. pressure difference in flow direction	58 psid at 70 °F (4.0 bar at 21 °C) 35 psid at 176 °F (2.4 bar at 80 °C)	58 psid at 70 °F (4.0 bar at 21 °C) 35 psid at 176 °F (2.4 bar at 80 °C)	58 psid at 70 °F (4.0 bar at 21 °C) 35 psid at 176 °F (2.4 bar at 80 °C)	43 psid at 70 °F (3.0 bar at 21 °C)	Polyacetal: 75 psid at 70 °F (5.2 bar at 21 °C) 50 psid at 230 °F (3.4 bar at 110 °C) Polypropylene: 50 psid at 77 °F (3.4 bar at 25 °C) 20 psid at 180 °F (1.4 bar at 82 °C)	50.7 psid at 77 °F (3.5 bar at 25 °C)

Filter cartridge type	LOFMEM W	LOFMEM N	LOFMEM T	LOFMEM TFA
Filter material	Polyethersulfone (PES)	Nylon 66 membrane	PTFE membrane	PTFE membrane
Retention rating (µm)	0.05, 0.1, 0.2, 0.45, 0.65	0.20, 0.45, 1.00	0.05, 0.1, 0.2, 0.45, 1	0.1, 0.2, 0.45, 1
Retention efficiency	Absolute	Absolute	Absolute	Absolute
Lengths (nominal)	10", 20", 30", 40"	10", 20", 30", 40"	10", 20", 30", 40"	10", 20", 30", 40"
Adapter code	DOE, 1, 2, 3, 4, 20	DOE, 1, 2, 3, 4, 10, 20	DOE, 1, 2, 3, 4, 10, 20	4
Inner core	Polypropylene	Polypropylene	Polypropylene	PFA
End caps	Polypropylene	Polypropylene	Polypropylene	PFA
Cages	Polypropylene	Polypropylene	Polypropylene	PFA
Max. operating temperature	180 °F (82 °C)	176 °F (80 °C)	203 °F (95 °C)	338 °F (170 °C)
Max. pressure difference in flow direction	60 psid at 80 °F (4.1 bar at 27 °C) 30 psid at 160 °F (2.0 bar at 71 °C) 15 psid at 200 °F (1.0 bar at 93 °C)	58 psid at 81 °F (4.0 bar at 21 °C)	75 psid at 70 °F (5.2 bar at 21 °C) 40 psid at 176 °F (2.8 bar at 80 °C) 15 psid at 203 °F (1.0 bar at 95 °C)	NA

North America
44 Apple Street
Tinton Falls, NJ 07724
Toll Free: 800 656-3344
(North America only)
Tel: +1 732 212-4700

Europe/Africa/Middle East
Auf der Heide 2
53947 Nettersheim, Germany
Tel: +49 2486 809-0

Friedensstraße 41
68804 Altlufheim, Germany
Tel: +49 6205 2094-0

An den Nahewiesen 24
55450 Langenlonsheim, Germany
Tel: +49 6704 204-0

China
No. 3, Lane 280,
Linhong Road
Changning District, 200335
Shanghai, P.R. China
Tel: +86 21 5200-0099

Singapore
100G Pasir Panjang Road #07-08
Singapore 118523
Tel: +65 6825-1668

Brazil
Av. Ermano Marchetti, 1435 -
Água Branca, São Paulo - SP,
05038-001, Brésil
Tel: +55 11 3616-8461

**For more information, please
email us at filtration@eaton.com
or visit www.eaton.com/filtration**

© 2019 Eaton. All rights reserved. All trademarks and registered trademarks are the property of their respective owners. All information and recommendations appearing in this brochure concerning the use of products described herein are based on tests believed to be reliable. However, it is the user's responsibility to determine the suitability for his own use of such products. Since the actual use by others is beyond our control, no guarantee, expressed or implied, is made by Eaton as to the effects of such use or the results to be obtained. Eaton assumes no liability arising out of the use by others of such products. Nor is the information herein to be construed as absolutely complete, since additional information may be necessary or desirable when particular or exceptional conditions or circumstances exist or because of applicable laws or government regulations.

US
04-2019

