



LOFPLEAT™ HF high flow filter cartridges

Eaton's LOFPLEAT HF filter cartridges can be used in a variety of applications where high flow capacity is required including chemical and water systems.

LOFPLEAT HF filter cartridges are designed with pleated polypropylene construction to provide a high total surface area. A single LPHF cartridge can replace several standard cartridge elements. Change-outs are quick and easy. Unlike standard design cartridges, the flow is inside out. The result is higher dirt-holding capacity.

Features and benefits

- Higher flow capacity reduces required number of cartridges
- Lower initial costs with smaller filter housings
- Less labor required for change-outs
- Available with absolute rated filter material at 1, 5, 10, 20 µm retention ratings
- Inside-out flow for greater dirt-holding capacity

- Capable of flow rates up to 500 GMP (1892.5 l/min) in a single 60" length
- Can be retrofitted in most competitive high-flow housings
- FDA listed (U.S. CFR, Title 21) materials of construction for food and beverage contact

Design

Filter material
Polypropylene

Cage, end caps
Polypropylene

Gaskets/O-rings
EPDM (standard),
Fluorelastomer

Retention ratings
1, 5, 10, 20 µm
@ 99.9% efficiency

Technical data

Nominal lengths
20", 40", 60" (508, 1016, 1524 mm)

Outside diameter
6" (1524 mm)

Surface area
25.8 ft² (2.4 m²) per 20" element

Max. operating temperature
176 °F (80 °C)

Max. differential pressures
43 psid @ 70 °F (3.0 bar @ 21 °C)

Recommended differential change-out pressure for disposal
29 psid (2.0 bar)

Max. flow rates
20" element: 175 USGPM (662 l/min)
40" element: 350 USGPM (1325 l/min)
60" element: 500 USGPM (1892 l/min)




Powering Business Worldwide

LOFPLEAT HF high flow filter cartridges


Flow rate*

(68°F/20°C per 40" filter cartridge for water)



* For liquids other than water, multiply pressure drop by fluid viscosity in centipoise.

Ordering code



North America
 44 Apple Street
 Tinton Falls, NJ 07724
 Toll Free: 800 656-3344
 (North America only)
 Tel: +1 732 212-4700

China
 No. 3, Lane 280,
 Linhong Road
 Changning District, 200335
 Shanghai, P.R. China
 Tel: +86 21 5200-0099

Europe/Africa/Middle East
 Auf der Heide 2
 53947 Nettersheim, Germany
 Tel: +49 2486 809-0

Singapore
 100G Pasir Panjang Road #07-08
 Singapore 118523
 Tel: +65 6825-1668

Friedensstraße 41
 68804 Altlußheim, Germany
 Tel: +49 6205 2094-0
 An den Nahewiesen 24
 55450 Langenlonsheim, Germany
 Tel: +49 6704 204-0

Brazil
 Rua Clark, 2061 - Macuco
 13279-400 - Valinhos, Brazil
 Tel: +55 11 3616-8400

For more information, please
 email us at filtration@eaton.com
 or visit www.eaton.com/filtration

© 2018 Eaton. All rights reserved. All trademarks and registered trademarks are the property of their respective owners. All information and recommendations appearing in this brochure concerning the use of products described herein are based on tests believed to be reliable. However, it is the user's responsibility to determine the suitability for his own use of such products. Since the actual use by others is beyond our control, no guarantee, expressed or implied, is made by Eaton as to the effects of such use or the results to be obtained. Eaton assumes no liability arising out of the use by others of such products. Nor is the information herein to be construed as absolutely complete, since additional information may be necessary or desirable when particular or exceptional conditions or circumstances exist or because of applicable laws or government regulations.

US
 EF-LPHF
 05-2018