




Hydraulic strut cutter

(for 4Dimension strut & various traditional channels)

- Patented **esp*** hydraulic strut cutter easily cuts 4Dimension strut and a variety of B-Line strut profiles to size in seconds
- Produces clean cuts without burrs or sharp edges - no post processing necessary
- Lightweight, black anodized 7075-T651 aluminum frame is portable to the jobsite - 65 lbs. (29.4kg)
- Collapsible handle creates a sturdy operations platform
- 10,000psi hydraulic power source and hose with universal coupling required for operation (sold separately)
- Adjustable material rest* feeds strut sections straight into cutter
- Adjustable backstop* provides for easy production cutting
- Die sets available for cutting 4D21, 4D22, B22, B24, B26, B52, B54, B56 strut profiles (see back for catalog numbers)
- Die life: thousands of cuts from a single set of blades

*requires two (2) sections of 1" OD tubing - sold separately



Part No.	Description	Wt./C	
		Lbs.	kg
BHSC100	complete esp set includes cutter, hydraulic pump & hose, material rest, backstop and the three (3) die sets listed below	173	(78.5)
Die Sets for Channel			
BHSC100B22	B22, B24, B26, B52, B54, B56	13	(5.9)
BHSC1004D22	4D22	13	(5.9)
BHSC1004D21	4D21	13	(5.9)



Eaton
 1000 Eaton Boulevard
 Cleveland, OH 44122
 United States
 Eaton.com

© 2015 Eaton
 All Rights Reserved
 Printed in USA
 Publication No. 4DSSCUT-15
 May 2015

B-Line Division
 509 West Monroe Street
 Highland, IL 62249
 Phone: 800-851-7415
 Fax: 618-654-1917
 www.eaton.com/b-lineseries

Eaton is a registered trademark
 All other trademarks are property
 of their respective owners.

