Arrow Hart commercial grade GFCI receptacles with audible alarm

| Project Name: | Prepared By: |
|-----------------|--------------|
| Project Number: | Date: |
| Catalog Number: | Type: |



TRSGFA15

Description

2-pole, 3-wire grounding 15A, 125V/AC 20A, 125V/AC









Design features

- Performs periodic self-tests to ensure integrity of GFCI
- Visual trip indicator light gives guick notification of a tripped or "end of life" condition
- · Audible alarm notifies user of tripped GFCI. Alarm can be turned off by sliding the switch on the device face if required
- Meets and exceeds 10 kA short circuit testing and Underwriters Laboratories (UL) UL943 safety standards
- Automatic grounding system eliminates need for bonding jumper in grounded metal enclosure, provides redundant measure of ground continuity where jumper is used
- Ground termination with back wire clamp provides secure wiring and reduces installation time
- Tamper resistant shutters help prevent foreign objects from being inserted
- Line side terminals are backed out and staked for fast installation
- Horizontal test/reset button alignment provides larger unobstructed area
- Test and reset buttons are color matched to provide superior aesthetics
- Tapered back wire openings handle multiple wire sizes and types for applications up to #10 AWG solid or stranded wire
- When downstream receptacles are wired from load side, a 20A feed-through rating offers full protection
- · Line-load miswiring protection: GFCIs will not provide power downstream when wired incorrectly
- Tri-combo head terminal and mounting screws
- UL Listed, fully compliant with all latest UL943 Class A GFCI requirements
- Tamper resistant models comply with 2017 and 2020 NEC Article 406.12
- Black tamper resistant shutters create seamless look
- Longer, wider "bridged" strap provides 40% more contact area with wallboard, virtually eliminating floating installations
- Matching standard size thermoplastic wallplate included (midsize wallplate on TRSGFA15W-M)

Compliances, specifications and availability are subject to change without notice.



| ı | Project Name: | Prepared By: |
|---|-----------------|--------------|
| | Project Number: | Date: |
| | Catalog Number: | Type: |

Table 1. Commercial grade

| | | Rating | | | |
|-------------|---|--------|------|-------|----------------------------|
| Catalog no. | Description | A | V/AC | NEMA | Color suffix |
| □ TRSGFA15 | Tamper resistant self-test GFCI w/ audible alarm w/ standard-size wallplate, back & side wire | 15 | 125 | 5-15R | A, B, BK, GY, LA, V, W |
| ☐ TRSGFA20 | Tamper resistant self-test GFCI w/ audible alarm w/standard-size wallplate, back & side wire | 20 | 125 | 5-20R | A, B, BK, GY, LA, RD, V, W |
| ☐ TRSGFA15M | Tamper resistant self-test GFCI w/ audible alarm w/ mid-size wallplate, back & side wire | 15 | 125 | 5-15R | W |
| □ SGFDA20 | Self test blank face / dead front GFCl w/ audible alarm w/ standard-size wallplate, back & side wire | 20 | 125 | | A, B, BK, GY, LA, V, W |

Table 2. GFCI status indicator

| EOL indicator RED LED | Trip indicator AMBER LED | Trip indicator ALARM (Sound) | Diagnosis | Action |
|--------------------------|-----------------------------|---------------------------------|--|--|
| OFF | OFF | OFF | Device is functioning properly OR branch circuit may have no power | Manually depress TEST button to trip device. Amber light should come ON If Amber light does <u>not</u> come ON, check if there is power to the branch If Amber light does come ON, manually depress the RESET button to restore power to the device If GFCI does not reset, replace GFCI If GFCI does reset, device is functioning properly |
| OFF | ON | ON | Device is in tripped state | Manually depress the RESET button to restore power to the device • If GFCI does not reset, replace GFCI |
| Blinking or ON | OFF | OFF | Device's "end of life" indication OR device is in reset state | Manually depress TEST button to trip device. Amber light should come ON • If Amber light does <u>not</u> come ON, check if there is power to the branch • If Amber light does come ON, manually depress the RESET button to restore power to the device • If it does not reset, and/or the blinking continues, replace GFCI |
| Blinking or ON | ON | ON | Device's "end of life" indication OR device is in tripped state | Manually depress the RESET button to restore power to the device • If it does not reset, and/or the blinking continues, replace GFCI |

 $^{^{\}ast}$ Alarm can be turned off by sliding the switch available on the face of GFCI $\mathbf{E0L}$ – End of Life

Applications

GFCI receptacles are designed with the safety of the user in mind. In commercial and industrial areas like public bathrooms, breakrooms and food service areas, the NEC requires GFCI receptacles. Arrow Hart GFCI receptacles are UL Listed and fully compliant with all of the latest UL943 Class A GFCI and UL498 requirements. Additionally, GFCIs incorporate lock-out functionality to protect against mis-wired line-load connections and GFCI circuitry damage. Audible alarm GFCI receptacles are perfect for low traffic areas, such as garages or basements, where LED indicator lights may not be as visible.

Table 3. Specifications

| Catalog no. | TRSGFA 15A & 20A | SGFDA20 | |
|------------------------------|--|--|--|
| Device type | Specification grade | Specification grade tamper resistant duplex | |
| Wiring type | Back & side wire | Back & side wire | |
| Testing & code compliance | cULus Listed to UL 498 and UL 943, file no. E60120 Meets all UL 943 (GFCI), UL 498 (receptacles) and applicable CSA requirements NOM certified | cULus Listed to UL 498 and UL 943, file no. E60120 Meets all UL 943 (GFCI), UL 498 (receptacles) and applicable CSA requirements NOM certified | |
| Environmental specifications | Flammability: Meets UL 94 requirements; V2 rated Temperature rating: -35°C to 66°C (-31°F to 150.8°F) | Flammability: Meets UL 94 requirements; V2 rated Temperature rating: -35°C to 66°C (-31°F to 150.8°F) | |
| Electrical specifications | Dielectric voltage: Withstands 2000V per UL 498 Current interrupting: Yes, at full-rated current Temperature rise: Max. 30°C (86°F) after 100 cycles of overload @ 150% of rated current (DC) Trip time: 0.025 seconds (Class A) Frequency: 60 Hz; Voltage: 125V; Amperage: 15A/20A 20A feed-through Short circuit testing: Meets and exceeds 10 kA Maximum interrupting capacity: 20 Amps | Dielectric voltage: Withstands 2000V per UL 498 Current interrupting: Yes, at full-rated current Temperature rise: Max. 30°C (86°F) after 100 cycles of overload ② 150% of rated current (DC) Trip time: 0.025 seconds (Class A) Frequency: 60 Hz; Voltage: 125V; Amperage: 20A feed-through Short circuit testing: Meets and exceeds 10 kA Maximum interrupting capacity: 20 Amps | |
| Mechanical specifications | Terminal accommodation: #14 - 10 AWG Voltage ratings: Permanently marked on device | Terminal accommodation: #14 - 10 AWG Voltage ratings: Permanently marked on device | |

| Project Name: | Prepared By: |
|-----------------|--------------|
| Project Number: | Date: |
| Catalog Number: | Type: |

Table 4. Audible alarm

| Catalog no. | TRSGFA 15A & 20A | SGFDA20 |
|-------------------------------|---------------------------------|---------------------------------|
| Minimum sound level intensity | 70 dB at 10 cm at rated voltage | 70 dB at 10 cm at rated voltage |

Table 5. Illumination


| Catalog no. | TRSGFA 15A & 20A | SGFDA20 | |
|--------------------------|--|---------------------------------|---|
| Top housing | Thermoplastic, polycarbonate 6/6 | Thermoplastic, nylon 6/6 | _ |
| Bottom housing | Thermoplastic, PVC | Thermoplastic, PVC | |
| Strap | 0.040" thick steel, zinc-plated | 0.040" thick steel, zinc-plated | |
| Line contacts | 0.030" thick brass | 0.030" thick brass | |
| Terminal & ground screws | #8-32 steel, brass-plated; neutral screw nickel-plated, ground screw green | | |
| Terminal clamps | 0.070" thick steel | | |

Table 6. Color ordering information

For ordering devices, include Cat. no. followed by the color code: A (Almond), B (Brown), BK (Black), GY (Gray), LA (Light Almond), V (Ivory), W (White)



Product dimensions








Figure 2. TRSGFA 20A Line art with dimensions

| Project Name: | Prepared By: |
|-----------------|--------------|
| Project Number: | Date: |
| Catalog Number: | Type: |

Product dimensions




Figure 3. SGFDA20 Line art with dimensions

Certifications & compliances

| Catalog no. | c(UL)us | NUM 426 |
|-------------|---------|------------|
| TRSGFA15 | • | • |
| TRSGFA20 | • | • |
| TRSGFA15W-M | • | • |
| SGFDA20 | • | • |

KEY: 6 Us CULus NOM

COLUS 426 NO

Parts are manufactured and designed in accordance with article 4 of the European Union's RoHS2 directive 2011/65/EU

Compliances, specifications and availability are subject to change without notice.

Electrical Sector 203 Cooper Circle Peachtree City, GA 30269 United States Eaton.com Eaton.com/arrowhart Electrical Sector Canada Operations 5925 McLaughlin Road Mississauga, Ontario, L5R 1B8 Canada EatonCanada.ca Eaton.com/arrowhart Electrical Sector Mexico Operations Carr. TlaInepantla -Cuautitlán Km 17.8 s/n Col. Villa Jardín esq. Cerrada 8 de Mayo Cuautitlán, México CP 54800 México Eaton.mx Eaton.com/arrowhart

